EDGE[™] Housing

1 rack unit, holds up to 12 EDGE modules or panels



 $\mathsf{EDGE}^{^{\bowtie}}$ HD solutions are high-density preterminated optical cabling solutions offering industry-leading connector density. With unprecedented finger access, there is no need for additional tools enabling faster moves, adds and changes (MACs).

Features and Benefits

Universal wired components

Enable moves, adds and changes without polarity concerns; provide a simple migration path between 2-fiber and parallel optic applications

Revolutionary drawer-style hardware

Offers unprecedented finger access while achieving the highest port density in the market

Rotatable trunk strain relief parking plates

Allows for rear cable entry direction, as well as the traditional side cable entry

Padlockable hasp on rear cover

Allows for customer provided padlock and enhanced security







EDGE[™] Housing

1 rack unit, holds up to 12 EDGE modules or panels



Specifications

General Specifications	
Application	Data Center, Data Center LAN/SAN, Enterprise Networks
Product Type	Fiber Optic Hardware
Mounting Type	Rack Mount, Cabinet-mount
Mounting Technology	Adjustable depth settings
Access Type	Front and rear access slidable
Lockable	Yes, rear side

Design - Hardware	
Housing Type	Pretium EDGE® HD
Height Unit	1U
Number of Panels per Housing	12
Housing Color	Silver
Fiber Capacity	144
Cable Entry Direction	Rear
Cable entry type	Side brush entry
Color	Silver
Number of Modules	12

Mechanical Characteristics	
Dimensions (W x D x H)	432 mm x 561 mm x 44 mm (17 in x 22.1 in x 1.75 in)
Weight	6.4 kg (14 lb)

Chemical Characteristics	
RoHS	Free of hazardous substances according to RoHS 2002/95/ EG



EDGE[™] Housing

1 rack unit, holds up to 12 EDGE modules or panels



Ordering Information

Part Number	EDGE-01U-SP
Product Description	EDGE™ Housing, 1 rack unit, holds up to 12 EDGE modules or panels
Module Capacity	12
Trunk Capacity	12 (size 1 or 2)

Shipping Information

Units per Delivery	1/1
Packaging Dimensions (W x D x H)	565 mm x 646 mm x 171 mm (19 in x 22.125 in x 7.75 in)
Packing dimensions (L x W x H)	646 mm x 565 mm x 171 mm
Shipping Weight	8.2 kg (18 lb)



Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA 800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2015 Corning Optical Communications. All rights reserved.

