


Multi-Technology Cards for SIO-Enabled MIFARE® / HID Prox



SECURE CONTACTLESS SMART CARD WITH MIFARE CLASSIC / HID PROX TECHNOLOGIES.

- **Supports Secure Identity Object™ (SIO)** – Multi-layered security beyond the card technology, providing added protection to identity data.
- **Trusted Identity Platform® (TIP™) enabled** – Provides trusted identity within a secure ecosystem of interoperable products.
- **Supports future growth** – MIFARE® Classic 13.56 MHz read/write contactless smart card technology with multiple, securely separated files enables multiple applications for future growth.
- **Flexible configurations** – Many ordering options, including magnetic stripe, external card numbering, vertical slot punch, custom artwork, and contact smart chip module.
- **Ideal migration solution** – Mutual use of SIO-enabled 13.56 Mhz smart card technology and 125 KHz HID Prox.

HID Global SIOs deliver three key benefits: portability, security and extensibility.

- SIOs are defined using open standards that can support any piece of data, including data for access control, biometrics, PC logon, and many other applications.



HID's SIO Technology-Enabled (SE) Cards for MIFARE and 125 KHz HID Prox are part of the next-generation access control platform and open ecosystem based on HID's Trusted Identity Platform™ (TIP) architecture. The SE Card was designed to provide additional key diversification, authentication, encryption and portability for advanced applications, unprecedented mobility, heightened security and enhanced performance.

HID Global's next generation access control platform goes beyond the traditional smart card model to offer a secure, standards-based, technology-independent and flexible identity data structure based on Secure Identity Object (SIO), a new HID portable credential methodology.

The 13.56 MHz read/write contactless SE Card for MIFARE / HID Prox is a credit card-sized smart card credential that can be used for diverse applications such as physical access control, PC logon, biometric verification, time and attendance, cashless vending, public transportation, airline ticketing and customer loyalty programs.

MULTI-TECHNOLOGY SIO-ENABLED (SE) CARDS FOR MIFARE® FEATURES

- 13.56 MHz read/write contactless smart card technology for high-speed, reliable communications with high data integrity.
- MIFARE® Application Directory (MAD) allows flexible programming of additional applications to the MIFARE Classic®.
- MIFARE Classic technology uses a mutual authentication and data encryption with a 32 or 56 bit serial number.
- Securely separated sectors allow complex applications and provide for future expansion.
- 125 KHz HID Prox with convenient read range and flexible format programming
- Durability - Passive, no-battery design allows for an infinite number of reads. Strong and resistant to damage.
- Photo ID Compatible - Print directly to the card with a direct image or thermal transfer printer.
- PVC card surface is optimized for dye sublimation printing.

HIGHER SECURITY

- Trusted Identity Platform (TIP) Enabled - Provides trusted identity within a secure ecosystem of interoperable products.
- Multi-Layered Security - Ensures data authenticity and privacy through the multi-layered security of HID's SIO.
- SIO Data Binding - Inhibits data cloning by binding an object to a specific credential.
- Expanded Elite™ Program - Extends security by providing unique keys for each application area (sector) within an SE card for MIFARE.
- Visual security and anti-counterfeiting features (holograms, ultra-violet fluorescent inks, micro-printing or a custom logo) to easily identify genuine cards.

SPECIFICATIONS



Base Part Number	3500	PVC SE Card for MIFARE® 1K
	3506	PVC SE Card for MIFARE 4K
	3550	Composite PET/PVC SE Card for MIFARE 1K
	3556	Composite PET/PVC SE Card MIFARE 4K
*Card Construction	Thin, flexible polyvinyl chloride (PVC) laminate, or Composite PVC/PET	
Dimensions	2.125" x 3.375" x 0.070" max. (5.40 x 8.57 x 0.18 cm)	
Weight	0.24 oz (6.8 g)	
Operating Temperature	PVC Cards: -40 to 122° F (-40 to 50° C) Composite Cards: -40 to 158° F (-40 to 70° C)	
Operating Humidity	5-95% non-condensing	
Operating Frequency	13.56 MHz for SIO-Enabled MIFARE, 125 KHz for HID Prox	
RF Interface	ISO 14443 A, Parts 1-3	
Transaction Time	<100 ms	
Baud Rate	106 Kbps	
Memory Type	EEPROM, read/write for SIO-Enabled MIFARE	
SIO-Enabled MIFARE Memory Specification	1K Byte (8,192 bits) or 4K Bytes (32,768 bits) Memory Sector 0 is used as the MIFARE® Application Directory (MAD) <ul style="list-style-type: none"> Unique 4 Byte (32 bit) ID per card (CSN) Each sector uses two encryption keys - Key "A" to read only; Key "B" to read/write Each encryption key is 6 Bytes (48 bits) 	
Multi-application Memory	MIFARE 1K: memory arranged in 16 64-Byte Sectors MIFARE 4K: memory arranged in 40 Sectors: 32 sectors of 64 Bytes, 8 sectors of 256 Bytes	
Write Endurance	Min. 100,000 cycles	
Data Retention	10 years	
Typical Maximum Read Range	Up to 4" *Dependent upon installation conditions.	
Card Marking	Inkjet standard, Laser engraving optional	
Custom Graphics	Optional	
Programming	Factory or field programmable	
Operates With	iCLASS SE readers and any reader that can read DESFire or MIFARE, and HID Prox technology.	
Warranty	Lifetime warranty. See complete warranty policy for details.	

ASSA ABLOY

An ASSA ABLOY Group brand

© 2012 HID Global Corporation. All rights reserved. HID, the HID logo and Secure Identity Object are trademarks or registered trademarks of HID Global in the U.S. and/or other countries. All other trademarks, service marks, and product or service names are trademarks or registered trademarks of their respective owners.
2012-04-27-hid-mifare-prox-sio-card-ds-en

North America: +1 949 732 2000

Toll Free: 1 800 237 7769

Europe, Middle East, Africa: +44 1440 714 850

Asia Pacific: +852 3160 9800

Latin America: +52 55 5081 1650