

SmartID® S10, SK10, SW100 and SWK100 Readers

ISO 14443 Reader or Reader/Writer

- ▶ Custom Configurations – Completely configurable for every access control application challenge.
- ▶ Open Architecture Design – ISO 14443A MIFARE®/ DESFire® Contactless smart card, compatible for broad card interoperability.
- ▶ HID MIFARE – Supports secure MIFARE applications including HID Corporate 1000 card formats
- ▶ Field Upgradeable - Use cards or a serial connection to upgrade reader firmware and/or field configuration



ACCESS flexibility.

The SmartID® ISO 14443 reader is a flexible, highly secure and stylish contactless smart card reader ideal for customers that require a customizable reader for new or existing installations. Designed for a wide variety of applications from entry level access control to secure ID management, the reader family is completely configurable for every access control application challenge.

The SmartID reader offers the ultimate choice in interoperability and programmability. Its unique capabilities, such as reading any MIFARE® and/or DESFire® application data file, meet all installation requirements.

SmartID readers provide one of the broadest ranges of card compatibility in the industry and can be configured as a specific solution for each project (see specifications chart on opposite side for specific compatibilities). The SmartID reader is available with or without keypad, adding an extra layer of protection for higher security installations.

- ▶ Configuration cards can further personalize reader configurations to best match installation requirements.
- ▶ Wide voltage span (5 - 24 VDC).
- ▶ Wiegand or Clock-and-Data outputs easily interface with existing access control panels.
- ▶ Communications configurable to RS232, RS485 and RS422 for read only or read/write applications.
- ▶ FlexSmart® MIFARE/DESFire format compatibility.
- ▶ Compatible with HID MIFARE (read-only) applications run on 6055, 6074, 6075 and 6071 readers.

Features

Mounting

The reader easily mounts on a door mullion or single-gang electrical box (using the electrical box cover plate accessories). An LED flashes green and the beeper sounds when reader is presented with MIFARE® and DESFire® or other reader application compatible card. The multiple LEDs and beeper can also be controlled by the host system.

Security

MIFARE®

Contactless smart card and reader platform according to the ISO 14443A. The card structure provides multi-application functionality, whereby each application is secured for read and read/write by security keys. All RF data transmission between card and reader is encrypted using mutual authentication and challenge response to prevent replay attacks. Readers and cards must have matching security keys.

DESFire®

Contactless smart card and reader platform according to ISO 14443 level 4. Featuring DES and 3DES Encryption on all RF data

transmission. The card structure provides multi-application functionality, whereby each application is secured up to 14 different user-definable security keys for read and read/write access. Readers and cards must have matching security keys

Looking for AES encryption with EV1? Search HID Global's website for "High Frequency Migration Readers".

Easily Interfaced

The SmartID® Reader line provides flexible configurable output formats and output protocols. Reader communication supported: Wiegand, Clock-and-Data, ISO 7811 Clock-and-Data ABA Track 2 Emulation, RS232, RS422, RS485 or custom format output.

Indoor/Outdoor Design

Rugged, weatherized polycarbonate enclosure, designed to withstand harsh environments, provides reliable performance and resistance to vandalism.

* Base Model Numbers

	803xD
	8030D SmartID Mullion SIO Reader or SW100 Reader/Writer 8031D SmartID Mullion Keypad SK10 Reader or SWK100 Reader/Writer
Dimensions	5.59" x 1.81" x 0.98" (14.2 x 4.6 x 2.5cm)
Read Range	Up to 1.18" (3.0 cm) Dependent upon installation conditions.
Mounting	Ideally suited for mullion-mounted door installations, any flat surface or over single-gang electrical box (see "Accessories" for more information).
Power Supply	5 - 24 VDC
Current Draw	68 mA AVG, 82 mA PEAK (@ 12 VDC)
Operating Temperature	-13° F to 149° F (-25° C to 65° C) ****.
Operating Humidity	0 – 95% non-condensing
Environmental	IP55
Transmit Frequency	13.56 MHz
Applications	MIFARE (CSN), MIFARE (Sector), Dual MIFARE, DESFire 0.6, T=CL (Read/Write), 3964 (Read/Write)
Reader Outputs	Wiegand, Clock-and-Data, ISO7811 Clock-and-Data ABA Track 2 Emulation, RS232, RS485, RS422 or custom format output
Cable Distance	Wiegand 500 ft (150 m) (18 AWG / 1.02 mm / 0.82 mm2), Clock-and-Data 82 ft (25 m) (22 AWG / 0.65 mm / 0.33 mm2), RS232 15 ft (4.6 m) (24 AWG / 0.51 mm / 0.20 mm2), RS485/RS422 4000 ft (1219 m) (24 AWG / 0.51 mm / 0.20 mm2)
Card Compatibility	ISO 14443A ** – read/write MIFARE, DESFire, * compatibility based on application selected
Certifications	UL294/cUL (US), FCC Certification (US), IC (Canada), CE (EU), C-tick (Australia, New Zealand), SRRC (China), MIC (Korea), NCC (Taiwan), iDA (Singapore), RoHS, IP55
Housing	SB TSG Polymers
Color	Silver
Accessories	8090AS Single-gang Electrical Box Cover 9287AS Spacer Kit 0300A Tamper Switch 0055A Screw Cover 0056A Black Plexiglass Cover
Termination	Terminal Strip
Works With	143x/144x SmartID MIFARE Credentials*** 145x SmartID DESFire Credentials*** 82000 EdgePlus E400 Single Door Controller**** 70100 VertX V100 Door/Reader Interface**** 72000 VertX V2000 Reader Interface/Network Controller****
Warranty	Warrantied against defects in materials and workmanship for life. (See complete warranty policy for details.)

* Additional configuration format must accompany all reader orders. See 13.56MHz How To Order Guide (HTOG) for more details.

** Compatibility based on selected application

*** See 13.56MHz HTOG for more details.

**** See Network Access Solutions HTOG for more details.

***** -20° F (-4° C) is lower temperature bound for keypad readers

© 2010 HID Global. All rights reserved. HID, the HID logo, and iCLASS are trademarks or registered trademarks of HID Global in the U.S. and/or other countries. All other trademarks, service marks, and product or service names are trademarks or registered trademarks of their respective owners. Rev. 10/2010 MKT-SmartID_REV_B_DS_EN



ACCESS experience.

hidglobal.com

HID Global Offices:

Corporate

North America

15370 Barranca Pkwy
Irvine, CA 92618
U.S.A.
Phone: (800) 237-7769
Phone: +1 (949) 732-2000
Fax: +1 (949) 732-2360

Asia Pacific

19/F 625 King's Road
North Point
Island East
Hong Kong
Phone: +852 3160-9800
Fax: +852 3160-4809

Latin America

Circunvalacion Ote. #201 B
Despacho 2
Col. Jardines del Moral
Leon 37160, Gto.
Mexico
Tel: +52 477 779 1492
Fax: +52 477 779 1493

Europe, Middle East & Africa

Haverhill Business Park
Phoenix Road
Haverhill, Suffolk
CB9 7AE
England
Phone: +44 (0) 1440 714 850
Fax: +44 (0) 1440 714 840