



- Jumbo Openings in Sides and Rear
- Bottom Hinging Uses Less Space to Open
- Side Hinging Allows Complete Access to the Rear of Components
- Enhanced Cable Management — Multiple Tie-Off Points for Both Nylon and VELCRO® Brand Ties

Specifications

- 16ga steel construction
- Finish: durable black powder coat
- Wall mount holes on 16" centers
- Width: 19"
- Load capacity:
 - 4 and 6 rack units: 50lb
 - 1 and 2 rack units: 25lb

Standards/Listings/Verifications

- EIA-310-D universal spacing tapped #12-24

Wall Mount Bracket, Bottom-Hinged

Contents: assembled bottom-hinged wall bracket

Rack Units	Height	Width	Depth	Catalog No.
1	1.75" (45)	19" (483)	4" (102)	HPWWB1U4
2	3.50" (89)	19" (483)	4" (102)	HPWWB2U4
2	3.50" (89)	19" (483)	8" (203)	HPWWB2U8
4	7.00" (178)	19" (483)	4" (102)	HPWWB4U4
4	7.00" (178)	19" (483)	8" (203)	HPWWB4U8
6	10.50" (267)	19" (483)	4" (102)	HPWWB6U4
6	10.50" (267)	19" (483)	8" (203)	HPWWB6U8
6	10.50" (267)	19" (483)	18" (457)	HPWWB6U18



HPWWB1U4



HPWWB2U4



HPWWB4U8

Wall Mount Bracket, Side-Hinged

Contents: assembled side-hinged wall bracket

Rack Units	Height	Width	Depth	Catalog No.
2	3.50" (89)	19" (483)	4" (102)	BRMCCMB19X35X4
4	7.00" (178)	19" (483)	4" (102)	BRMCCMB19X7X4
2	3.50" (89)	19" (483)	8" (203)	BRMCCMB19X35X8
4	7.00" (178)	19" (483)	8" (203)	BRMCCMB19X7X8



BRMCCMB19X35X4



BRMCCMB19X7X8

VELCRO® is a registered trademark of Velcro Industries B.V.