

2





1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	WEIGHT
CFPH4**	.47 LB/10 PCS (214 G/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. DIMENSIONS IN [] ARE IN METRIC.
3. PART INCLUDES:
1- FACEPLATE
2- MOUNTING SCREWS



PART NUMBER		CFPH4**	
TITLE		MINI-COM 4 POSITION HORIZONTAL CLASSICE SERIES FACEPLATE	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		D35544CS/00 D35544CS_DC/00C	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .010 [.3] .XX ± .03 [.8]		PANDUIT MATERIAL: ABS	
THIRD ANGLE PROJECTION		DRAWING NUMBER: 35544 - 41	
DRAWN BY	DATE	CHK	SCALE
RCA	4-3-97	HIW	NONE
SHT 1 OF 1		A	

3	4/14/14	JSP	REFR	MMR	REVISED AND REDRAWN, PREVIOUS REVISIONS HAVE BEEN OMITTED.	35544-41
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

2

1

B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A



B

A

