

2




1


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
CPA48HDBL	6.88 LB/10 PCS (3215.2 g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS WITH THIS WIRING SYSTEM
2. THE HIGH DENSITY PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
3. PACKAGE CONTAINS:
 - (1) 48 PORT ANGLED STAMPING
 - (6) 8 POSITION FACEPLATES (ASSEMBLED TO PANEL)
 - (6) GROUNDING STRIPS (ASSEMBLED TO PANEL)
 - (1) SCREW KIT (INCLUDES FOUR #12-24 SCREWS)
 - (1) SCREW KIT (INCLUDES FOUR M6 SCREWS)
 - (2) M6 GROUNDING SCREWS
 - (2) #12-24 GROUNDING SCREWS
4. DIMENSIONS IN [] ARE IN METRIC.



PART NUMBER CPA48HDBL		PRODUCT SPEC/PKG SPEC N/A	
I.T. NUMBER N/A		WORK INSTRUCTION N/A	
TITLE MINI-COM 48 PORT ANGLED HIGH DENSITY SHIELDED MODULAR PATCH PANEL CUSTOMER DRAWING			
ITEM REVISION NAME 11M249AR/00.PRT		PANDUIT TM	
DATASET FILE NAME 11M249AR_DC/00A.PRT			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .x ± .xxx ± .010 (.3) .xx ± .03 (.8) 		MATERIAL : STAMPING-20 GAUGE STAINLESS STEEL GROUNDING STRIP- PHOS BRONZE FACEPLATE-ABS	
THIRD ANGLE PROJECTION		DRAWING NUMBER: 11M249AR-02	
DRAWN BY BJN	DATE 11-26-12	CHK JSP	SCALE NONE
SHT 1 OF 1		SIZE A	

2

1

R	11-26-12	BJN	JSP	JSP	RELEASED TO PRODUCTION	11M249AR-02
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN