

Sentry Smart CDU

Key Features

- > **High Density:** Single-power input feed; 18 outlets per enclosure (Qty 18 x IEC C19)
- > **High Power Distribution:** 208V, 3-phase Delta, 100-Amp input feed option
- > **Input Current Monitor:** Precisely measure the aggregate current draw (in amps) on each phase. On-site verification of the input current with the LED digital display. Remote verification via web browser or serial screen.
- > **IP Access & Security:** Web interface, SSL, SSH, Telnet, SNMP, FTP, SNTp, Syslog, LDAP, LDAPS, RADIUS, TACACS and RS-232 access
- > **SNMP Traps & Alerts:** Provide automated SNMP-based alarms or Email alerts for power and environmental conditions
- > **Environmental Monitoring:** Each Smart CDU supports two external temperature & humidity probes and reports conditions thru the user interface without the need for additional IP addresses
- > **Add an Expansion Module:** Connect the Smart Expansion CDU (CL) to a Master unit (CS) for power monitoring of separate power circuits from a single IP address

CS-18VD/VY 100A with (18) C19 Outlets

High Density Power Distribution

The Smart Cabinet Distribution Units (CDU) provide reliable power distribution combined with local and remote power monitoring and environmental monitoring via IP. Use the network interface to view power, temperature and humidity levels via Web browser, or receive SNMP-based alarms and email alerts when conditions exceed defined thresholds.

Specifically designed for storage devices, blade servers, switches and other rack mounted devices with high current draws, the CS-18VD/VY provides power distribution for 208V 100A power.

The Smart CDU family has the capability to daisy chain units together. The Expansion CDU Module gives the ability to use one IP address across different power circuits.

Additional Benefits:



Branch Circuit Protection

The Sentry CDU Family meets the UL 60950-1 requirement for branch circuit protection.
- UL 489 rated circuit breakers



Input Current Monitoring

Exclusive Digital True RMS current monitoring is critical to preventing overloads in high-density computing environments. LED digital display on the CDU enclosure reports the input current of each phase.



Temperature and Humidity

The Smart CDU supports two external 10' (3m) probes. Each of these probes measure both temperature and humidity. Receive SNMP-based alerts or email notifications when conditions exceed defined thresholds.



Linking for Smart CDU (Expansion Modules)

The Smart CDU family has the capability to daisy chain units together. The Expansion Module provides the ability to link two power circuits under one IP address.



Model	Available Input Voltages	Amperage	Available Input Cord	Outlets	Dimensions (L x W x D)
CS-18VD8454A3 CL-18VD8454A3*	240 V, 3-phase Delta 50/60 Hz	100A	IEC Blue 9hr 3P+G IP67 Plug, 10'(3m), Top Cord Entry	(18) IEC 60320/C19	84.0 x 1.75 x 3.5 in. (2134 x 44 x 89 mm)
CS-18VD9454A3 CL-18VD9454A3*	240 V, 3-phase Delta 50/60 Hz	100A	Unterminated, 10' (3m), Top Cord Entry	(18) IEC 60320/C19	84.0 x 1.75 x 3.5 in. (2134 x 44 x 89 mm)

* CL part numbers refer to the Expansion CDU

Additional Features and Specifications

Agency Approvals

- > US & Canada (cTUVus Mark) to UL 60950-1:2003 and CAN/CSA 22.2 No. 60950-1-03
- > FCC Class A, Part 15
- > CE Mark
- > EMC to EN 55022 Class A, EN 55024 CISPR 22 Class A

Communications and Security

- > 10/100 BaseT Ethernet
- > HTTP/HTTPS
- > SSLv3/TLSv1
- > SNMPv2
- > SSHv2
- > Telnet
- > LDAPS/LDAPv3
- > TACACS+
- > RADIUS
- > RS-232 (Serial)

Branch Circuit Protection

- > Compliant to UL 60950-1

Accessories

- > Optional Temperature & Humidity Probe
 - EMTH-1-1 Temperature & Humidity Probe, 10 ft (3m)
- > Environmental Monitor
 - EMCU-1-1B allows up to (2) additional temperature & humidity probes, (1) water sensor, (4) dry contact closures, (1) analog-to-digital contact sensor. Includes (1) temperature/humidity probe with unit.
- > SPM (Sentry Power Manager) Appliance:
 - Monitor and Manage multiple Sentry CDU's
 - Monitor and Manage all alarm conditions
 - Reporting and Trending
 - Group or Cluster outlets for reboot and power information

1U SPM Appliance



Expansion Module
Model Number

- > CL-18VD8454A3
- > CL-18VD9454A3



Server Technology

HEADQUARTERS - NORTH AMERICA
Server Technology, Inc.
1040 Sandhill Drive
Reno, NV 89521
United States
1.775.284.2000 Tel
1.775.284.2065 Fax
sales@servertech.com
www.servertech.com
www.servertechblog.com

EMEA
Server Technology Intl
Sienna Court
The Broadway
Maidenhead
Berkshire
SL6 1NJ
United Kingdom
+44 (0) 1628 509053 Tel
+44 (0) 1628 509100 Fax
salesintl@servertech.com

APAC
Server Technology Intl
37th Floor, Singapore Land Tower
50 Raffles Place
Singapore 048623
+65 (0) 6829 7008 Tel
+65 (0) 6234 4574 Fax
salesintl@servertech.com