



# Sentry Smart CDU

# **Key Features**

- > High Density: Single Power input feed; 48 outlets per enclosure (Quantity 36xC13 and 12xC19 outlets)
- > Power Distribution: 240/415V 3-Phase Wye 60A power input feed. 43.2kW (34.5kW derated).
- > Input Current Monitor:
  Precisely measure the
  aggregate current draw (in
  amps) of the circuit. On-site
  verification of the input
  current with LED digital
  display. Remote verification
  via web browser or serial
  screen.
- > IP Access & Security: Web interface, SSL, SSH, Telnet, SNMP, FTP, SNTP, Syslog, LDAP, LDAPS, TACACS, RADIUS, and RS-232 access
- > SNMP Traps and Email alerts: Provide automated alerts for power and environmental conditions
- > Environmental Monitoring:
  Each Smart CDU supports two
  external temperature &
  humidity probes and reports
  conditions thru the user
  interface without the need for
  additional IP addresses
- > Add an Expansion Module: Connect the Smart Expansion CDU (CLG) to a Master unit (CSG) for power monitoring of separate power circuits from a single IP address

# CSG-48V5 240/415V 60A Smart POPS Mixed Outlets

# **High-Density Power Distribution**

The Smart Cabinet Power Distribution Units (CDU) provide reliable power distribution combined with local and remote power monitoring and environmental monitoring via IP. Use the network interface to view power, temperature and humidity levels via Web browser, or receive SNMP-based alarms and email alerts when conditions exceed defined thresholds.

Sentry POPS (Per Outlet Power Sensing) combines all of the features and functions of a Smart CDU with the ability to provide power monitoring per an individual outlet/device. Power information per individual outlet/device includes current, voltage, power (kW), apparent power, crest factor, and power factor. Using out grouping technology, power information is available per device, groups of devices (application), individual CDU or cabinet.

## **Additional Benefits:**



# POPS<sup>™</sup> (Per Outlet Power Sensing)

Monitor Current Load (A), Voltage (V), Power (W), Apparent Power (VA), Crest Factor and Power Factor per outlet at an accuracy of  $\pm 2\%$ .



#### **Branch Circuit Protection**

The Sentry CDU Family meets the UL 60950-1 requirement for Branch Circuit Protections

> UL-489 rated circuit breakers with 10 KAIC rating



## PIPS - Per Input Power Sensing

Accurately measures Active Power, Apparent Power, Energy k-Wh, Power Capacity, and Power Capacity Used using the network interface. See the aggregate current draw, in Amps, locally using the onboard LED.



## **Temperature and Humidity**

The Smart CDU supports two external 10ft (3m) probes. Each of these probes measure both temperature and humidity. Receive SNMP-based alerts or email notifications when conditions exceed defined thresholds.



#### **Mixed Outlets**

This Smart CDU combines (36) IEC C13 and (12) IEC C19 outlets within a single CDU to monitor power at the outlet-level.





Model	Available Input Voltages	Amperage	Available Input Cord	Outlets	Dimensions (L x W x D)
CSG-48V57425A1	240/415V 3-Phase Wye	60A	IEC Red 6hr 3P+N+E Plug,	(36) IEC 60320/C13	72.0 x 3.5 x 3.5 in.
CLG-48V57425A1*	50/60Hz		10' (3m), Bottom/Frt Cord	(12) IEC 60320/C19	(1829 x 89 x 89 mm)

<sup>\*</sup> CLG part numbers refer to the Expansion CDU

# **Additional Features and Specifications**

### **Agency Approvals**

- > US & Canada (cTUVus Mark) to UL 60950-1:2003 and CAN/CSA 22.2 No. 60950-1-03
- > FCC Class A, Part 15
- > EMC to EN 55022 Class A, EN 55024, CISPR 22 Class A

#### **Communications and Security**

- > 10/100 BaseT Ethernet
- > HTTP/HTTPS
- > SSLv3/TLSv1
- > SNMPv2, V3
- > SSHv2
- > Telnet
- > LDAPS/LDAPv3
- > TACACS+
- > RADIUS
- > RS-232 (Serial)

#### **Branch Circuit Protection**

> Compliant to UL 60950-1

#### **Accessories**

- > Optional Temperature & Humidity Probe
  - EMTH-1-1 Temperature & Humidity Probe, 10 ft (3m)
- > Environmental Monitor
  - EMCU-1-1B allows up to (2) additional temperature & humidity probes, (1) water sensor, (4) dry contact closures, (1) analog-to-digital contact sensor. Includes (1) temperature/humidity probe with unit.
- > SPM (Sentry Power Manager):
  - Monitor and Manage multiple Sentry CDU's
  - Monitor and Manage all alarm conditions
  - Reporting and Trending
  - Group or Cluster outlets for reboot and power information
  - Optional Appliance or virtual version
  - SPM v5.1+ is VMware READY



VMware and VMware Ready is a registered trademark or trademark of VMware, Inc. in the United States and/or other jurisdictions





HEADQUARTERS - NORTH AMERICA Server Technology, Inc. 1040 Sandhill Drive Reno, NV 89521 United States 1.775.284.2000 Tel 1.775.284.2065 Fax sales@servertech.com www.servertech.com www.servertechblog.com EMEA
Server Technology Intl
Sienna Court
The Broadway
Maidenhead
Berkshire
SL6 1NJ
United Kingdom
+44 (0) 1628 509053 Tel

+44 (0) 1628 509100 Fax

salesint@servertech.com

Server Technology Intl 37th Floor, Singapore Land Tower 50 Raffles Place Singapore 048623 +65 (0) 6829 7008 Tel +65 (0) 6234 4574 Fax salesint@servertech.com