

Sentry Switched CDU

Key Features

- > Remote Power Management: Power cycle individual power outlets, or groups of power outlets, to remotely reboot servers and network devices, anywhere in the world. Or, power-off unused power receptacles
- > High Power Distribution: 3-Phase power; 20 or 30-Amp power input feed options
- > High Density: Single power input feed; 24 outlets per enclosure
- > IP Access & Security: Web interface, SSL, SSH, Telnet, SNMP, FTP, SNTp, Syslog, LDAP, LDAPS, TACACS and RS-232 access
- > Add an Expansion Unit: Connect the Switched Expansion CDU (CX) to a Master unit (CW) for power monitoring and control of separate circuits from a single IP address
- > Environmental Monitoring: Each Switched CDU supports two temperature & humidity probes and reports conditions thru the Web interface
- > SNMP Traps: Provide automated alerts for power and environmental conditions
- > Input Current Monitor: Precisely measure the aggregate current draw (in amps) on each power circuit. On-site verification of the input current with the LED digital display. Remote verification via browser or serial screen.
- > Power-up Sequencing: Prevent an in-rush power overload

CW-24VD/Y

High-Density Power Distribution

The Switched CDU's combine remote configuration and management with power distribution and power and environmental monitoring. Reboot a single or dual-power server with one command. Receive SNMP-based alerts and email alerts when power or environmental conditions exceed thresholds. Assign users specific access rights to designated outlets or groups.

Only the Switched CDU products provide the flexibility needed for all data centers and remote sites, including power requirements for high-amp, high voltage; UL 60950-1 branch circuit protection; SSL & SSH security; and SNMP-based input current monitoring.

Additional Benefits:



Branch Circuit Protection

The Sentry CDU Family meets the new UL 60950-1 requirement for branch circuit protection.

Attention! The Sentry CDU products meet the above criteria by providing overcurrent protection with UL-listed Bussman SC fuses for each branch circuit.



Input Current Monitoring

The CDU's exclusive True RMS current monitoring is critical to preventing overloads in high-density computing environments. LED digital displays on the CDU enclosure report the input current of each phase or branch circuit.



Temperature and Humidity

The Switched CDU supports two external probes. Each of these probes measure both temperature and humidity. Receive SNMP-based alert notifications when conditions exceed defined thresholds.



Model	Available Input Voltages	Amperage	Available Input Cord	Outlets	Dimensions** (L x W x D)
CW-24VD-L20M CX-24VD-L20M***	240V 3-phase Delta 50/60 Hz	20A	NEMA L15-20P, 10'(3m), Bottom/front Cord	(24) IEC 60320/C13	69.0 x 1.75 x 2.25 in. (1753 x 44 x 57 mm)
CW-24VD-L30M CX-24VD-L30M***	240V 3-phase Delta 50/60 Hz	30A	NEMA L15-30P, 10'(3m), Bottom/front Cord	(24) IEC 60320/C13	69.0 x 1.75 x 2.25 in. (1753 x 44 x 57 mm)
CW-24V7V311 CX-24V7V311***	240V 3-phase Delta 50/60 Hz	30A	CS8365, 10'(3m), Bottom/front Cord	(24) IEC 60320/C13	69.0 x 1.75 x 2.25 in. (1753 x 44 x 57 mm)
CW-24VY-L20M CX-24VY-L20M***	208 V 3-phase Wye 50/60 Hz	20A	NEMA L21-20P, 10'(3m), Bottom/front Cord	(24) IEC 60320/C13*	69.0 x 1.75 x 2.25 in. (1753 x 44 x 57 mm)
CW-24VY-L30M CX-24VY-L30M***	208 V 3-phase Wye 50/60 Hz	30A	NEMA L21-30P, 10'(3m), Bottom/front Cord	(24) IEC 60320/C13*	69.0 x 1.75 x 2.25 in. (1753 x 44 x 57 mm)

*This unit has an additional NEMA 5-20R, 110V Utility Outlet

**Please note that the depth of these enclosures are 3.0" deep at the placement of the fuse

***CX refers to the Expansion Unit

Additional Features and Specifications

Agency Approvals

- > US & Canada (cTUVus Mark) to UL 60950-1: 2007 and CAN/CSA 22.2 No. 60950-1-07
- > FCC Class A, Part 15
- > EMC to EN 55022 Class A, EN 55024, CISPR 22 Class A

Communications and Security

- > 10/100 BaseT Ethernet
- > HTTP/HTTPS
- > SSLv3/TLSv1
- > SNMPv2 and v3
- > SSHv2
- > Telnet
- > LDAPv3
- > LDAPS
- > TACACS+
- > RS-232 (Serial)
- > IPv4 and v6

Branch Circuit Protection

- > Compliant to UL 60950-1

Accessories

- > Optional Temperature & Humidity Probe
 - EMTH-1-1 Temperature & Humidity Probe, 10ft (3m)
- > Environmental Monitor
 - EMCU-1-1B allows up to (2) additional temperature & humidity probes, (1) water sensor, (4) dry contact closures, (1) analog-to-digital contact sensor. Includes (1) temperature/humidity probe with unit.
- > SPM (Sentry Power Manager) Appliance:
 - Monitor and Manage multiple Sentry CDU's
 - Monitor and Manage all alarm conditions
 - Reporting and Trending
 - Group or Cluster outlets for reboot and power information



Expansion Module Model Numbers

- > CX-24VD-L20M
- > CX-24VD-L30M
- > CX-24V7V311
- > CX-24VY-L20M
- > CX-24VY-L30M



Server Technology

HEADQUARTERS - NORTH AMERICA

Server Technology, Inc.
1040 Sandhill Drive
Reno, NV 89521
United States
1.775.284.2000 Tel
1.775.284.2065 Fax
sales@servertech.com
www.servertechblog.com

Western Europe, Middle East and Africa

Fountain Court
2 Victoria Square
Victoria Street
St. Albans
AL1 3TF
United Kingdom
+44 (0) 1727 884676 Tel
+44 (0) 1727 220815 Fax
salesint@servertech.com

Central Europe, Eastern Europe and Russia

Niederlassung Deutschland
Server Technology LLC
42119 Wuppertal
Germany
Tel: + 49 202 693917 x 0
Fax: + 49 202 693917-10
salesint@servertech.com

APAC

37th Floor
Singapore Land Tower
50 Raffles Place
Singapore 048623
Phone: +65 9739.0396
Fax: +65 6234.4574
salesint@servertech.com