

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	DESCRIPTION	FIBER COUNT	DIAMETER	FLAME RATING	BEND RADIUS (INSTALLATION)	BEND RADIUS (LONG TERM)	TENSILE LOAD (INSTALLATION)	TENSILE LOAD (LONG TERM)	ATTENUATION
FSLP502	MULTIMODE 50/125 OM2 INDOOR/OUTDOOR CABLE	2	0.45" [11.4mm]	OFCP	4.5" [11.5cm]	9.0" [22.9mm]	100lbs [440 N]	30lbs [133 N]	3.5dB/km @ 850nm 1.5dB/km @ 1300nm
FSLR502			0.52" [13.1mm]	OFGR	5.2" [13.2mm]	10.4" [26.5mm]			
FSLP504		4	0.45" [11.4mm]	OFCP	4.5" [11.5mm]	9.0" [22.9mm]			
FSLR504			0.55" [14.0mm]	OFGR	5.5" [14.0mm]	11.0" [28.0mm]			
FSLP602	MULTIMODE 62.5/125 OM1 INDOOR/OUTDOOR CABLE	2	0.45" [11.4mm]	OFCP	4.5" [11.5cm]	9.0" [22.9mm]			3.5dB/km @ 850nm 1.0dB/km @ 1300nm
FSLR602			0.52" [13.1mm]	OFGR	5.2" [13.2mm]	10.4" [26.5mm]			
FSLP604		4	0.45" [11.4mm]	OFCP	4.5" [11.5mm]	9.0" [22.9mm]			
FSLR604			0.55" [14.0mm]	OFGR	5.5" [14.0mm]	11.0" [28.0mm]			
FOLPX02	MULTIMODE 50/125 OM3 INDOOR/OUTDOOR CABLE	2	0.45" [11.4mm]	OFCP	4.5" [11.5cm]	9.0" [22.9mm]			3.5dB/km @ 850nm 1.5dB/km @ 1300nm
FOLRX02			0.52" [13.1mm]	OFGR	5.2" [13.2mm]	10.4" [26.5mm]			
FOLPX04		4	0.45" [11.4mm]	OFCP	4.5" [11.5mm]	9.0" [22.9mm]			
FOLRX04			0.55" [14.0mm]	OFGR	5.5" [14.0mm]	11.0" [28.0mm]			
FOLPZ02	MULTIMODE 50/125 OM4 INDOOR/OUTDOOR CABLE	2	0.45" [11.4mm]	OFCP	4.5" [11.5cm]	9.0" [22.9mm]			3.5dB/km @ 850nm 1.5dB/km @ 1300nm
FOLRZ02			0.52" [13.1mm]	OFGR	5.2" [13.2mm]	10.4" [26.5mm]			
FOLPZ04		4	0.45" [11.4mm]	OFCP	4.5" [11.5mm]	9.0" [22.9mm]			
FOLRZ04			0.55" [14.0mm]	OFGR	5.5" [14.0mm]	11.0" [28.0mm]			
FSLP902	SINGLEMODE 9/125 INDOOR/OUTDOOR CABLE	2	0.45" [11.4mm]	OFCP	4.5" [11.5cm]	9.0" [22.9mm]			0.7dB/km @ 1310nm 0.7dB/km @ 1550nm
FSLR902			0.52" [13.1mm]	OFGR	5.2" [13.2mm]	10.4" [26.5mm]			
FSLP904		4	0.45" [11.4mm]	OFCP	4.5" [11.5mm]	9.0" [22.9mm]			
FSLR904			0.55" [14.0mm]	OFGR	5.5" [14.0mm]	11.0" [28.0mm]			

						TITLE 2, 4 FIBER ARMORED INDOOR/OUTDOOR CABLE WITH 900um BUFFERED FIBERS						
						CUSTOMER DRAWING						
						ITEM REVISION NAME M02055JK/00				PANDUIT		
						DATASET FILE NAME M02055JK_DC/00A						
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .010 [0.3] .XX ± .03 [0.8] ANGLES ±						
						THIRD ANGLE PROJECTION				PART NUMBER: SEE TABLE		
						DRAWING NUMBER: M02055JK - DC						
00	02-03-14	SAT	WMA	TCB	RELEASED TO PRODUCTION	M02055JK - DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY SAT	DATE 02-03-14	CHK WMA	SCALE NONE	SHT 2 OF 2	SIZE A