

Sentry Switched CDU

Key Features

- > **High Density:** Single-power input feed; 24 outlets per enclosure (Qty 18 IEC C13 & qty 6 IEC C19 outlets)
- > **High Power Distribution:** 208V 3-phase 50 and 60 amp input feed options
- > **Input Current Monitor:** Precisely measure the aggregate current draw (in amps) on each phase. On-site verification of the input current with LED digital display. Remote verification via web browser or serial screen.
- > **Remote Power Management:** Power cycle individual power outlets, or groups of power outlets, to remotely reboot servers and network devices, anywhere in the world. Or, power-off unused power receptacles
- > **IP Access & Security:** Web interface, SSL, SSH, Telnet, SNMP, FTP, SNT, Syslog, LDAP, LDAPS, TACACS, RADIUS, and RS-232 access
- > **SNMP Traps and Email alerts:** Provide automated alerts for power and environmental conditions
- > **Environmental Monitoring:** Each Switched CDU supports two external temperature & humidity probes and reports conditions thru the user interface without the need for additional IP addresses
- > **Add an Expansion Module:** Connect the Switched Expansion CDU (CXG) to a Master unit (CWG) for power management of separate power circuits from a single IP address

CWG-24VD/Y Switched POPS™ CDU with Mixed Outlets

High-Density Power Distribution

The Switched CDU combines network configuration and management with power distribution, environmental monitoring and the ability to provide power monitoring per an individual outlet/device. Power information per outlet includes current, voltage, power (kW), apparent power (VA), crest factor and power factor. Reboot a single or dual-power server with one command. Receive SNMP or email-based alerts when power or environmental conditions exceed thresholds. Assign user specific access rights to designated outlets or groups.

This Switched CDU has middle entry for network, serial & environmental connections combined with a top power cord entry. This provides the ultimate flexibility when connecting Switched CDU's to overhead power or busways. Current monitors are easily inverted via the web GUI or serial interface.

Additional Benefits:



POPS™ (Per Outlet Power Sensing)

Monitor Current Load (A), Voltage (V), Power (W), Apparent Power (VA), Crest Factor and Power Factor per outlet at an accuracy of $\pm 2\%$.



Branch Circuit Protection

The Sentry CDU Family meets the UL 60950-1 requirement for Branch Circuit Protections
> UL-489 rated circuit breakers



Input Current Monitoring

Exclusive Digital True RMS current monitoring is critical to preventing overloads in high-density computing environments. LED digital displays on the CDU enclosure report the input current of each phase or branch circuit for simple load balancing



Temperature and Humidity

The Switched CDU supports two external 10ft (3m) probes. Each of these probes measure both temperature and humidity. Receive SNMP-based alerts or email notifications when conditions exceed defined thresholds.



Mixed Outlets

This Switched CDU combines both IEC 60320/C13 and IEC 60320/C19 switched outlets within a single CDU. For rebooting non-responsive servers & network devices.



| Model | Available Input Voltages | Amperage | Available Input Cord | Outlets | Dimensions (L x W x D) |
|------------------------------------|---------------------------------|----------|-----------------------------------|---|---|
| CWG-24VDV454A1 CXG-24VDV454A1 * | 240V, 3-phase Delta 50/60 Hz | 50A | CS8365C Cord Set, 10ft (3 m) | (18) IEC 60320/C13 (6) IEC 60320/C19 | 70.0 x 1.75 x 3.50 in. (1778 x 44 x 89 mm) |
| CWG-24VDX454A1 CXG-24VDX454A1 * | 240V, 3-phase Delta 50/60Hz | 60A | IEC 60309 Cord set, 10ft (3 m) | (18) IEC 60320/C13 (6) IEC 60320/C19 | 70.0 x 1.75 x 3.50 in. (1778 x 44 x 89 mm) |
| CWG-24VYY454A1 CXG-24VYY454A1 * | 208V, 3-phase Wye 50/60 Hz | 60A | IEC 60309 Cord set, 10ft (3 m) | (18) IEC 60320/C13 (6) IEC 60320/C19 | 70.0 x 1.75 x 3.50 in. (1778 x 44 x 89 mm) |

* CXG part numbers refer to the Expansion CDU

Additional Features and Specifications

Agency Approvals

- > US & Canada (cTUVus mark) to UL 60950-1:2003 and CAN/CSA 22.2 No. 60950-1-03
- > FCC Class A, Part 15
- > CE
- > EMC to EN 55022 Class A, EN 55024

Communications and Security

- > 10/100 BaseT Ethernet
- > HTTP/HTTPS
- > SSLv3/TLSv1
- > SNMPv2
- > SSHv2
- > Telnet
- > LDAP/LDAPv3
- > TACACS+
- > RADIUS
- > RS-232 (Serial)

Branch Circuit Protection

- > Compliant to UL 60950-1

Accessories

- > Optional Temperature & Humidity Probe
 - EMTH-1-1 Temperature & Humidity Probe, 10 ft (3m)
- > SPM (Sentry Power Manager) Appliance:
 - Monitor and Manage multiple Sentry CDU's
 - Monitor and Manage all alarm conditions
 - Reporting and Trending
 - Group or Cluster outlets for reboot and power information
- > Environmental Monitor
 - EMCU-1-1B allows up to (2) additional temperature & humidity probes, (1) water sensor, (4) dry contact closures, (1) analog-to-digital contact sensor. Includes (1) temperature/humidity probe with unit.



Server Technology

HEADQUARTERS - NORTH AMERICA
Server Technology, Inc.
1040 Sandhill Drive
Reno, NV 89521
United States
1.775.284.2000 Tel
1.775.284.2065 Fax
sales@servertech.com
www.servertech.com
www.servertechblog.com

EMEA
Server Technology Intl
Sienna Court
The Broadway
Maidenhead
Berkshire
SL6 1NJ
United Kingdom
+44 (0) 1628 509053 Tel
+44 (0) 1628 509100 Fax
salesintl@servertech.com

APAC
Server Technology Intl
37th Floor, Singapore Land Tower
50 Raffles Place
Singapore 048623
+65 (0) 6829 7008 Tel
+65 (0) 6234 4574 Fax
salesintl@servertech.com