

Sentry Switched CDU

Key Features

- > High Density: Single-power input feed; 30 outlets per enclosure (Qty 24 IEC C13 and 6 IEC C19 outlets)
- > High Power Distribution: 208V, 3-Phase power option; 20A and 30A Delta or Wye input feed options.
- > Input Current Monitor: Precisely measure the aggregate current draw (in amps) on each phase. On-site verification of the input current with LED digital displays. Remote verification via web browser or serial screen.
- > Remote Power Management: Power cycle individual power outlets, or groups of power outlets, to remotely reboot servers and network devices, anywhere in the world. Or, power-off unused power receptacles
- > IP Access & Security: Web interface, SSL, SSH, Telnet, SNMP, FTP, SNTp, Syslog, LDAP, LDAPS, TACACS and RS-232 access
- > SNMP Traps and Email alerts: Provide automated alerts for power and environmental conditions
- > Environmental Monitoring: Each Switched CDU supports two external temperature & humidity probes and reports conditions thru the user interface without the need for additional IP addresses
- > Add an Expansion Module: Connect the Switched Expansion CDU (CXG) to a Master unit (CWG) for power monitoring of separate power circuits from a single IP address

CWG-30VD/VY Switched POPS with (24) C13s and (6) C19s

High-Density Power Distribution

The Switched CDU combines network configuration and management with power distribution, environmental monitoring and the ability to provide power monitoring per an individual outlet/device. Power information per outlet includes current, voltage, power (kW), apparent power (VA), crest factor and power factor. Reboot a single or dual-power server with one command. Receive SNMP or email-based alerts when power or environmental conditions exceed thresholds. Assign user specific access rights to designated outlets or groups.

This Switched CDU has top entry for network, serial & environmental connections combined with a bottom power cord entry. Current monitors are easily inverted via the web GUI or serial interface. This provides flexibility when connecting Switched CDU's to overhead power or busways.

Additional Benefits:



POPS (Per Outlet Power Sensing)

Monitor Current Load (A), Voltage (V), Power (W), Apparent Power (VA), Crest Factor and Power Factor per outlet at an accuracy of $\pm 2\%$.



Branch Circuit Protection


The Sentry CDU Family meets the UL 60950-1 requirement for Branch Circuit Protection

- > UL-489 rated circuit breakers



PIPS - Per Input Power Sensing

Accurately measures Active Power, Apparent Power, Energy k-Wh, Power Capacity, Reactance, and Power Capacity Used using the network interface. See the aggregate current draw, in Amps, locally using the onboard LED.



Temperature and Humidity

The Switched CDU supports two external 10ft (3m) probes. Each of these probes measure both temperature and humidity. Receive SNMP-based alerts or email notifications when conditions exceed defined thresholds.



Mixed Outlets

This Switched CDU combines both IEC 60320/C13 and IEC 60320/C19 switched outlets within a single CDU. For rebooting non-responsive servers & network devices.



| Model | Available Input Voltages | Amperage | Available Input Cord | Outlets | Dimensions (L x W x D) |
|-----------------------------------|---------------------------------|-------------------------|------------------------------------|---|--|
| CWG-30VDD458C2 CXG-30VDD458C2* | 240V, 3-phase Delta, 50/60Hz | 20A (16A continuous) | NEMA L15-20P Cordset, 10ft (3m) | (24) IEC 60320/C13 (6) IEC 60320/C19 | 73.5 x 1.75 x 3.50 in (1867 x 44 x 89 mm) |
| CWG-30VDE458C2 CXG-30VDE458C2* | 240V, 3-phase Delta, 50/60Hz | 30A (24A continuous) | NEMA L15-30P Cordset, 10ft (3m) | (24) IEC 60320/C13 (6) IEC 60320/C19 | 73.5 x 1.75 x 3.50 in (1867 x 44 x 89 mm) |
| CWG-30VYL458C2 CXG-30VYL458C2* | 208V, 3-phase Wye, 50/60Hz | 20A (16A continuous) | NEMA L21-20P Cordset, 10ft (3m) | (24) IEC 60320/C13 (6) IEC 60320/C19 | 73.5 x 1.75 x 3.50 in (1867 x 44 x 89 mm) |
| CWG-30VYM458C2 CXG-30VYM458C2* | 208V, 3-phase Wye, 50/60Hz | 30A (24A continuous) | NEMA L21-30P Cordset, 10ft (3m) | (24) IEC 60320/C13 (6) IEC 60320/C19 | 73.5 x 1.75 x 3.50 in (1867 x 44 x 89 mm) |
| CWG-30V7V458C2 CXG-30V7V458C2* | 208V, 3-phase Wye, 50/60Hz | 50A (30A continuous) | CS8365 Cordset, 10ft (3m) | (24) IEC 60320/C13 (6) IEC 60320/C19 | 73.5 x 1.75 x 3.50 in (1867 x 44 x 89 mm) |

* CX part numbers refer to the Expansion CDU

Additional Features and Specifications

Agency Approvals

- > US & Canada (cTUVus mark) to UL 60950-1:2003 and CAN/CSA 22.2 No. 60950-1-03
- > FCC Class A, Part 15
- > EMC to EN 55022 Class A, EN 55024, CISPR 22 Class A

Communications and Security

- > 10/100 BaseT Ethernet
- > HTTP/HTTPS
- > SSLv3/TLSv1
- > SNMPv2 and v3
- > SSHv2
- > Telnet
- > LDAPv3
- > LDAPS
- > TACACS+
- > RADIUS
- > RS-232 (Serial)

Branch Circuit Protection

- > Compliant to UL 60950-1

Accessories

- > Optional Temperature & Humidity Probe
 - EMTH-1-1 Temperature & Humidity Probe, 10ft (3m)
- > Environmental Monitor
 - EMCU-1-1B allows up to (2) additional temperature & humidity probes, (1) water sensor, (4) dry contact closures, (1) analog-to-digital converter. Includes (1) temperature/humidity probe with unit.
- > SPM (Sentry Power Manager) Appliance:
 - Monitor and Manage multiple Sentry CDU's
 - Monitor and Manage all alarm conditions
 - Reporting and Trending
 - Group or Cluster outlets for reboot and power information

> 1 U SPM Appliance



Expansion Module Model Numbers

- > CXG-30VDD458C2
- > CXG-30VDE458C2
- > CXG-30VYL458C2
- > CXG-30VYM458C2
- > CXG-30V7V458C2



Server Technology

HEADQUARTERS - NORTH AMERICA

Server Technology, Inc.
1040 Sandhill Drive
Reno, NV 89521
United States
1.775.284.2000 Tel
1.775.284.2065 Fax
sales@servertech.com
www.servertech.com
www.servertechblog.com

Western Europe, Middle East and Africa

Fountain Court
2 Victoria Square
Victoria Street
St. Albans
AL1 3TF
United Kingdom
+44 (0) 1727 884676 Tel
+44 (0) 1727 220815 Fax
salesint@servertech.com

Central Europe, Eastern Europe and Russia

Niederlassung Deutschland
Server Technology LLC
42119 Wuppertal
Germany
Tel: + 49 202 693917 x 0
Fax: + 49 202 693917-10
salesint@servertech.com

APAC

37th Floor
Singapore Land Tower
50 Raffles Place
Singapore 048623
Phone: +65 9739.0396
Fax: +65 6234.4574
salesint@servertech.com