



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
PEV6	51.2 LBS/EACH (23.3 kg/EACH)

NOTES:

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
- COMPONENTS: (1) 6" DUAL-SIDE VERTICAL MANAGER
(1) HARDWARE KIT
(2) FINGER KITS
(4) DOOR BRACKETS
(4) DOOR BRACKET BASES
- CAN BE USED WITH ANY 19 OR 23 INCH EIA STANDARD RACK.
- 3 ROWS OF 2RU 19" CEA OPENINGS (6 TOTAL RU)
- 6" DOOR SOLD SEPARATELY (P/N: PED6)
- DIMENSIONS IN PARENTHESIS ARE METRIC.
- ALL DIMENSIONS ARE REFERENCE ONLY.

TITLE PATCHRUNNER HIGH CAPACITY VERTICAL MANAGER 6" WIDE, DUAL-SIDED (PEV6) CONTROL DRAWING				
ITEM REVISION NAME 09V054AA/08			PANDUIT	
DATASET FILE NAME 09V054AA_DC/08A				
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)			MATERIAL: BACKBONE- STEEL FINGERS- ABS	
			DRAWING NUMBER: 09V054AA - DC	
DRAWN BY BAME	DATE 2/3/10	CHK NAGL	SCALE NONE	SIZE A
			SHT 1 OF 1	