


NOTES:  
1. IDENTIFICATION: VERTICAL, MIXED (24) C-13 & (6) C-19 NETWORKED  
208V / 30A / THREE-PHASE WYE POU



2. ACCESSORY COMPONENTS:  
 (4) #10-32 x 1/2" MOUNTING SCREWS  
 (4) #12-24 x 1/2" MOUNTING SCREWS  
 (2) #10-32 LOCKING COLLAR SCREWS  
 (2) L-BRACKETS

3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).

4. CURRENT METER - RED, 4-DIGIT LED DISPLAY PROVIDES TRUE RMS CURRENT THAT CONTINUOUSLY SCROLLS THROUGH THE THREE DIFFERENT MEASURED CIRCUITS. METER DISPLAYS CIRCUIT NAME FOLLOWED BY THE MEASURED CURRENT (E.G. CR-1 REPRESENTS PHASE 1). BREAKER/CIRCUIT (XY,YZ,ZX) LEVEL MONITORING CAN ALSO BE ACCESSED REMOTELY VIA ETHERNET CONNECTION.


5. UL® & c-UL® LISTED 60950 AND NOM COMPLIANT.

6. RoHS COMPLIANT.


7. VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.

8. MAXIMUM AVAILABLE INPUT POWER = 8.6 KW

9. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.




## TOOLLESS MOUNTING BUTTON LOCATION



NETWORKED CURRENT METER  
(SEE DETAIL A)


20 AMP, 2 POLE UL LISTED ELECTRO  
MECHANICAL SWITCH/BREAKER  
3 PLACES




– 10 FOOT INLET POWER CORD



PLUG  
30 AMP, 120/208V x 3~ WYE  
TWIST LOCK  
NEMA L21-30P



TWENTY-FOUR (24)  
RECEPTACLES  
15 AMP, 250V  
STRAIGHT BLADE  
IEC 60320/C13



SIX (6)  
RECEPTACLES  
20 AMP, 250V  
STRAIGHT BLADE  
IEC 60320/C19

01A	8-30-12	PIP	MRWA	A. UPDATED NOTE #5 & 8. B. ADDED NOTE #9. C. UPDATED DETAIL A.	09V098NE					
00A	11-23-10	MAV	KRKE	RELEASED TO PRODUCTION	09V098NE					
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH		

MODEL FILENAME		09V098NE/01.PRT	
CAD FILENAME/LAYERS		09V098NE_DC/01A.PRT	
PANDUIT CORP TINLEY PARK, ILLINOIS			
VERTICAL, MIXED (24) C-13 & (6) C-19 NETWORKED POWER OUTLET UNIT CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED,	
INCHES	[METRIC - MILLIMETER]	ALL DIMENSIONS ARE GIVEN IN	
X.X +/- 0.03	X. +/- 0.8	INCHES, THIRD ANGLE PROJECTION	
X.XX +/- 0.015	X.X +/- 0.4		
X.XXX +/- 0.005	X.XX +/- 0.13		
DRAWN BY		SCALE	
MAV		NONE	
DATE		DRAWING NO.	
11-23-10		09V098NE	
CHK'D		DWG	
KRKE		B	
		SIZE	