


NOTES:



2. ACCESSORY COMPONENTS:
 (4) #10-32 x 1/2" MOUNTING SCREWS
 (4) #12-24 x 1/2" MOUNTING SCREWS
 (2) #10-32 LOCKING COLLAR SCREWS
 (2) L-BRACKETS

4. CURRENT METER - RED, 4-DIGIT LED DISPLAY PROVIDES TRUE RMS CURRENT THAT CONTINUOUSLY SCROLLS THROUGH THE THREE DIFFERENT MEASURED CIRCUITS. METER DISPLAYS CIRCUIT NAME FOLLOWED BY THE MEASURED CURRENT (E.G. CR-1 REPRESENTS PHASE 1). BREAKER/CIRCUIT (XY,YZ,ZX) LEVEL MONITORING CAN ALSO BE ACCESSED REMOTELY VIA ETHERNET NETWORK CONNECTION.

6. RoHS COMPLIANT.

8. MAXIMUM AVAILABLE INPUT POWER = 8.6KW

9. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.

- 20 AMP, 125V DUAL OUTLET
NEMA STYLE RECEPTACLES
(5-20R)
3 PLACES





66.25 (1682.8)

NETWORKED CURRENT METER
(SEE DETAIL A)

CIRCUIT CIRCUIT CIRCUIT
3 2 1

20 AMP, 2 POLE UL LISTED ELECTRO
MECHANICAL SWITCH/BREAKER
3 PLACES

- 10 FOOT INLET POWER CORD



01A	9-5-12	PIP	MRWA	A. UPDATED NOTE #5 & 8. B. ADDED NOTE #9. C. UPDATED DETAIL A.	09V098NW					
00A	11-23-10	MAV	KRKE	RELEASED TO PRODUCTION	09V098NW					
REV	DATE	BY	CHK	DESCRIPTION	ECN - R		CUST	SUP	OTH	

MODEL FILENAME		09V098NW/01.PRT	
CAD FILENAME/LAYERS		09V098NW_DC/01A.PRT	
PANDUIT CORP TINLEY PARK, ILLINOIS			
VERTICAL, MIXED (24) C-13 & (3) C-19 & (6) 5-20R NETWORKED POWER OUTLET UNIT CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED,	
INCHES	[METRIC - MILLIMETER]	ANGLE	
X.X +/- 0.03	X. +/- 0.8	ALL DIMENSIONS ARE GIVEN IN	
X.XX +/- 0.015	X.X +/- 0.4	INCHES, THIRD ANGLE PROJECTION	
X.XXX +/- 0.005	X.XX +/- 0.13		
DRAWN BY MAV		SCALE NONE	
DATE 11-23-10		DRAWING NO. 09V098NW	
CHK'D KRKE		DWG B	