

# Sentry Switched CDU

## CW-8H1 Switched 120V 20/30A with Circuit Breakers

### Key Features

- > **Medium Density:** Single power input feed; 8 outlets per 1U enclosure
- > **High Power Distribution:** 120V, 20A and 30A power input feed options
- > **Remote Power Management:** Power cycle individual power outlets, or groups of power outlets, to remotely reboot servers and network devices, anywhere in the world. Or, power-off unused power receptacles
- > **Input Current Monitor:** Precisely measure the aggregate current draw (in amps) on each power circuit. On-site verification of the input current with the LED digital display. Remote verification via browser or serial screen.
- > **IP Access & Security:** Web interface, SSL, SSH, Telnet, SNMP, FTP, SNT, Syslog, LDAP, LDAPS, TACACS and RS-232 access
- > **Traps & Alerts:** Provide automated SNMP-based alarms and email alerts for power and environmental conditions
- > **Environmental Monitoring:** Each Switched CDU supports two temperature & humidity probes and reports conditions thru the Web interface
- > **Add an Expansion Module:** Connect the Switched Expansion CDU (CX) to a Master unit (CW)
- > **Power-up Sequencing:** Prevent an in-rush power overload



### Medium-Density Power Distribution

The Switched CDU's combine remote configuration and management with power distribution and power and environmental monitoring. Reboot a single or dual-power server with one command. Receive SNMP-based alerts and email alerts when power or environmental conditions exceed thresholds. Assign users specific access rights to designated outlets or groups.

Only the Switched CDU products provide the flexibility needed for all data centers and remote sites, including power requirements for high-amp, high voltage; UL 60950-1 branch circuit protection; SSL & SSH security; and SNMP-based input current monitoring.

### Additional Benefits:



#### Branch Circuit Protection

The Sentry CDU Family meets the UL 60950-1 requirement for Branch Circuit Protection

- > UL-489 rated circuit breakers



#### PIPS - Per Input Power Sensing

Accurately measures Active Power, Apparent Power, Energy k-Wh, Power Capacity, and Power Capacity Used using the network interface. See the aggregate current draw, in Amps, locally using the onboard LED.



#### Temperature and Humidity

The Switched CDU supports two external probes. Each of these probes measure both temperature and humidity. Receive SNMP-based alert notifications when conditions exceed defined thresholds.

Model	Available Input Voltages	Amperage	Available Input Cord	Outlets	Dimensions (L x W x D)
CW-8H1A413 CX-8H1A413*	100-120V 50/60Hz	20A	IEC 60320/C20 Power Inlet	(8) NEMA 5-20R	1.75 x 17.2 x 7.0 in. (44 x 437 x 178 mm)
CW-8H1B413 CX-8H1B413*	100-120V 50/60Hz	30A	NEMA L5-30P Cordset, 10 ft (3m)	(8) NEMA 5-20R	1.75 x 17.2 x 7.0 in. (44 x 437 x 178 mm)

\*CX refers to the Expansion Module

## Additional Features and Specifications

### Agency Approvals

- > US & Canada (cTUVus mark) to UL 60950-1:2007 and CAN/CSA 22.2 No. 60950-1-07
- > FCC Class A, Part 15
- > EMC to EN 55022 Class A, EN 55024, CISPR 22 Class A

### Communications and Security

- > 10/100 BaseT Ethernet
- > HTTP/HTTPS
- > SSLv3/TLSv1
- > SNMPv2 & v3
- > SSHv2
- > Telnet
- > LDAPv3
- > LDAPS
- > TACACS+
- > RADIUS
- > RS-232 (Serial)
- > IPv6

### Power Cord Options

- > PTCORD-5 IEC 60320/C19 - 5-15P (15A Straight-Blade) 10ft (3m)
- > PTCORD-6 IEC 60320/C19 - 5-20P (20A Straight-Blade) 10ft (3m)
- > PTCORD-7 IEC 60320/C19 - L5-20P (20A Twist-Lock) 10ft (3m)

### Branch Circuit Protection

- > Compliant to UL 60950-1

### Accessories

- > Optional Temperature & Humidity Probe
  - EMTH-1-1 Temperature & Humidity Probe, 10ft (3m)
- > Environmental Monitor
  - EMCU-1-1B allows up to (2) additional temperature & humidity probes, (1) water sensor, (4) dry contact closures, (1) analog-to-digital converter. Includes (1) temperature/humidity probe with unit.
- > SPM (Sentry Power Manager):
  - Monitor and Manage multiple Sentry CDU's
  - Monitor and Manage all alarm conditions
  - Reporting and Trending
  - Group or Cluster outlets for reboot and power information
  - Optional Appliance or virtual version
  - SPM v5.1+ is VMware READY



VMware and VMware Ready is a registered trademark or trademark of VMware, Inc. in the United States and/or other jurisdictions



Rear View: Linking port and circuit breakers



1 U SPM Appliance

Expansion Module  
Model Numbers  
> CX-8H1A413  
> CX-8H1B413



## Server Technology

HEADQUARTERS -  
NORTH AMERICA  
Server Technology, Inc.  
1040 Sandhill Drive  
Reno, NV 89521  
United States  
1.775.284.2000 Tel  
1.775.284.2065 Fax  
sales@servertech.com  
www.servertech.com  
www.servertechblog.com

EMEA  
Server Technology Intl  
Fountain Court  
2 Victoria Square  
Victoria Square  
St. Albans  
AL1 3TF  
United Kingdom  
+44 (0)1727 884676 Tel  
+44 (0) 1727220815 Fax  
salesint@servertech.com

APAC  
Server Technology Intl  
37th Floor, Singapore Land Tower  
50 Raffles Place  
Singapore 048623  
+65 (0) 6829 7008 Tel  
+65 (0) 6234 4574 Fax  
salesint@servertech.com