


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. PRIMARY DIMENSIONS ARE IN MILLIMETERS.
3. RAIL ADJUSTMENT MEASUREMENTS ARE TAKEN FROM THE FRONT FACE OF EACH EQUIPMENT RAIL. INDEPENDENT ADJUSTABLE REAR EQUIPMENT MOUNTING RAILS (EIA) ADJUST FROM 141mm [5.5in] TO 437mm [17.2in] AND FROM 526mm [20.7in] TO 933mm [36.7in] WITH PDU BRACKETS AND CABLE MANAGEMENT FINGERS IN PLACE.
4. CAN BE USED WITH ANY 19" EIA STANDARD COMPONENT IN ADDITION TO ALL PANDUIT HORIZONTAL CABLE MANAGEMENT AND PATCH PANEL PRODUCTS.
5. EIA UNIVERSAL STANDARD HOLE PROGRESSION ON EQUIPMENT RAILS 15.88mm [.625in], 15.88mm [.625in], 12.70mm [.5in], 15.88mm [.625in], 15.88mm [.625in], 12.7mm [.5in]...ETC.
6. PARTS SUPPLIED:
 - BASE CABINET
 - FRONT PERFORATED SINGLE HINGE DOOR (SEE CHART ON SHEET 2)
 - REAR PERFORATED SPLIT DOOR (SEE CHART ON SHEET 2)
 - EQUIPMENT RAILS FRONT & REAR (SEE CHART ON SHEET 2)
 - PDU BRACKETS (SEE CHART ON SHEET 2)
 - CASTERS (SEE CHART ON SHEET 2)
 - INSTRUCTION SHEET
7. RACK UNIT SPACING NUMERALS ARE CLEARLY PRINTED ON EQUIPMENT MOUNTING RAILS.
8. FULLY BONDED STRUCTURE WHEN ASSEMBLED PER INSTRUCTIONS.
9. STATIC LOAD RATING. 1360 Kg (3000 LBS)
10. ROLLING LOAD RATING. 1133 Kg (2500 LBS)
11. SINGLE POINT GROUND LOCATIONS AT TOP AND BOTTOM OF CABINET.
12. ALL CABINET RAILS ARE INSTALLED NUMBERS UP.
13. MAXIMUM EQUIPMENT DEPTH, 959mm [37.75].

01A	10-02-14	PBS	ADP	TCN	FLOOR MOUNT DIMENSIONS UPDATED	V09000BX	
00B	5-09-13	PBS	JDW	JDWE	REVISED CHART	12V305TJ-DC	
00A	8-29-12	TKW	JDW	PBD	RELEASED TO PRODUCTION	12V305TJ-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	

TITLE		NET-ACCESS S TYPE CABINET 700mm WIDE X 1070mm DEEP FAMILY	
		CUSTOMER DRAWING	
ITEM REVISION NAME		12V305TJ/01.PRT	
DATASET FILE NAME		12V305TJ_DC/01A.PRT	
		MATERIAL:	
		N/A	
		DRAWING NUMBER:	
		12V305TJ-DC	
DRAWN BY		DATE	CHK
TKW		8-29-12	JDW
SCALE		NONE	
SHT 1 OF 5		A	

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	DESCRIPTION	SINGLE HINGE FRONT DOOR	SPLIT REAR DOOR	SPLIT SIDE PANEL	FRONT CAGE NUT E-RAIL	REAR CAGE NUT FINGER MGMT E-RAIL	REAR CAGE NUT VERTICAL PATCH E-RAIL	STANDARD PDU BRACKETS	CASTERS	CABLE MGMT FINGERS	VERTICAL PATCHING	CABINET WEIGHT FULLY UNPACKAGED	CABINET WEIGHT SHIPPING WEIGHT
S7212*	NET-ACCESS S-TYPE CABINET 700mm X 42RU X 1070mm DEEP	01	01	02	02	02	00	02	04	00	00	129 Kg/EACH 285 LBS/EACH	149 Kg/EACH 330 LBS/EACH
S7512*	NET-ACCESS S-TYPE CABINET 700mm X 45RU X 1070mm DEEP	01	01	02	02	02	00	02	04	00	00	136 Kg/EACH 300 LBS/EACH	156 Kg/EACH 345 LBS/EACH
S7812*	NET-ACCESS S-TYPE CABINET 700mm X 48RU X 1070mm DEEP	01	01	02	02	02	00	02	04	00	00	142 Kg/EACH 315 LBS/EACH	163 Kg/EACH 360 LBS/EACH
S7219*	NET-ACCESS S-TYPE CABINET 700mm X 42RU X 1070mm DEEP	01	01	00	02	02	00	02	04	00	00	96 Kg/EACH 212 LBS/EACH	118 Kg/EACH 257 LBS/EACH
S7519*	NET-ACCESS S-TYPE CABINET 700mm X 45RU X 1070mm DEEP	01	01	00	02	02	00	02	04	00	00	102 Kg/EACH 227 LBS/EACH	123 Kg/EACH 272 LBS/EACH
S7819*	NET-ACCESS S-TYPE CABINET 700mm X 48RU X 1070mm DEEP	01	01	00	02	02	00	02	04	00	00	109 Kg/EACH 242 LBS/EACH	130 Kg/EACH 287 LBS/EACH
S7212*F	NET-ACCESS S-TYPE CABINET 700mm X 42RU X 1070mm DEEP	01	01	02	02	02	00	02	04	01	00	130 Kg/EACH 287 LBS/EACH	150 Kg/EACH 332 LBS/EACH
S7512*F	NET-ACCESS S-TYPE CABINET 700mm X 45RU X 1070mm DEEP	01	01	02	02	02	00	02	04	01	00	137 Kg/EACH 302 LBS/EACH	157 Kg/EACH 347 LBS/EACH
S7812*F	NET-ACCESS S-TYPE CABINET 700mm X 48RU X 1070mm DEEP	01	01	02	02	02	00	02	04	01	00	144 Kg/EACH 317 LBS/EACH	164 Kg/EACH 362 LBS/EACH
S7219*F	NET-ACCESS S-TYPE CABINET 700mm X 42RU X 1070mm DEEP	01	01	00	02	02	00	02	04	01	00	97 Kg/EACH 214 LBS/EACH	117 Kg/EACH 259 LBS/EACH
S7519*F	NET-ACCESS S-TYPE CABINET 700mm X 45RU X 1070mm DEEP	01	01	00	02	02	00	02	04	01	00	104 Kg/EACH 229 LBS/EACH	124 Kg/EACH 274 LBS/EACH
S7819*F	NET-ACCESS S-TYPE CABINET 700mm X 48RU X 1070mm DEEP	01	01	00	02	02	00	02	04	01	00	111 Kg/EACH 244 LBS/EACH	131 Kg/EACH 289 LBS/EACH
S7212*S	NET-ACCESS S-TYPE CABINET 700mm X 42RU X 1070mm DEEP	00	00	02	02	02	00	02	04	00	00	104 Kg/EACH 230 LBS/EACH	125 Kg/EACH 275 LBS/EACH
S7512*S	NET-ACCESS S-TYPE CABINET 700mm X 45RU X 1070mm DEEP	00	00	02	02	02	00	02	04	00	00	111 Kg/EACH 245 LBS/EACH	131 Kg/EACH 290 LBS/EACH
S7812*S	NET-ACCESS S-TYPE CABINET 700mm X 48RU X 1070mm DEEP	00	00	02	02	02	00	02	04	00	00	118 Kg/EACH 260 LBS/EACH	138 Kg/EACH 305 LBS/EACH
S7219*S	NET-ACCESS S-TYPE CABINET 700mm X 42RU X 1070mm DEEP	00	00	00	02	02	00	02	04	00	00	71 Kg/EACH 157 LBS/EACH	92 Kg/EACH 202 LBS/EACH
S7519*S	NET-ACCESS S-TYPE CABINET 700mm X 45RU X 1070mm DEEP	00	00	00	02	02	00	02	04	00	00	78 Kg/EACH 172 LBS/EACH	98 Kg/EACH 217 LBS/EACH
S7819*S	NET-ACCESS S-TYPE CABINET 700mm X 48RU X 1070mm DEEP	00	00	00	02	02	00	02	04	00	00	85 Kg/EACH 187 LBS/EACH	105 Kg/EACH 232 LBS/EACH

* DENOTES COLOR

"B" = BLACK

"W" = WHITE

TITLE

NET-ACCESS S TYPE CABINET
700mm WIDE X 1070mm DEEP FAMILY

CUSTOMER DRAWING

ITEM REVISION NAME

12V305TJ/01.PRT

DATASET FILE NAME

12V305TJ_DC/01A.PRT


PANDUIT

MATERIAL:

N/A

DRAWING NUMBER:

12V305TJ-DC

THIRD ANGLE
PROJECTION

DRAWN BY

DATE

TKW 8-29-12

CHK

SCALE

JDW NONE

SHT 2 OF 5

SIZE

A


2

1


2

1


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




LEFT VIEW



FRONT VIEW



RIGHT VIEW



REAR VIEW

							TITLE NET-ACCESS S TYPE CABINET 700mm WIDE X 1070mm DEEP FAMILY CUSTOMER DRAWING					
							ITEM REVISION NAME 12V305TJ/01.PRT			PANDUIT		
							DATASET FILE NAME 12V305TJ_DC/01A.PRT					
01A	10-02-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX	THIRD ANGLE PROJECTION			MATERIAL: N/A		
00B	5-09-13	PBS	JDW	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V305TJ-DC						
00A	8-27-12	TKW	JDW	PBD	SEE SHEET 1 OF 5 FOR REVISIONS	12V305TJ-DC				DRAWING NUMBER: 12V305TJ-DC		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY TKW	DATE 8-27-12	CHK JDW	SCALE NONE	SHT 3 OF 5	SIZE A


2

1

2


1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



2


1

							TITLE NET-ACCESS S TYPE CABINET 700mm WIDE X 1070mm DEEP FAMILY CUSTOMER DRAWING						
							ITEM REVISION NAME 12V305TJ/01.PRT						
							DATASET FILE NAME 12V305TJ_DC/01A.PRT						
01A	10-02-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX	 THIRD ANGLE PROJECTION				MATERIAL: N/A		
00B	5-09-13	PBS	JDW	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V305TJ-DC					DRAWING NUMBER: 12V305TJ-DC		
00A	8-29-12	TKW	JDW	PBD	SEE SHEET 1 OF 5 FOR REVISIONS	12V305TJ-DC							
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY TKW	DATE 8-29-12	CHK JDW	SCALE NONE	SHT 4 OF 5		SIZE A


2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



FLOOR MOUNTING HOLE LOCATIONS -
SOME PARTS REMOVED FOR CLARITY

							TITLE NET-ACCESS S TYPE CABINET 700mm WIDE X 1070mm DEEP FAMILY CUSTOMER DRAWING					
							ITEM REVISION NAME 12V305TJ/01.PRT					
							DATASET FILE NAME 12V305TJ_DC/01A.PRT					
							 THIRD ANGLE PROJECTION					
01A	10-02-14	PBS	ADP	TCN	SEE SHEET 1 OF 5 FOR REVISIONS	V09000BX				MATERIAL: N/A		
00B	5-09-13	PBS	JDW	JDWE	SEE SHEET 1 OF 5 FOR REVISIONS	12V305TJ-DC						
00A	8-29-12	TKW	JDW	PBD	SEE SHEET 1 OF 5 FOR REVISIONS	12V305TJ-DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY TKW	DATE 8-29-12	CHK JDW	SCALE NONE	DRAWING NUMBER: 12V305TJ-DC	SIZE A

2

1