

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
VB0A1P3BN30P1	17 lb (7.7 kg)

NOTES:

1. IDENTIFICATION: VERTICAL, MIXED (24) C-13 & (6)C-19
120V / 30A / THREE-PHASE WYE POU

<u>PART NO.</u>	<u>COLOR</u>
VB0A1P3BN30P1	BLACK

2. ACCESSORY COMPONENTS:
 (4) #10-32 x 1/2" MOUNTING SCREWS
 (4) #12-24 x 1/2" MOUNTING SCREWS
 (2) #10-32 LOCKING COLLAR SCREWS
 (2) L-BRACKETS

3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).


4. UL® & c-UL® LISTED 60950 AND NOM COMPLIANT.

5. RoHS COMPLIANT.


6. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.

7. MAXIMUM AVAILABLE INPUT POWER = 8.6 KW


8. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.



TOOLLESS MOUNTING BUTTON LOCATION




20 AMP, 2 POLE UL LISTED ELECTRO
MECHANICAL SWITCH/BREAKER
3 PLACES




— 10 FOOT INLET POWER CORD



PLUG
30 AMP, 120/208V x 3~ WYE
TWIST LOCK
NEMA L21-30P



TWENTY-FOUR (24)
RECEPTACLES
15 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13



SIX (6)
RECEPTACLES
20 AMP, 250V
STRAIGHT BLADE
IEC 60320/C19

01A	8-7-12	PIP	MRWA	B. UPDATED NOTE #4 & 7. C. ADDED NOTE #8.	09V098EK					
00B	1-31-11	MAV	KRKE	A. ADDED MAXIMUM AVAILABLE POWER	09V098EK					
00A	10-15-10	MAV	KRKE	RELEASED TO PRODUCTION	09V098EK					
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH		

MODEL FILENAME		09V098EK/01.PRT	
CAD FILENAME/LAYERS		09V098EK_DC/01A.PRT	
PANDUIT CORP TINLEY PARK, ILLINOIS			
VERTICAL, MIXED (24)C-13 & (6) C-19 POWER OUTLET UNIT CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED,	
INCHES	[METRIC - MILLIMETER]	ANGLE	
X.X +/- 0.03	X. +/- 0.8	ALL DIMENSIONS ARE GIVEN IN	
X.XX +/- 0.015	X.X +/- 0.4	+/- 1°	
X.XXX +/- 0.005	X.XX +/- 0.13	INCHES, THIRD ANGLE PROJECTION	
DRAWN BY MAV		SCALE NONE	
DATE 10-15-10		DRAWING NO. 09V098EK	
CHK'D KRKE		DWG B	