


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs (N)	WEIGHT lbs/100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)								
ERT2M-CXX	.38 (9.7)	2.35 (59.7)	.090 (2.29)	.500 (12.70)	.323 (8.20)	.406 (10.31)	.841 (21.36)	8.5 (216)	18 (80)	1.39 (633)
ERT3M-CXX	.38 (9.7)	3.0 (76.2)	.090 (2.29)	.500 (12.70)	.323 (8.20)	.406 (10.31)	.841 (21.36)	11.0 (279)	18 (80)	1.71 (776.3)
ERT4.5M-CXX	.38 (9.7)	4.5 (114)	.090 (2.29)	.500 (12.70)	.323 (8.20)	.406 (10.31)	.841 (21.36)	16.0 (406)	18 (80)	2.41 (1093.1)

* ERTXM-CXX

COLOR
QUANTITY IN PACKAGE
C = 100
PART NUMBER

XX	COLOR
20	BLACK

NOTES:

1. SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
2. MATERIAL FLAMMABILITY RATING: UL94V-0
3. HALOGEN FREE
4. PART IS RELEASABLE AND REUSABLE
5. PRODUCT IS RoHS COMPLIANT.
6. BLACK COLOR PROVIDES GREATER RESISTANCE TO DAMAGE CAUSED BY ULTRAVIOLET LIGHT - INDOOR OR OUTDOOR USE

CAD FILENAME/LAYERS W10001CK/07

PANDUIT CORP. TINLEY PARK, ILLINOIS

ELASTOMERIC CABLE TIES

UNLESS OTHERWISE SPECIFIED,
US NOMINAL DIMENSIONAL TOLERANCES ARE:

(.X)	± .1	(2.5)	(.XXX)	± .020	(.5)
(.XX)	± .02	(.5)	ANGLES	±	---

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES. THIRD ANGLE PROJECTION.

DRAWN BY ERW	DATE 11/11/2011
-----------------	--------------------

MAT'L;

DATE	12/26/07
------	----------

TPU

SCALE	NONE
-------	------

DRAWING NO.

SS-27570

DWG
A
SIZE

7	3/11/09	MJVE		ADDED NOTE 6	SS-27570	7			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	