

## Basic Rack PDU


### Overview

The American Power Conversion<sup>®</sup> Basic Rack PDU distributes power to devices in the rack.

**Outlets.** The Rack PDU has thirty-six (36) IEC 320-C13 outlets and 6 (6) IEC 320-C19 outlets.

**Power cord.** The 3-foot (0.91-meter) power cord terminates with a NEMA L21-20 connector.

**AP7564**



# Specifications for AP7564

---

## Electrical

---

Input connector	NEMA L21-20 plug
Output connectors	(36) IEC 320-C13 outlets (6) IEC 32-C19 outlets
Nominal input voltage	120/208 VAC 3-phase
Acceptable input voltage	± 10% of normal voltage
Input frequency	47–63 Hz

---

## Physical

---

(H × W × D)	70.00 × 2.19 × 1.73 in (177.80 × 5.56 × 4.39 cm)
Shipping dimensions (H × W × D)	84.00 × 6.00 × 5.00 in (213.36 × 15.24 × 12.7 cm)
Weight	12 lb (5.44 kg)
Shipping weight	19.5 lb (8.85 kg)

---

## Environmental

---

Maximum elevation (above MSL)	
Operating	15 000 ft (4500 m)
Storage	50 000 ft (15 000 m)
Temperature	
Operating	–5 to 45° C (23 to 115° F)
Storage	–25 to 65° C (–13 to 149° F)
Humidity	
Operating	5–95% RH non-condensing
Storage	5–95% RH non-condensing

---

## Compliance

---

Safety verification	UL, cUL 60950
---------------------	---------------

---

