


HLW TIES ARE CUSTOM PRINTED,
SEE DIMENSIONS G & H FOR MAXIMUM PRINTING AREA.

HLWM TIES ARE MARKER TIES WITH A WRITE-ON AREA
(SEE DIMENSIONS G & H)



PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	G in (mm)	H in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	APPROXIMATE WEIGHT lbs/100 PARTS (g)
	in MIN. (mm)	in MAX. (mm)											
HLW1.5S*	.25 (6.4)	1.5 (38.1)	.076 (1.9)	.79 (20.1)	.080 (2.0)	3.2 (81)	3.2 (81)	6.0 (152)	.5 (12.7)	2.5 (63.5)	50 (222)	STANDARD	.24 (108)
HLW3S*		3.2 (81.3)				6.2 (157)	6.2 (157)	12.0 (305)		3.1 (78.7)			.48 (217)
HLWM1.5S		1.5 (38.1)				3.2 (81)	3.2 (81)	6.0 (152)		2.5 (63.5)			.24 (108)
HLWM3S		3.2 (81.3)				6.2 (157)	6.2 (157)	12.0 (305)		.48 (217)			

2) MINIMUM 2" OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.

W10001CQ/01.PRT

PANDUIT CORP. TINLEY PARK, ILLINOIS

HOOK & LOOP TIES

HLW SERIES ARE CUSTOM PRINTED
HLWM SERIES ARE MARKER TIES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) $\pm .25$ (.XXX) $\pm .030$
(.XX) $\pm .125$ ANGLES \pm

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY JABO	
------------------	--

MAT'L:

SCALE	NONE
-------	------

DATE	7/31/09
------	---------

WOVEN NYLON
HOOK/LOOP

DRAWING NO.

SS - 27598

DWG
A
SIZE

--	----	---		CHANGED NOTE 1 SEE CURRENT PRICE SHEET... TO SEE www.panduit.com ...	---	--				
--	----	---		CORRECT BUNDLE DIA PER RAM1/DWW	---	--				
01	8/27/08	JABO		MOVED DIMS G & H TO DIMENSION AREA	27598	01				
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		