



by **Schneider** Electric

Metered Rack PDU

Overview


The American Power Conversion (APC®) Metered Rack Power Distribution Unit (PDU) distributes power to devices in the rack. It has a sensor that measures the current used by the PDU and its attached devices. The PDU can be monitored through Web, Telnet, SNMP, SSH, or InfraStruXure™ Central interfaces.

Outlets. The Rack PDU has twenty-four (24) NEMA 5-20 outlets.

Digital display. A digital display shows the aggregate current used by the Rack PDU.

Power cord. The 10-foot (3.05-meter) power cord terminates with a NEMA L5-20 connector.

AP7830





by **Schneider** Electric

Specifications

Electrical

Input connector	NEMA L5-20 plug
Output connectors	(24) NEMA 5-20 outlets
Nominal input voltage	120 VAC
Acceptable input voltage	$\pm 10\%$ of nominal voltage
Input frequency	50/60 Hz

Physical

Dimensions (H \times W \times D)	63.75 x 2.19 x 1.73 in (161.92 x 5.56 x 4.39 cm)
Shipping dimensions (H \times W \times D)	84.00 x 6.00 x 5.00 in (213.36 x 15.24 x 12.7 cm)
Weight	9.5 lb (4.3 kg)
Shipping weight	17 lb (7.7 kg)

Environmental

Maximum elevation (above MSL)	
Operating	15,000 ft (4500 m)
Storage	50,000 ft (15 000 m)
Temperature 11/2008	
Operating	23 to 115° F (–5 to 45° C)
Storage	–13 to 149° F (–25 to 65° C)
Humidity	
Operating	5 – 95% RH non-condensing
Storage	5 – 95% RH non-condensing

Compliance

EMC verification	FCC Part 15 Class A ICES-003 Class A
Safety verification	UL 60950 cUL CSA22.2 No. 60950

Customer support and warranty information is available at the APC Web site, www.apc.com.

© 2008 American Power Conversion. All rights reserved. All APC trademarks are property of American Power Conversion. Other trademarks are property of their respective owners.



990-1947B
11/2008

