



PANDUIT P/N	WEIGHT
T70FSB	0.34 LB/ 10 PCS (154 G / 10PCS)



- NOTES:
- 1) THIS PART IS TO BE USED WITH THE T70 OR T702 SERIES RACEWAY.
 - 2) THIS BRACKET WILL LATCH ONTO THE CENTER OF THE RACEWAY BASE- IF NO DIVIDER WALLS ARE PRESENT.
 - 3) THIS BRACKET CAN ALSO LATCH OFFSET TO THE CENTER OF THE RACEWAY BASE- IF ONE OUTER DIVIDER WALL IS PRESENT.
 - 4) TWO OF THESE BRACKETS MUST BE INSTALLED IN ORDER TO OBTAIN A COMPLETE FIBER SPOOL. THIS TWO-PIECE SPLIT DESIGN ALLOWS THE BRACKET DISTANCE TO BE ADJUSTED TO FIT THE LENGTH OF CABLE STORAGE REQUIRED.
 - 5) THIS PART CAN STORE A MINIMUM OF 3.28 FEET (1 METER) OF DUPLEX FIBER OPTIC CABLE AT A 1 INCH (25.4 MILLIMETER) MINIMUM BEND RADIUS- WHEN THE SPOOL PORTIONS OF THE BRACKET HALVES ARE TOUCHING. CABLE STORAGE CAN BE INCREASED BEYOND 1 METER BY SPREADING THE BRACKET HALVES FARTHER APART.
 - 6) DIMENSIONS IN PARENTHESES ARE IN METRIC.



										CAD FILENAME/LAYERS		D37336BE_DC_T70FSB_00A.PRT		
										PANDUIT				
										CORP. TINLEY PARK, ILLINOIS				
										T70 FIBER SPOOL BRACKET				
										(T70FSB)				
										CUSTOMER DRAWING				
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ±.03(.8) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.		
										DRAWN BY JHNU	MAT'L: PVC	SCALE NONE		
R	12/21/99	JHNU	RCRO	RELEASED TO PRODUCTION.		37336-02	HIW	HIW		DATE 12/21/99		DRAWING NO. 37336-02		DWG A
REV	DATE	BY	CHK	DESCRIPTION		ECN	CHK	CUST	SUP	CHECKED BY RCRO		SIZE A		