

Product Data Sheet

Welding Cable



Product Description

Thermoset insulation
 Thermoset jacket
 105°C

Welding Machine Rating	Lengths up to 45 ft. AWG	Lengths up to 100 ft. AWG	Lengths up to 250 ft. AWG
75 Amperes	4	4	4
100 Amperes	2	2	2
200 Amperes	1	1	2/0
300 Amperes	1/0	2/0	4/0
400 Amperes	2/0	3/0	-
600 Amperes	3/0	4/0	-

Note: Lengths are from power supply to electrode holder (one way). Ampacity values are not NEC values.

Applications

For use as flexible lead from welding machine to electrode holder. These cables are designed for use only with the secondary voltages typical of welding equipment. Can not be used as motor lead.

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied.

The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.

Specifications

- CONDUCTOR: Highly flexible stranded no. 30 awg bare copper with separator applied over the conductor
- OVERALL JACKET: Industrial Grade Ethylene Propylene Thermoset (EPDM) Rubber

Class K and M and UL approved available upon request. Diameters and weights may vary among manufacturers. Additional colors available from stock. Stranding varies by manufacturers.

Anixter No.	Conductor Size AWG/kcmil	No. of Strands	Insulation Thickness (in.)	Nom. O.D. (in.)	Approx Wt. lb./1,000 ft.
5J-0101	1	30	0.08	0.503	313
5J-0201	2	30	0.06	0.42	236
5J-0301	3	532	0.07	0.470	230
5J-0401	4	30	0.06	0.348	147
5J-0601	6	30	0.06	0.32	113
5J-1011	1/0	30	0.08	0.533	378
5J-2021	2/0	30	0.08	0.586	463
5J-2501	250	30	0.08	0.815	962
5J-3031	3/0	30	0.08	0.625	563
5J-3501	350	30	0.1	0.955	1310
5J-4041	4/0	30	0.08	0.72	734
5J-5001	500	30	0.125	1.21	1700

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied. The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.