


Automatic Transfer Switch

Overview

The American Power Conversion (APC®) Rack Automatic Transfer Switch (ATS) provides reliable, redundant power to single-corded equipment. The Rack ATS has dual input power cords supplying power to the connected load. If the primary source becomes unavailable, the Rack ATS will seamlessly source power from the secondary source without interrupting critical loads. Networked units have built-in network connectivity, which allows for remote management via Web, SNMP, or Telnet interfaces.

Rear view—AP7730



	Item	Description/Function
❶	Power cords	The two cords connect the ATS to two separate power sources (A, B). The switch draws power from the preferred source and automatically switches to the secondary source when necessary. The two (2) 2.44-m (8-ft) power cords have L6-20 plugs.
❷	Outlets	The outlets connect the ATS to equipment in the rack or enclosure, providing a redundant source of power to the connected equipment. Each switch has eight (8) C13 outlets and one (1) C19 outlet.

Specifications

AP7730

Electrical

Nominal input voltage	200–208 Vac
Acceptable input voltage	±10% of nominal
Input frequency	50/60 Hz
Input connectors	Two (2) 2.44-m (8-ft) L6-20 power cords
Input overcurrent protection	20 A
Output connectors	Eight (8) C13 outlets One (1) C19 outlet
Maximum output current (outlet)	12 A–C13 (15 A Japan) 16 A–C19 (20 A Japan)
Maximum output/input current	16 A (derated) for U.S. and Canada 20 A for Japan
Overload protection	
Internal	Not provided with unit
External (recommended)	20 A facility provided
Transfer time	8–12 ms typical, 16 ms maximum 60 Hz, 18 ms maximum 50 Hz

Physical

Dimensions (H x W x D)	4.37 x 43.00 x 23.62 cm (1.72 x 17.00 x 9.30 in)
Shipping dimensions (H x W x D)	11.43 x 60.02 x 35.56 cm (4.50 x 23.63 x 14.00 in)
Weight	4.74 kg (10.45 lb)
Shipping weight	6.51 kg (14.35 lb)

Environmental

Maximum elevation (above MSL)	
Operating	0 to 3000 m (0 to 10,000 ft)
Storage	0 to 15 000 m (0 to 50,000 ft)
Temperature	
Operating	–5 to 45°C (23 to 113°F)
Storage	–25 to 65°C (–13 to 149°F)
Humidity	
Operating	0 to 95%, non-condensing
Storage	0 to 95%, non-condensing

Compliance

EMC approvals	FCC-Class A, VCCI, ICES-003 Class A
Safety approvals	TUVR-NRTL, TUVR-C, TUVR-PSE