



**2 Series**

# F2164

**FAIL SECURE  
FIRE-RATED**

# 2364

**FAIL SAFE**



Strength  
1500lbf Static



Warranty  
5 Year Limited Warranty



Door Frames  
Design Works With  
Most Material Types



Mode  
Fail Secure or Fail Safe




Latch Monitor  
Optional Plug-In Latch Monitor (Accessory)



Fire-Rated  
F2164 – 3 Hour Fire Rating

Versatile, all-in-one strike  
designed for offset and  
centerline latch entry

# F2164/2364 ELECTRIC STRIKE



Saw-tooth  
adjustment locator†

Deadbolt plug



Adjustable  
deadbolt keeper

Adjustable  
deadlatch ramp

Optional plug-in  
latch monitor†  
(accessory)

†Patent pending  
features

## Dimensions

ANSI 1-1/4" x 4-7/8" x 1-3/4"  
(31.75mm x 124mm x 45mm)

## Features

- Modular design allows compatibility with most locks – no special faceplates required
- Adjustable deadbolt keeper and deadlatch ramp
- Heavy-duty stainless steel construction with brushed stainless steel finish (32D)
- Up to 1500lbf (680kgf) holding force
- Fits HES 1006 (1003) frame cutout (hollow metal)
- Accommodates up to 3/4" latch projection
- Faceplate and screws included for centerline latch entry
- Unique sliding shim design for up to 1/8" (3mm) horizontal adjustment for misaligned frames ‡
- Vertical adjustability up to 5/16" of strike for precise alignment with lockset
- Accommodates up to 1" deadbolt (night-latch function only, bolt will not release)
- Field selectable voltage input – accommodates 12 or 24VDC and 12 to 24VAC
- Anti-tamper security screws
- Star and security driver bit included
- Optional "Plug-in" latch monitor kit (accessory)
- Low current draw (0.19 Amps @24VDC)
- "Cool keeper" solenoid design prevents keeper from heating up
- Plug-in wire connector
- Trim plate included
- Adhesive paper template included
- Non-handed
- 5 year limited warranty

## Faceplates

- F2-19-32D – Centerline Latch Entry 1-3/8"x9"
- F2-29-32D – Offset Latch Entry 1-3/8"x9"

(Faceplates are not fire-rated or security tested)

## Accessories

- F2LM – Latch Monitor Kit
- 940-LG – High Profile Latch Guard
- ICEPK – Heat Reducer for Continuous Duty Strikes
- 2FP – Filler Plate (use only when replacing discontinued 2 Series models)

The Latch Monitor Module has a SPDT switch. This module can be mounted anywhere in the strike cavity to correspond to latch position.

**Note:** F2LM is rated at 2 Amps @ 24VDC and is only compatible with up to 3/4" latch throw

## Frame Type



Hollow Metal



Aluminum




Wood

## Door Lock Type



Mortise



Cylindrical



Mortise Exit Device

## Certifications & Testing

- Listed to UL 10C, 3 hour fire-rated (F2164 – fail secure only)
- Listed to UL 1034, burglary-resistant listed
- CAN/ULC S104 for
- Factory tested to meet ANSI/BHMA 156.31 for strength and endurance
- Factory tested to exceed 2,000,000 cycles

## SECURITY



F2164 on cylindrical  
and mortise locks only

Model	Mode	Volts	Duty	Sound	Amps*	Ohms†
F2164	Fail Secure	12VDC	Continuous	Silent	0.375	37
		24VDC			0.190	148
		12-24VAC	Intermittent	Buzz	0.280-0.565	37
2364	Fail Safe	12VDC	Continuous	Silent	0.375	37
		24VDC			0.190	148

Intermittent Duty: Energized less than 1 minute with Duty Ratio 1:5

Continuous Duty: Energized 1 minute or more

\*Ratings are based on maximum current draw at +10°C and include initial power-up current draw

†Nominal resistance at +25°C ± 7% tolerance