
FD1 Series Entry-Level Indoor Fixed Dome

1/3-INCH CCD, 540 TVL WITH HIGH SENSITIVITY, IR OPTION

Product Features

- 540 TV Lines
- 0.2 Lux Sensitivity (No IR), Zero Lux (with IR)
- Sony® 1/3-Inch Super HAD CCD II™ 760H
- NextChip Digital Signal Processor (DSP)
- · 2 Camera Options:
 - IR Illumination Day/Night Indoor Dome
 - Color Indoor Dome
- Diversified Fixed or Varifocal Lens (Based on Model)
- Shipped Completely Assembled, Easy to Install
- 12 VDC Power with Internal Synchronization



The **FD1-IRF/FD1-IRV Series** integrates fixed and varifocal lenses with supplemental IR lighting. This camera can be mounted to a ceiling or wall and positioned using a 3-axis gimbal.

The **FD1 Series** offers two camera options suitable for a variety of indoor environments:

- IR Illumination Day/Night Indoor Dome: Features a 540 TVL color camera with fixed or varifocal lens and electronic day/night functions. This camera uses a group of IR LEDs as supplemental lighting, creating an effective IR Illumination distance of 15 to 20 meters. This camera is suitable for environments with low-light conditions that need a supplemental IR light source.
- Color Indoor Dome: Features a 540 TVL color camera with a fixed lens. This camera is suitable for general applications in general fixed lighting conditions.

The **FD1 Series** is shipped completely assembled, making installation fast and easy. To surface-mount the unit, remove it from the box, attach it to the mounting surface, and connect video and power.



FD1-F SERIES



FD1-IRV SERIES





TECHNICAL SPECIFICATIONS

CAMERA/OPTICS

	FD1-F Series Fixed Lens Models	FD1-IRF Series IR Illumination Fixed Lens Models	FD1-IRV Series IR Illumination Varifocal Lens Models	
Image Sensor	Sony 1/3-Inch Super HAD CCD II [™] 760H	Sony 1/3-Inch Super HAD CCD II 760H	Sony 1/3-Inch Super HAD CCD II 760H	
Signal Processing	NextChip DSP	NextChip DSP	NextChip DSP	
Effective Pixels NTSC PAL	768 (H) x 494 (V) 752 (H) x 582 (V)	768 (H) x 494 (V) 752 (H) x 582 (V)	768 (H) x 494 (V) 752 (H) x 582 (V)	
Scanning Area	5.59 (H) mm x 4.68 (V) mm (0.22 x 0.18 inch)	5.59 (H) mm x 4.68 (V) mm (0.22 x 0.18 inch)	5.59 (H) mm x 4.68 (V) mm (0.22 x 0.18 inch)	
Scanning System NTSC PAL	525 lines, 2:1 interlace 625 lines, 2:1 interlace	525 lines, 2:1 interlace 625 lines, 2:1 interlace	525 lines, 2:1 interlace 625 lines, 2:1 interlace	
Scanning Frequency NTSC PAL	Horizontal, 15.734 kHz Vertical, 59.94 Hz Horizontal, 15.625 kHz Vertical, 50.00 Hz	Horizontal, 15.734 kHz Vertical, 59.94 Hz Horizontal, 15.625 kHz Vertical, 50.00 Hz	Horizontal, 15.734 kHz Vertical, 59.94 Hz Horizontal, 15.625 kHz Vertical, 50.00 Hz	
Synchronization	Internal	Internal	Internal	
Horizontal Resolution	540 TVL	540 TVL	540 TVL	
Minimum Illumination	f/2.0; 2,850°K; 30 IRE Color 0.2 lux	f/2.0; 2,850°K; 30 IRE Color 0.2 lux Mono (with IR) 0.0 lux	f/1.2; 2,850°K; 30 IRE Color 0.13 lux Mono (with IR) 0.0 lux	
IR Cut Filter	Fixed	Dual band OLPF	Dual band OLPF	
IR Illumination Distance	_	15 m	20 m	
IR Sensitivity	_	>40% at 850 nm, peak response	>40% at 850 nm, peak response	
Low-Light Technology	_	LEDs	LEDs	
Electronic Shutter Range NTSC PAL	Auto 1/60 ~ 1/10,000 sec Auto 1/50 ~ 1/10,000 sec	Auto 1/60 ~ 1/10,000 sec Auto 1/50 ~ 1/10,000 sec	Auto 1/60 ~ 1/10,000 sec Auto 1/50 ~ 1/10,000 sec	
Video Output	1.0 Vp-p, NTSC/PAL composite, 75 ohms, BNC connector	1.0 Vp-p, NTSC/PAL composite, 75 ohms, BNC connector	1.0 Vp-p, NTSC/PAL composite, 75 ohms, BNC connector	
White Balance	Auto	Auto	Auto	
Signal-to-Noise Ratio	48 dB	48 dB	48 dB	
Lens	Fixed	Fixed	Varifocal	
F-Number	f/2.0	f/2.0	f/1.2	
Focal Length	3.6 mm	3.6 mm	3.0 to 9.0 mm, DC AI	
Focus Range	∞ to 1.2 m (3.9 ft)	∞ to 1.2 m (3.9 ft)	∞ to 0.5 m (1.6 ft)	
Horizontal Angle of View	72° at 3.6 mm	72°	85.3° at 3.0 mm wide zoom; 31.5° at 9.0 mm telephoto zoom	
Vertical Angle of View	52° at 3.6 mm	52°	63.8° at 3.0 mm wide zoom; 23.7° at 9.0 mm telephoto zoom	
Adjusting Angle Panning Range Tilting Range Rotation Range	±180° +80° to 0° 0°	±180° +55° to 0° ±180°	±180° +55° to 0° ±180°	
Noise Reduction	2D	2D	2D	

TECHNICAL SPECIFICATIONS

GENERAL

Back Box Construction ABS plastic
Bubble Type Lightly obscured

 Weight
 Unit
 Shipping

 FD1-F Series
 0.12 kg (0.26 lb)
 0.22 kg (0.49 lb)

 FD1-IRF Series
 0.25 kg (0.55 lb)
 0.55 kg (1.21 lb)

 FD1-IRV Series
 0.26 kg (0.57 lb)
 0.56 kg (1.23 lb)

ELECTRICAL

Power Requirement

NTSC 12 VDC +10% to -15%, 60 Hz PAL 12 VDC +10% to -15%, 50 Hz

Power Consumption

FD1-F Series 1 W FD1-IRF/FD1-IRV Series 2.7 W

Power Connector 2-pin terminal block with screw terminal

Video Connector BNC

ENVIRONMENTAL

Operating Temperature -10° to 50°C (14° to 122°F)
Storage Temperature -20° to 60°C (-40° to 140°F)
Operating Humidity 20% to 80%, noncondensing
Storage Humidity 20% to 90%, noncondensing


CERTIFICATIONS

- CE, Class B
- FCC, Class B
- UL/cUL Listed




NOTE: VALUES IN PARENTHESES ARE INCHES; ALL OTHERS ARE CENTIMETERS.

FD1-F SERIES



FD1-IRF/FD1-IRV SERIES



TECHNICAL SPECIFICATIONS

MODELS

Camera Type	Lens Type	NTSC	PAL
Color	Fixed, 3.6 mm	FD1-F4-4	FD1-F4-4X
IR Illumination	Fixed, 3.6 mm	FD1-IRF4-4	FD1-IRF4-4X
IR Illumination	Varifocal, 3.0 to 9.0 mm	FD1-IRV9-4	FD1-IRV9-4X

OPTIONAL ACCESSORIES

TW4001PC

Passive twisted wire transmission for use in unshielded twisted pair (UTP) installations