



by Schneider Electric

Basic Rack PDU


Overview

The American Power Conversion (APC™) Basic Rack Power Distribution Unit (PDU) distributes power to devices in the rack.

Outlets. The Rack PDU has thirty (30) IEC-320-C13 outlets (15 A maximum) and six (6) IEC-320-C19 outlets (16 A maximum). APC power cord AP9877 (1.98 m; 6.5 ft) is available for purchase for use with C19 outlets.

Input power cord. The 0.91-m (3-ft) power cord terminates with a CS8365C connector.

AP7568



Specifications

Electrical

Input connector	CS8365C plug
Output connectors	(30) IEC-320-C13 (6) IEC-320-C19 outlets
Cord length	0.91 m (3 ft)
Nominal input voltage	200 - 240 VAC, 3-phase
Acceptable input voltage	+6%, -10% of nominal voltage
Input frequency	50/60 Hz
Output current	15A/C13, 16A/C19; 16A/bank
Overload protection	
Internal	(3) 20-A 2-pole breakers
External	(1) 50-A 3-pole breaker

Physical

Dimensions (H × W × D) <i>(Including breaker box)</i>	1778×56×45 mm (70.00×2.20×1.75 in) 1778×56×89 mm (70.00×2.20×3.50 in [†])
Shipping dimensions (H × W × D)	211 × 15 × 127 mm (83.00×6.00×5.00 in)
Weight	6.93 kg (15.28 lb)
Shipping weight	10.15 kg (22.38 lb)

Environmental

Maximum elevation (above MSL)	
Operating	3000 m (10,000 ft)
Storage	15 000 m (50,000 ft)
Temperature	
Operating	-5 to 45° C (23 to 115° F)
Storage	-25 to 65° C (-13 to 149° F)
Humidity	
Operating	5 – 95% RH non-condensing
Storage	5 – 95% RH non-condensing

Regulatory Approvals

Product safety	UL, cUL Listed
----------------	----------------

[†] The depth with the breaker box (89 mm; 35.0 in) extends for only a part (190 mm; 7.50 in) of the height of the unit.