



SAFETY DATA SHEET

FUELSEAL

Page: 1

Compilation date: 24/11/2014

Revision date: 6/07/15

Revision No: 3

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: FUELSEAL

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Joining compound.

1.3. Details of the supplier of the safety data sheet

Company name: ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

Tel: +44 (0) 113 232 2700

Fax: +44 (0) 113 232 2740

Email: customer-service@rocol.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 113 232 2600

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: STOT SE 3: H336; Eye Irrit. 2: H319; Flam. Liq. 2: H225; Skin Sens. 1: H317

Most important adverse effects: Highly flammable liquid and vapour. May cause an allergic skin reaction. Causes serious eye irritation. May cause drowsiness or dizziness.

2.2. Label elements

Label elements:

Hazard statements: H225: Highly flammable liquid and vapour.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H336: May cause drowsiness or dizziness.

Hazard pictograms: GHS02: Flame

GHS07: Exclamation mark



[cont...]

SAFETY DATA SHEET

FUELSEAL

Page: 2

Signal words: Danger

Precautionary statements: P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P302+352: IF ON SKIN: Wash with plenty of water/.

P303+361+353: IF ON SKIN (or hair): Take off immediately all contaminated clothing.

Rinse skin with water/shower.

P304+340: IF INHALED: Remove person to fresh air and keep comfortable for breathing.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

PROPAN-2-OL

EINECS	CAS	PBT / WEL	CLP Classification	Percent
200-661-7	67-63-0	-	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336	20-30%

PINE TAR

232-374-8	8011-48-1	-	Skin Sens. 1: H317	1-5%
-----------	-----------	---	--------------------	------

XYLENE

215-535-7	1330-20-7	-	Flam. Liq. 3: H226; Acute Tox. 4: H332; Acute Tox. 4: H312; Skin Irrit. 2: H315	<1%
-----------	-----------	---	---	-----

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Drench the affected skin with running water for 10 minutes or longer if substance is still on skin. Consult a doctor.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Do not induce vomiting. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Drowsiness or mental confusion may occur.

[cont...]

SAFETY DATA SHEET

FUELSEAL

Page: 3

4.3. Indication of any immediate medical attention and special treatment needed

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Use water spray to cool containers. Dry chemical powder. Alcohol resistant foam.
Carbon dioxide.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Eliminate all sources of ignition. Do not attempt to take action without suitable protective clothing - see section 8 of SDS.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Clean-up should be dealt with only by qualified personnel familiar with the specific substance. Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area.
Smoking is forbidden. Use non-sparking tools.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep away from sources of ignition. Keep container tightly closed.

7.3. Specific end use(s)

Section 8: Exposure controls/personal protection

8.1. Control parameters

[cont...]

SAFETY DATA SHEET

FUELSEAL

Page: 4

Hazardous ingredients:

PROPAN-2-OL

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	400 ppm, 999 mg/m3	500 ppm, 1250 mg/m3	-	-

XYLENE

UK	220 mg/m3	441 mg/m3	-	-
----	-----------	-----------	---	---

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area. Ensure lighting and electrical equipment are not a source of ignition.

Respiratory protection: Respiratory protection not normally required.

Hand protection: Nitrile gloves.

Eye protection: Safety glasses with side-shields. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Red-brown

Odour: Characteristic odour

Evaporation rate: Fast

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Slightly soluble

Viscosity: Viscous

Melting point/range°C: < 0

Flash point°C: <21

Autoflammability°C: > 200

Relative density: > 1

pH: Approx. 7

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

[cont...]

SAFETY DATA SHEET

FUELSEAL

Page: 5

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

10.4. Conditions to avoid

Conditions to avoid: Heat. Direct sunlight.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong reducing agents.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

PROPAN-2-OL

IVN	RAT	LD50	1088	mg/kg
ORL	MUS	LD50	3600	mg/kg
ORL	RAT	LD50	5045	mg/kg
SCU	MUS	LDLO	6	gm/kg

XYLENE

ORL	MUS	LD50	2119	mg/kg
ORL	RAT	LD50	4300	mg/kg
SCU	RAT	LD50	1700	mg/kg

Relevant hazards for substance:

Hazard	Route	Basis
Serious eye damage/irritation	OPT	Hazardous: calculated
Respiratory/skin sensitisation	DRM	Hazardous: calculated
STOT-single exposure	-	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Drowsiness or mental confusion may occur.

[cont...]

SAFETY DATA SHEET

FUELSEAL

Page: 6

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Only slightly biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Volatile. Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN1993

14.2. UN proper shipping name

Shipping name: FLAMMABLE LIQUID, N.O.S.
(contains propan-2-ol, xylene)

14.3. Transport hazard class(es)

Transport class: 3

14.4. Packing group

Packing group: II

14.5. Environmental hazards

Environmentally hazardous: No

Marine pollutant: No

14.6. Special precautions for user

Tunnel code: D/E

Transport category: 2

[cont...]

SAFETY DATA SHEET

FUELSEAL

Page: 7

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

Compiled in accordance with REACH.

Phrases used in s.2 and s.3: H225: Highly flammable liquid and vapour.

H226: Flammable liquid and vapour.

H312: Harmful in contact with skin.

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H332: Harmful if inhaled.

H336: May cause drowsiness or dizziness.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.