



SAFETY DATA SHEET

DRY MOLY SPRAY

Page: 1

Compilation date: 09/09/2014

Revision No: 6

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: DRY MOLY SPRAY

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Dry film lubricant.

1.3. Details of the supplier of the safety data sheet

Company name: ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

Tel: +44 (0) 113 232 2700

Fax: +44 (0) 113 232 2740

Email: customer-service@rocol.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 113 232 2600

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Eye Irrit. 2: H319; Flam. Aerosol 1: H222; STOT SE 3: H336; -: H229

Most important adverse effects: Extremely flammable aerosol. Pressurised container: May burst if heated. Causes serious eye irritation. May cause drowsiness or dizziness.

2.2. Label elements

Label elements:

Hazard statements: H222: Extremely flammable aerosol.

H229: Pressurised container: May burst if heated

H319: Causes serious eye irritation.

H336: May cause drowsiness or dizziness.

Hazard pictograms: GHS02: Flame

GHS07: Exclamation mark



[cont...]

SAFETY DATA SHEET

DRY MOLY SPRAY

Page: 2

Signal words: Danger

Precautionary statements: P410+412: Protect from sunlight. Do not expose to temperatures exceeding 50 °C.
P251: Do not pierce or burn, even after use.
P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211: Do not spray on an open flame or other ignition source.
P285: In case of inadequate ventilation wear respiratory protection.
P280: Wear protective gloves/protective clothing/eye protection/face protection.
P304+340: IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P312: Call a POISON CENTER/doctor//if you feel unwell.
P501: Dispose of contents/container to local/national regulations.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

HYDROCARBON AEROSOL PROPELLANT (<0.1% 1,3-BUTADIENE) - REACH registered number(s): EXEMPT

EINECS	CAS	PBT / WEL	CLP Classification	Percent
270-704-2	68476-85-7	Substance with a Community workplace exposure limit.	Flam. Gas 1: H220; Press. Gas: H280	50-70%

ACETONE

200-662-2	67-64-1	-	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336; -: EUH066	10-30%
-----------	---------	---	--	--------

XYLENE

215-535-7	1330-20-7	-	Flam. Liq. 3: H226; Acute Tox. 4: H332; Acute Tox. 4: H312; Skin Irrit. 2: H315	<2%
-----------	-----------	---	---	-----

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water. Consult a doctor.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Do not induce vomiting. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

[cont...]

SAFETY DATA SHEET

DRY MOLY SPRAY

Page: 3

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat. May cause dizziness.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Drowsiness or mental confusion may occur.

Delayed / immediate effects: No data available.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: No data available.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Do not use water. Alcohol resistant foam. Carbon dioxide. Dry chemical powder. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: Extremely flammable. Forms explosive air-vapour mixture. In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. Eliminate all sources of ignition.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Do not use equipment in clean-up procedure which may produce sparks. Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS. Refer to section 13 of SDS.

Section 7: Handling and storage

[cont...]

SAFETY DATA SHEET

DRY MOLY SPRAY

Page: 4

7.1. Precautions for safe handling

Handling requirements: Ensure there is sufficient ventilation of the area. Do not handle in a confined space.
Smoking is forbidden.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep away from sources of ignition. Keep away from direct sunlight. Ensure lighting and electrical equipment are not a source of ignition.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

HYDROCARBON AEROSOL PROPELLANT (<0.1% 1,3-BUTADIENE)

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	1000ppm 1750mg/m3	1250ppm 2180mg/m3	-	-

ACETONE

UK	1210 mg/m3	3620 mg/m3	-	-
----	------------	------------	---	---

XYLENE

UK	220 mg/m3	441 mg/m3	-	-
----	-----------	-----------	---	---

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area. Ensure lighting and electrical equipment are not a source of ignition.

Respiratory protection: Respiratory protection not normally required. Gas/vapour filter, type A: organic vapours (EN141).

Hand protection: Protective gloves. Nitrile gloves.

Eye protection: Safety glasses with side-shields.

Skin protection: Protective clothing.

Environmental: No data available

Section 9: Physical and chemical properties

[cont...]

SAFETY DATA SHEET

DRY MOLY SPRAY

Page: 5

9.1. Information on basic physical and chemical properties

State: Aerosol

Colour: Black

Odour: Sweet-smelling

Evaporation rate: Fast

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Soluble

Viscosity: Non-viscous

Boiling point/range°C: < 0

Melting point/range°C: < -130

Flammability limits %: lower: 1.8

upper: 9.4

Flash point°C: < -100

Autoflammability°C: 430

Relative density: < 1

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

10.4. Conditions to avoid

Conditions to avoid: Direct sunlight. Heat. Sources of ignition.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong reducing agents.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

[cont...]

SAFETY DATA SHEET

DRY MOLY SPRAY

Page: 6

ACETONE

IVN	RAT	LD50	5500	mg/kg
ORL	MUS	LD50	3	gm/kg
ORL	RAT	LD50	5800	mg/kg

XYLENE

ORL	MUS	LD50	2119	mg/kg
ORL	RAT	LD50	4300	mg/kg
SCU	RAT	LD50	1700	mg/kg

Relevant hazards for product:

Hazard	Route	Basis
Serious eye damage/irritation	OPT	Hazardous: calculated
STOT-single exposure	-	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat. May cause dizziness.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Drowsiness or mental confusion may occur.

Delayed / immediate effects: No data available.

Section 12: Ecological information

12.1. Toxicity

Hazardous ingredients:

ACETONE

BLUEGILL (<i>Lepomis macrochirus</i>)	LC50	8300	mg/l
---	------	------	------

12.2. Persistence and degradability

Persistence and degradability: Only slightly biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Highly volatile. Soluble in water.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

[cont...]

SAFETY DATA SHEET

DRY MOLY SPRAY

Page: 7

12.6. Other adverse effects

Other adverse effects: No data available.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: No data available.

Recovery operations: No data available

Waste code number: 16 05 05

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN1950

14.2. UN proper shipping name

Shipping name: AEROSOLS, FLAMMABLE

14.3. Transport hazard class(es)

Transport class: 2.1

14.4. Packing group

Packing group: n/a

14.5. Environmental hazards

Environmentally hazardous: No

Marine pollutant: No

14.6. Special precautions for user

Special precautions: No special precautions.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: No data available

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

[cont...]

SAFETY DATA SHEET

DRY MOLY SPRAY

Page: 8

EC Directive 94/1/EC adapting some technicalities of Council Directive 75/324/EEC on the approximation of the laws of Member States relating to aerosol dispensers.

Phrases used in s.2 and s.3: EUH066: Repeated exposure may cause skin dryness or cracking.

H220: Extremely flammable gas.

H222: Extremely flammable aerosol.

H225: Highly flammable liquid and vapour.

H226: Flammable liquid and vapour.

H229: Pressurised container: May burst if heated

H280: Contains gas under pressure; may explode if heated.

H312: Harmful in contact with skin.

H315: Causes skin irritation.

H319: Causes serious eye irritation.

H332: Harmful if inhaled.

H336: May cause drowsiness or dizziness.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.