



SAFETY DATA SHEET

PX-28

Page: 1

Compilation date: 08/12/2014

Revision No: 4

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: PX-28

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Corrosion Inhibitor

1.3. Details of the supplier of the safety data sheet

Company name: ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

Tel: +44 (0) 113 232 2700

Fax: +44 (0) 113 232 2740

Email: customer-service@rocol.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 113 232 2600

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: STOT SE 3: H336; Aquatic Chronic 3: H412; Flam. Liq. 3: H226; Skin Irrit. 2: H315; STOT SE 3: H335

Most important adverse effects: Flammable liquid and vapour. Causes skin irritation. May cause respiratory irritation. May cause drowsiness or dizziness. Harmful to aquatic life with long lasting effects.

2.2. Label elements

Label elements:

Hazard statements: H226: Flammable liquid and vapour.

H315: Causes skin irritation.

H335: May cause respiratory irritation.

H336: May cause drowsiness or dizziness.

H412: Harmful to aquatic life with long lasting effects.

Hazard pictograms: GHS02: Flame

GHS07: Exclamation mark



[cont...]

SAFETY DATA SHEET

PX-28

Page: 2

Signal words: Warning

Precautionary statements: P233: Keep container tightly closed.

P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P241: Use explosion-proof electrical/ventilating/lighting equipment.

P243: Take precautionary measures against static discharge.

P261: Avoid breathing dust/fumes/gas/mist/vapours/spray.

P271: Use only outdoors or in a well-ventilated area.

P273: Avoid release to the environment.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P302+352: IF ON SKIN: Wash with plenty of water/.

P303+361+353: IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.

P304+340: IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P312: Call a POISON CENTER/doctor//if you feel unwell.

P332+313: If skin irritation occurs: Get medical advice/attention.

P501: Dispose of contents/container to local/national regulations.

2.3. Other hazards

Other hazards: In use, may form flammable / explosive vapour-air mixture.

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

HYDROCARBONS, C9-C11, N-ALKANES, ISOALKANES, CYCLICS, < 2% AROMATICS - REACH registered number(s): 01-2119463258-33

EINECS	CAS	PBT / WEL	CLP Classification	Percent
919-857-5	-	Substance with a Community workplace exposure limit.	Flam. Liq. 3: H226; Asp. Tox. 1: H304; STOT SE 3: H336; -: EUH066	10-30%

HYDROTREATED LIGHT DISTILLATE (PETROLEUM)

265-149-8	64742-47-8	-	Flam. Liq. 3: H226; Skin Irrit. 2: H315; STOT SE 3: H335; Asp. Tox. 1: H304; Aquatic Chronic 2: H411; STOT SE 3: H336	10-30%
-----------	------------	---	---	--------

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.

[cont...]

SAFETY DATA SHEET

PX-28

Page: 3

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Eye bathing equipment should be available on the premises.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Alcohol resistant foam. Water spray. Carbon dioxide. Dry chemical powder. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: Flammable. In combustion emits toxic fumes. Forms explosive air-vapour mixture.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn leaking containers leak-side up to prevent the escape of liquid. Eliminate all sources of ignition.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method. Do not use equipment in clean-up procedure which may produce sparks.

[cont...]

SAFETY DATA SHEET

PX-28

Page: 4

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area.
Do not handle in a confined space. Avoid the formation or spread of mists in the air.
Smoking is forbidden. Use non-sparking tools.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed. Keep away from sources of ignition. Prevent the build up of electrostatic charge in the immediate area.
Ensure lighting and electrical equipment are not a source of ignition.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

HYDROCARBONS, C9-C11, N-ALKANES, ISOALKANES, CYCLICS, < 2% AROMATICS

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	1200mg/m3, 197ppm	-	-	-

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area. Ensure lighting and electrical equipment are not a source of ignition.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency.

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

[cont...]

SAFETY DATA SHEET

PX-28

Page: 5

Colour: Brown

Odour: Characteristic odour

Evaporation rate: Negligible

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Insoluble

Viscosity: Viscous

Boiling point/range°C: > 150

Flammability limits %: lower: 0.6

upper: 7

Flash point°C: 40

Autoflammability°C: > 200

Relative density: < 1

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions. Stable at room temperature.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat. Hot surfaces. Sources of ignition. Flames.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

HYDROCARBONS, C9-C11, N-ALKANES, ISOALKANES, CYCLICS, < 2% AROMATICS

DERMAL	RBT	LD50	> 5000	ppmV
ORAL	RAT	LD50	> 5000	mg/kg

[cont...]

SAFETY DATA SHEET

PX-28

Page: 6

Relevant hazards for substance:

Hazard	Route	Basis
Skin corrosion/irritation	DRM	Hazardous: calculated
STOT-single exposure	INH	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

[cont...]

SAFETY DATA SHEET

PX-28

Page: 7

14.1. UN number

UN number: UN1993

14.2. UN proper shipping name

Shipping name: FLAMMABLE LIQUID, N.O.S.
(contains Hydrocarbons C9-C11, Distillates (petroleum) hydrotreated light)

14.3. Transport hazard class(es)

Transport class: 3

14.4. Packing group

Packing group: III

14.5. Environmental hazards

Environmentally hazardous: No

Marine pollutant: No

14.6. Special precautions for user

Special precautions: No special precautions.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

Compiled in accordance with REACH.

Product label must specify:

CONTAINS SUBSTANCE(S):

HYDROCARBONS, C9-C11, N-ALKANES, ISOALKANES, CYCLICS, < 2% AROMATICS
(EINECS 919-857-5)

HYDROTREATED LIGHT DISTILLATE (PETROLEUM) (CAS 64747-47-8)

Phrases used in s.2 and s.3: EUH066: Repeated exposure may cause skin dryness or cracking.

H226: Flammable liquid and vapour.

H304: May be fatal if swallowed and enters airways.

H315: Causes skin irritation.

H335: May cause respiratory irritation.

[cont...]

SAFETY DATA SHEET

PX-28

Page: 8

H336: May cause drowsiness or dizziness.

H411: Toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.