

## PROLINE™-CL COLOCATION SERVER CABINET



### INDUSTRY STANDARDS

EIA 310-D

### Standard Product

| Catalog Number | AxBxC mm/in.                              | No. of Compartments | Rack Units |
|----------------|---|---------------------|------------|
| PCLC2069B      | 1991 x 608 x 898<br>78.39 x 23.94 x 35.34 | 1                   | 42         |
| PCL2C2069B     | 1991 x 608 x 898<br>78.39 x 23.94 x 35.34 | 2                   | 20         |

### APPLICATION

PROLINE™ -CL Colocation Cabinets are designed for secure data centers that store computer equipment for multiple customers. Standard components allow cabinets to be configured with up to four separate, secure compartments that can be reconfigured on-site as needs change. Each compartment has its own front and back access and is passively cooled by virtue of the overall cabinet design.

### FEATURES

- Doors have locking trigger latch for easy access plus security
- Integral floor bolt-down brackets provide quick, secure installation
- Cable entry and fan mounting provision on top and two access panels on right side facilitate mounting and wiring equipment
- Usable cabinet depth is 660 mm ( 26 in.)

### Dual compartment pre-assembled package also includes:

- Colocation frame shelf to divide the frame into two secure compartments
- Cable management system to isolate the wiring to each compartment
- Optional compact cooling fan



### SPECIFICATIONS

- Welded 12 gauge steel frame
- 19-in. adjustable square hole, L-shaped rack angles front and rear
- Square holes spaced per EIA 310-D standards
- Front and rear vented 16 gauge steel door
- Optional 16 gauge vented window door with acrylic window
- Vented 16 gauge steel top
- 16 gauge right side barrier with two access plates

### FINISH

Pretreated steel coated with RAL 9005 black textured, low-gloss polyester powder paint. Other finishes available—contact Hoffman Customer Service.

### BULLETIN: DPSR



SIDES FOR COLOCATION CABINET PACKAGES

Order two sides for each row of cabinets for a secure, finished appearance. Order barriers to go between cabinets. Sides are finished with RAL 9005 fine-textured black polyester powder paint.

BULLETIN: DPC

| Catalog Number | Type    | Fits Frame H x D | Nominal Height x Depth | Nominal H x W in./mm |
|----------------|---------|------------------|------------------------|----------------------|
| PS209VB        | Vented  | 2000 x 900       | 1939 x 853             | 76.34 x 33.60        |
| PS2010VB       | Vented  | 2000 x 1000      | 1939 x 953             | 76.34 x 37.54        |
| PBCL209B       | Barrier | 2000 x 900       | 1939 x 853             | 76.34 x 33.60        |
| PBCL2010B      | Barrier | 2000 x 1000      | 1939 x 953             | 76.34 x 37.54        |

COLOCATION CABINET FRAMES

Colocation cabinet frames are available in two sizes.


BULLETIN: DPC

| Catalog Number | AxBxC in./mm                               |
|----------------|--|
| PF2069CLB      | 78.70 x 23.60 x 35.40<br>2000 x 600 x 900  |
| PF20610CLB     | 78.70 x 23.60 x 39.40<br>2000 x 600 x 1000 |

### COLOCATION DIVIDER SHELF

Provides a barrier that maintains security between compartments in colocation applications. Made of 14 gauge steel. Provides mounting surface for adjustable L-shaped rack angles. RAL 9005 black textured polyester paint finish. Load rating is 150 lb. (68 kg).

**BULLETIN: DPC**



| Catalog Number | L<br>mm/in.  | D<br>mm/in.  | Fits PROLINE<br>Enclosure Size<br>mm/in. |
|----------------|--------------|--------------|--|
| PFSHCL69B      | 842<br>33.14 | 680<br>26.77 | 600 x 900 (23.62 x 36.43)                |
| PFSHCL610B     | 942<br>37.08 | 780<br>30.75 | 600 x 1000 (23.62 x 39.37)               |

### COLOCATION POWER CABLE AND DATA CABLE WAY



Cable ways provide a means for distributing power or data connections to each compartment in an isolated fashion. Non-metallic light-gray composite material. Both kits include cable runway with cover and two end caps with cable knockouts. Power Cable Way Kit also includes four dual category 5 RJ45 connectors and cover plates.

**BULLETIN: DPC**

| Catalog Number | Type  | Connectors   | Length |
|----------------|-------|--|--------|
| PCLCMP         | Power | 6 duplex outlet boxes with covers                  | 2000   |
| PCLCMD         | Data  | 4 dual category 5 RJ45 connectors and cover plates | 2000   |

COLOCATION CABINET EXTERNAL COMPONENTS

Colocation cabinet external options include vented doors, with and without a window, vented tops and sides, a barrier side, a locking latch kit, a cooling fan and a fan finger guard.

BULLETIN: D85, DPC

PROLINE-CL Colocation Cabinet Vented Doors

| Catalog Number | Door Type | Fits Frame H x W | Nominal H x W<br>mm/in.     |
|----------------|-----------|------------------|-----------------------------|
| PD206VB        | Full      | 2000 x 600       | 1939 x 592<br>76.34 x 23.30 |
| PD206V2B       | 1/2       | 2000 x 600       | 967 x 592<br>38.08 x 23.30  |
| PD206V3B       | 1/3       | 2000 x 600       | 643 x 592<br>25.32 x 23.30  |
| PD206V4B       | 1/4       | 2000 x 600       | 481 x 592<br>18.94 x 23.30  |

PROLINE-CL Colocation Cabinet Vented Window Doors

| Catalog Number | Door Type | Fits Frame H x W | Nominal H x W<br>mm/in.     | Window H x W<br>mm/in.      |
|----------------|-----------|------------------|-----------------------------|-----------------------------|
| PDW206VB       | Full      | 2000 x 600       | 1939 x 592<br>76.34 x 23.30 | 1805 x 370<br>71.08 x 14.55 |
| PDW206V2B      | 1/2       | 2000 x 600       | 967 x 592<br>38.08 x 23.30  | 833 x 370<br>32.81 x 14.55  |
| PDW206V3B      | 1/3       | 2000 x 600       | 643 x 592<br>25.32 x 23.30  | 509 x 370<br>20.06 x 14.55  |
| PDW206V4B      | 1/4       | 2000 x 600       | 481 x 592<br>18.94 x 23.30  | 347 x 370<br>13.68 x 14.55  |

PROLINE-CL Colocation Cabinet Vented Top

| Catalog Number | Fits Frame Top W x D | Nominal W x D<br>mm/in.    |
|----------------|----------------------|----------------------------|
| PTCL69B        | 600 x 900            | 592 x 899<br>23.30 x 35.39 |
| PTCL610B       | 600 x 1000           | 592 x 999<br>23.30 x 39.32 |

Locking Latch, Fan and Finger Guard

| Catalog Number | Description  | Includes                         |
|----------------|--|----------------------------------|
| PTKLDC         | Individually Keyed Locking Latch Set, fits all DataCom doors | Two latches and two keys         |
| A4AXFNPG       | 4-in. Compact Cooling Fan, 115V, 50/60 Hz                    | One finger guard and power cord  |
| AGARD4         | Finger Guard   | Use on 4-in. Compact Cooling Fan |

COLOCATION CABINET INTERNAL COMPONENTS

Available colocation cabinet internal components customize the enclosure.

BULLETIN: DPC

L-Shaped, Square Hole Rack Angles

| Catalog Number | Door Style | Height<br>mm/in. | Fits Frame Height<br>mm/in. | Rack Units |
|----------------|------------|------------------|-----------------------------|------------|
| PRA1920THL1    | Full       | 1905<br>75.00    | 2000<br>78.74               | 42         |
| PRA1920THL2    | 1/2        | 914<br>36.00     | 2000<br>78.74               | 20         |
| PRA1920THL3    | 1/3        | 594<br>23.38     | 2000<br>78.74               | 13         |
| PRA1920THL4    | 1/4        | 419<br>16.50     | 2000<br>78.74               | 9          |