



SAFETY DATA SHEET

Z30 SPRAY

Page: 1

Compilation date: 08/09/2014

Revision No: 8

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: Z30 SPRAY

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Lubricant and Corrosion Preventative

1.3. Details of the supplier of the safety data sheet

Company name: ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

Tel: +44 (0) 113 232 2700

Fax: +44 (0) 113 232 2740

Email: customer-service@rocol.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 113 232 2600

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Flam. Aerosol 1: H222; Aquatic Chronic 3: H412; Skin Irrit. 2: H315; STOT SE 3: H336; -: EUH066; -: H229

Most important adverse effects: Repeated exposure may cause skin dryness or cracking. Extremely flammable aerosol.
Pressurised container: May burst if heated. Causes skin irritation. May cause drowsiness or dizziness. Harmful to aquatic life with long lasting effects.

2.2. Label elements

Label elements:

Hazard statements: EUH066: Repeated exposure may cause skin dryness or cracking.

H222: Extremely flammable aerosol.

H229: Pressurised container: May burst if heated

H315: Causes skin irritation.

H336: May cause drowsiness or dizziness.

H412: Harmful to aquatic life with long lasting effects.

Hazard pictograms: GHS02: Flame

GHS07: Exclamation mark

[cont...]

SAFETY DATA SHEET

Z30 SPRAY

Page: 2



Signal words: Danger

Precautionary statements: P410+412: Protect from sunlight. Do not expose to temperatures exceeding 50 °C.
P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211: Do not spray on an open flame or other ignition source.
P251: Do not pierce or burn, even after use.
P285: In case of inadequate ventilation wear respiratory protection.
P280: Wear protective gloves/protective clothing/eye protection/face protection.
P302+352: IF ON SKIN: Wash with plenty of water/.
P304+340: IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P332+313: If skin irritation occurs: Get medical advice/attention.
P264: Wash thoroughly after handling.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

HYDROCARBONS, C9-C11, N-ALKANES, ISOALKANES, CYCLICS, < 2% AROMATICS - REACH registered number(s): 01-2119463258-33

EINECS	CAS	PBT / WEL	CLP Classification	Percent
919-857-5	-	-	Flam. Liq. 3: H226; Asp. Tox. 1: H304; STOT SE 3: H336; -: EUH066	50-70%

HYDROTREATED LIGHT DISTILLATE (PETROLEUM)

265-149-8	64742-47-8	-	Flam. Liq. 3: H226; Skin Irrit. 2: H315; STOT SE 3: H335; Asp. Tox. 1: H304; Aquatic Chronic 2: H411; STOT SE 3: H336	10-30%
-----------	------------	---	---	--------

CARBON DIOXIDE AEROSOL PROPELLANT

204-696-9	124-38-9	Substance with a Community workplace exposure limit.	Press. Gas: H280	2-10%
-----------	----------	--	------------------	-------

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Do not induce vomiting. Consult a doctor.

[cont...]

SAFETY DATA SHEET

Z30 SPRAY

Page: 3

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat. May cause dizziness.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Drowsiness or mental confusion may occur.

Delayed / immediate effects: No data available.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: No data available.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Do not use water. Alcohol resistant foam. Carbon dioxide. Dry chemical powder. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: Highly flammable. In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. Eliminate all sources of ignition.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Do not use equipment in clean-up procedure which may produce sparks. Mix with sand or vermiculite. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

[cont...]

SAFETY DATA SHEET

Z30 SPRAY

Page: 4

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Ensure there is sufficient ventilation of the area. Do not handle in a confined space.
Smoking is forbidden.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep away from sources of ignition. Keep away from direct sunlight. Ensure lighting and electrical equipment are not a source of ignition.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
EU	5mg/m3	10mg/m3	-	-

Hazardous ingredients:

HYDROCARBONS, C9-C11, N-ALKANES, ISOALKANES, CYCLICS, < 2% AROMATICS

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	1200mg/m3, 197ppm	-	-	-

CARBON DIOXIDE AEROSOL PROPELLANT

UK	5000ppm 9150mg/m3	15000ppm 27400mg/m3	-	-
----	-------------------	---------------------	---	---

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area. Ensure lighting and electrical equipment are not a source of ignition. The floor of the storage room must be impermeable to prevent the escape of liquids.

Respiratory protection: Respiratory protection not normally required for normal use in well ventilated areas.
Respiratory protection not normally required. Respiratory protection should be used in enclosed spaces, with poor ventilation, for extended repeated use, or where exposure limits may be exceeded. Recommended filter types are A1P2 or A2P2.

Hand protection: Protective gloves.

Eye protection: Safety glasses with side-shields.

[cont...]

SAFETY DATA SHEET

Z30 SPRAY

Page: 5

Skin protection: Protective clothing.

Environmental: Refer to specific Member State legislation for requirements under Community environmental legislation.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Aerosol

Colour: Brown

Odour: Characteristic odour

Evaporation rate: Moderate

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Not miscible

Viscosity: Non-viscous

Boiling point/range°C: > 150

Flammability limits %: lower: 0.6

upper: 7.0

Flash point°C: 40

Autoflammability°C: >200

Vapour pressure: < 2

Relative density: 0.81

9.2. Other information

Other information: Not applicable.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: No data available.

10.4. Conditions to avoid

Conditions to avoid: Direct sunlight. Heat. Sources of ignition.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong reducing agents.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

Section 11: Toxicological information

11.1. Information on toxicological effects

[cont...]

SAFETY DATA SHEET

Z30 SPRAY

Page: 6

Hazardous ingredients:

HYDROCARBONS, C9-C11, N-ALKANES, ISOALKANES, CYCLICS, < 2% AROMATICS

DERMAL	RBT	LD50	> 5000	ppmV
ORAL	RAT	LD50	> 5000	mg/kg

Relevant hazards for product:

Hazard	Route	Basis
Skin corrosion/irritation	DRM	Hazardous: calculated
STOT-single exposure	-	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat. May cause dizziness.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Drowsiness or mental confusion may occur.

Delayed / immediate effects: No data available.

Other information: Not applicable.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Only slightly biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Highly volatile. Soluble in water.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: No data available.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: No data available.

Recovery operations: Not applicable.

[cont...]

SAFETY DATA SHEET

Z30 SPRAY

Page: 7

Waste code number: 16 05 05

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN1950

14.2. UN proper shipping name

Shipping name: AEROSOLS, FLAMMABLE

14.3. Transport hazard class(es)

Transport class: 2.1

14.4. Packing group

Packing group: n/a

14.5. Environmental hazards

Environmentally hazardous: No

Marine pollutant: No

14.6. Special precautions for user

Special precautions: No data available

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Transport in bulk: No data available.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

EC Directive 94/1/EC adapting some technicalities of Council Directive 75/324/EEC on the approximation of the laws of Member States relating to aerosol dispensers.

Compiled in accordance with REACH.

Phrases used in s.2 and s.3: EUH066: Repeated exposure may cause skin dryness or cracking.

H222: Extremely flammable aerosol.

[cont...]

SAFETY DATA SHEET

Z30 SPRAY

Page: 8

H226: Flammable liquid and vapour.

H229: Pressurised container: May burst if heated

H280: Contains gas under pressure; may explode if heated.

H304: May be fatal if swallowed and enters airways.

H315: Causes skin irritation.

H335: May cause respiratory irritation.

H336: May cause drowsiness or dizziness.

H411: Toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.