



Panel cutting I





C = 19,8 and D = 4,0 for solder pin data layout
C = 21,0 and D = 4,1 for SMD data layout

Panel cutting II




Interface	Panel Cutting
RJ 45 jack 0945 551 1100	I
RJ 45 jack 0945 551 1101	I
RJ 45 jack 0945 551 1102	I
Push Pull Power	II




Connector pitch on panel:
Axis X = 27 mm and Axis Y = 21 mm
Receptacle mating side according to
600076-3-106 IEC - variant 04


Mating references A and B
according to IEC 60603-7

(1) Screwing x2 M2.5 screws between 0.5N.m and 0.8N.m
screw according to DIN 912 and ISO 4762



1 mm tickness flat seal
before screwing



36306	08/12/10	AB		Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	Push pull RJ Industrial Thermoplastic IP67 Receptacle And flat Seal	Maßstab/ Scale 1,5:1
EC02645	08/12/10	AB	Detail.	12/jan/05	JFB			
EC01204	12/01/10	AB	Insp.					
35413	17/11/08	AB	Stand.					
35092	17/07/08	AB	HARTING EURL F-95972 Paris				TB 09 45 545 00 21	Blatt/ Page 1/1
33793	28/07/06	PK						
Mod.	Dat.	Name				Sub.		