

SNC-DH160

Network HD Mini Dome Camera — E series

SONY
make.believe

Outdoor IP66 Vandal-Resistant 720p HD Security Camera with IR Illuminators

- Excellent 720p HD picture quality, supporting H.264 at 30 fps
- 1.3 Megapixel (1280 x 1024) maximum resolution
- Three codecs (H.264, MPEG-4, JPEG) and dual streaming capability
- Exmor™ CMOS sensor incorporated to deliver high image quality and low noise
- Dynamic range better than 60 dB



HD **1.3M**
MEGAPIXEL

KEY FEATURES

- Built-in IR (Infrared) illuminators to assist capturing objects in the dark even under 0 lx, up to 82 feet (25 m) (50 IRE) away. Adaptive IR auto adjusts IR level for best picture.




OFF

ON

Actual images of one of Sony's HD cameras with IR illuminators.

- IP66-rated water-resistant and dust-tight feature for outdoor surveillance, or indoor where water ingress may pose an issue.
- IK10-rated impact-resistant feature to protect the camera from destructive behaviors.
- Easy Focus/Easy Zoom functions allow changing field of view and focus remotely.
- True Day/Night function to switch to Day or Night mode depending on the light level.
- Recording software (RealShot™ Manager Lite) is bundled to start recording and monitoring instantly.
- Stream Squared function allows simultaneous streaming of two 4:3 aspect ratio videos in user selectable SD resolutions. User can select the entire image or a portion of the image from the original field of view and resize to VGA resolution or lower for each stream. With this feature, the SNC-DH160 can replace two standard definition cameras installed in the same line of view.



- Intelligent Motion Detection that supports DEPA™ analytics.



- Analog monitor output (phono jack).
- Powered by PoE (Power over Ethernet) for simple installation.
- Equipped with a built-in heater for continued camera operation in cold weather.
- ONVIF™ (Open Network Video Interface Forum) software that ensures greater interoperability and more flexibility in building multiple-vendor systems.




SPECIFICATIONS

SNC-DH160	
Camera	
Image device	1/3 type progressive scan Exmor CMOS sensor
Minimum illumination	0.50lx (Color), 0 lx (BW) (IR ON) (F1.2/AGC 42dB/50IRE (IP))
Dynamic Range	Better than 60 dB
Number of effective pixels (H x V)	1.4 Megapixel (1329 x 1049)
Electronic shutter speed	1 s to 1/10000 s
Gain control	Auto
Exposure control	Auto, EV Compensation, Auto Slow Shutter
White balance mode	Auto (ATW, ATW-PRO), Preset, One-push WB, Manual
Lens type	Vari-focal lens
Zoom ratio	Optical 2.9X
Horizontal viewing angle	85.4 to 31.2 degrees
Focal length	f=3.1 to 8.9 mm
F-number	F1.2 (Wide), F2.1 (Tele)
Minimum object distance	300 mm
Powered focus	Yes (Easy Focus)
Powered zoom	Yes (Easy Zoom)
IR illuminators	Yes (Wave Length: 850nm [Typical], IR LED: 21 pcs)
IR working distance	82 feet (25 m) (60 IRE)
Camera Features	
Day/Night *1	Yes (True D/N)
Noise reduction	Yes
Image	
Codec image size (H x V)	1280 x 1024, 1280 x 960, 1280 x 800, 1280 x 720, 1024 x 768, 1024 x 576, 800 x 480, 768 x 576, 720 x 576, 720 x 480, 704 x 576, 640 x 480, 640 x 368, 384 x 288, 320 x 240, 320 x 192 (H.264, MPEG-4, JPEG)
Video compression format	H.264, MPEG-4, JPEG
Codec streaming capability	Dual streaming
Maximum frame rate	H.264: 20fps (1280 x 1024) / 30 fps (1280 x 720) MPEG-4: 25fps (1280 x 1024) / 30 fps (1280 x 720) JPEG: 30fps (1280 x 1024) / 30 fps (1280 x 720)
Scene Analytics	
Intelligent motion detection	Yes
Network	
Protocols	IPv4, IPv6, TCP, UDP, ARP, ICMP, IGMP, HTTP, HTTPS, FTP (client only), SMTP, DHCP, DNS, NTP, RTP/RTCP, RTSP, SNMP (MIB-2)
ONVIF software	Yes
Number of clients	5
Authentication	IEEE802.1X
Analog Monitor Output	
Signal system	NTSC
Interface	
Ethernet	10BASE-T / 100BASE-TX (RJ-45)
Analog monitor output	Phono jack x 1
Sensor input	x 1, make contact, break contact
Alarm output	x 1, 24V AC/DC, 1A (Mechanical relay outputs electrically isolated from the camera)
General	
Weight	2 lb 15 oz (1320 g)
Dimensions (ø x H)	ø 6 5/8 x 4 3/4 inches (166 x 119 mm)
Power requirements	PoE
Power consumption	12.9 W max
Starting temperature	-4°F to +122°F (-20°C to +50°C)
Working temperature	-22°F to +122°F (-30°C to +50°C)
Storage temperature	-4°F to +140°F (-20°C to +60°C)
Ingress protection	IP66
Vandal resistant	IK10
Safety regulation	UL2044, FCC 15B Class A, IC Class A, IEC60950-1, EN55022(A)+EN55024+EN50130-4, VCCI Class A, C-Tick Class A
System Requirements	
Operating system	Microsoft Windows XP™, Windows Vista™ (32bit), Windows® 7 (32bit)
Processor	Intel Core2 Duo 2 GHz or higher
Memory	1 GB or more
Web browser	Microsoft Internet Explorer® Ver. 6.0, Ver. 7.0, Ver. 8.0, Ver. 9.0 Firefox® Ver. 3.5 (Plug-in free viewer only) Safari® Ver. 4.0 (Plug-in free viewer only) Google® Chrome Ver. 4.0 (Plug-in free viewer only)
Supplied Accessories	
CD-ROM (User's Guides, SNC Toolbox), Installation Manual, Bracket, Template, Wire rope, Camera unit mounting screws (4), Shoulder screw M4, VO cable, LAN cable, B&P Warranty Booklet	

*1 Removable IR Cut Filter.


*The SNC-DH160 includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (<http://www.openssl.org/>).

SYSTEM CONFIGURATIONS



DIMENSIONS

Unit: inches (mm)



Optional Accessory	
Model	
UNI-MDB3	GOOSENECK WALL Mount (includes Pendant Cap)
UNI-WMB4	GOOSENECK WALL Mount (without pendant cap)
UNI-MDPDH180	PENDANT CAP ONLY
UNI-WMBB1	CONDUIT BOX
UNI-CMA1	CORNER ADAPTER
UNI-PMA1	POLE ADAPTER
YT-ICB45	RECESSED BRACKET - Flush mount

© 2013 Sony Electronics Inc. All rights reserved.
 Reproduction in whole or in part without written permission is prohibited.
 Features and specifications are as subject to change without notice.
 Sony, Sony make.believe, IPELA, DEPA, Exmor, ONVIF and their respective logos are trademarks of Sony.
 Windows, XP and Vista are trademarks of Microsoft Corporation.
 All other trademarks are the property of their respective owners.