

2x2 HDMI over Cat5 / Cat6 Matrix Splitter Switch, Transmitter for Video and Audio, 1920x1200 1080p at 60Hz

MODEL NUMBER: **B126-2X2**



Highlights

- Extend HDMI up to 175ft (1080i)
- Switch input sources via Push-button, Remote, or RS232 serial
- HDCP compatible
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- B126-2X2 Transmitter Unit
- External Power Supply (Input: 100-240V, 50/60Hz, 0.5A Output B126-2X2: 5V, 2A
- 3.5 mm to DB9 Adapter Cable (serial)
- Mounting Hardware
- Remote Control
- Owner's Manual

Description

Tripp Lite B126-2X2 allows two HDMI video sources (DVR, Cable box, etc) to be shared among multiple monitors, over ordinary Cat5e/Cat6 cable. When used with Tripp Lite [Active HDMI receivers](#), can extend a 1080P signal up to 125ft, and 1080i up to 175ft. Allows any Input to be routed to any Output; or the same Input to be routed to multiple outputs. Two monitors can be supported with the basic switch...further expand the range and number of monitors by adding B126-110 remote repeater units. Switch is HDCP compliant, and is Plug-and-Play...no software or drivers required. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Share multiple HDMI sources between multiple monitors
- Allows any input to be routed to any output; or the same input to be routed to multiple outputs
- Transmits the signal over one Cat5e/6 cable to a remote monitor up to 175 ft. away
- A B126-Series remote receiver is needed at each monitor
- For longer distances: Use a B126-1A0 or B126-1A0-WP-1 active remote receiver to extend a 1080p @ 60Hz signal up to 125 ft. from the transmitter (or a 1080i @ 60Hz signal up to 175 ft. from the transmitter)
- For shorter distances: Use a B126-1P0 or B126-1P0-WP-1 passive remote receiver to extend a 1080p @ 60Hz signal up to 50 ft. from the transmitter (or a 1080i @ 60Hz signal up to 75 ft. from the transmitter)
- Use 24AWG, Solid Wire Cat5e/6 cable, such as Tripp Lite's N202-Series, to achieve maximum distance and resolution
- Further expand the range and number of monitors by adding B126-110 remote repeater units
- Add up to three repeaters on each channel of the matrix switch, for a total of 4 displays per channel (An active remote receiver should be the last unit in a channel)
- A 1080p @ 60Hz signal can be extended up to 125 ft. for each repeater added into a channel (or up to 175 ft. for a 1080i @60Hz signal)
- Switch between inputs via pushbuttons, remote control, or RS232 serial
- HDCP-compatible
- Mounting hardware included
- Plug-and-play; no software or drivers required



- Compatible with all operating systems
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

General Info	
RoHS	Y
OVERVIEW	
Chromebook Compatible	Yes
Display Style	Extender
Model Type	HDMI
Cable Types	CAT5/CAT5E
PHYSICAL	
Unit Dimensions (hwd / in.)	1.20 x 5.0 x 3.90
Included Mounting Accessories	Yes
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	0 to 40 C (32 to 104 F)
Storage Temperature Range	-20 to 60 C (-4 to 140 F)
Relative Humidity	20 to 90%
CONNECTIONS	
Connector A	HDMI (FEMALE) (X2)
Connector B	RJ45 (FEMALE) (X2)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.