

## Internet Office 120V 350VA 180W Standby UPS, Ultra-Compact Desktop, 6 Outlets, DB9 Serial port

MODEL NUMBER: **INTERNET350SER**



### Highlights

- 350VA ultra-compact 120V standby UPS
- Maintains AC output during power failures
- 3 UPS battery supported outlets, 3 surge-only outlets
- DB9 serial port, TEL/DSL protection
- NEMA 5-15P input plug and 6 NEMA 5-15R outlets

### Package Includes

- INTERNET350SER UPS system
- DB9 Serial Cable
- Instruction manual

### Description

Ultra-compact standby UPS with built-in DB9 serial monitoring port protects PCs, network workstations, and other systems reliant upon a basic communications interface for UPS monitoring and unattended system shutdown. Maintains AC output during blackouts and brownouts starting at 99V. Includes DB9 monitoring port with cabling, TEL/DSL line surge suppression, surge only outlets and LED indicators. PowerAlert software available free via download.

### Features

- INTERNET350SER standby UPS offers protection from blackouts, brownouts and surges on both AC and dialup modem lines
- Provides seamless battery derived AC output during blackouts and severe brownouts so that connected equipment can be shut down without data loss
- Built-in DB9 interface port with basic communication monitoring enables automatic system shutdown if power fails while the system runs unattended
- PowerAlert software available via free download from <http://www.tripplite.com>, DB9 cable included
- 3 battery supported outlets protect computer, monitor and one vital system peripheral, plus 3 additional surge suppression-only outlets for printers and other system accessories not requiring battery support
- Attractive stealth black UPS color scheme
- Built-in single line phone jacks with line splitter protects peripherals with a standard dialup phone line connection
- Built-in audible alarm and front panel LEDs offer continuous status information regarding line and battery power operation
- 350VA /180 watt power handling ability supports entry-level PC systems for several minutes during power fail conditions
- Includes attached 6 ft. AC power cord with space saving right-angle plug, on/off power switch
- Compatible with 120V/60 Hz applications in USA, Canada, Mexico and other countries
- Optional PDUB15 bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment
- \$100,000 Ultimate Lifetime Insurance (USA, Puerto Rico, & Canada only)

## Specifications

### General Info



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

RoHS	Y
<b>OUTPUT</b>	
Output Volt Amp Capacity (VA)	350
Output Watt Capacity (Watts)	180
Nominal Output Voltage(s) Supported	115V; 120V
Frequency Compatibility	60 Hz
Output Voltage Regulation (Battery Mode)	115V (+/- 5%)
Output Receptacles	(6) 5-15R
UPS Output Receptacles (Surge Suppression Only)	3 UPS outlets, 3 surge-only outlets
Hot-Swap PDU options	PDUB15 (2U / 8 5-15R outlets)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
<b>INPUT</b>	
Rated input current (Maximum Load)	12A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase
<b>BATTERY</b>	
Half Load Runtime (min.)	10 min. (90w)
DC System Voltage (VDC)	12
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Combination switch controls on/off power status and self-test operation
Audible Alarm	Audible alarm indicates power-failure and overload status
LED Indicators	2 LEDs indicate power status and overload/check battery status
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	510



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

UPS AC Suppression Response Time	Instantaneous
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out)
EMI / RFI AC Noise Suppression	Yes
<b>PHYSICAL</b>	
Installation Form Factors Supported with Included Accessories	Tower; Ultra-compact desktop
Primary Form Factor	Desktop
UPS Power Module Dimensions (hwd, in.)	3 x 10.5 x 5
UPS Power Module Dimensions (hwd, cm)	7.6 x 26.7 x 12.7
UPS Power Module Weight (lbs.)	7.7
UPS Power Module Weight (kg)	3.5
UPS Shipping Dimensions (hwd / in.)	4.5 x 12.5 x 7.8
UPS Shipping Dimensions (hwd / cm)	11.4 x 31.8 x 19.7
Shipping Weight (lbs.)	10
Shipping Weight (kg)	4.5
UPS Housing Material	ABS
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	39.1
Battery Mode BTU / Hr. (Full Load)	53.2
AC Mode Efficiency Rating (100% Load)	94%
<b>COMMUNICATIONS</b>	
Communications Interface	DB9 Serial
PowerAlert Software	Free download from <a href="http://www.tripplite.com">www.tripplite.com</a>
Communications Cable	DB9 interface cable included
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	99



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

High Voltage Transfer to Battery Power (Setpoint)	139
<b>SPECIAL FEATURES</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
<b>CERTIFICATIONS</b>	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI)
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (Latin America)	3-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 <a href="#">Ultimate Lifetime Insurance</a>

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.