




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:


1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
3. PART NUMBERS: SEE SHEET 2 FOR ALL PART NUMBERS.
4. CASSETTE WIRING COMPLIES WITH ANSI/TIA-568-C.0 SEE ANSI/TIA-568-C.0 FOR POLARITY DETAILS AND AN EXAMPLE OF A BASIC LINK.
5. CASSETTE WEIGHT: 3oz (85g)
6. SEE TABLE ON SHEET 2 FOR LIST OF PART NUMBERS.



											TITLE HD FLEX 12 FIBER LC- MPO CASSETTE			
											CUSTOMER DRAWING			
											ITEM REVISION NAME 12F187HA/00			
											DATASET FILE NAME 12F187HA_DC/00B			
											UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °		MATERIAL:	
00	01-22-15	SAT	JESA	RAR	RELEASED TO PRODUCTION					12F187HA-DC	 THIRD ANGLE PROJECTION		DRAWING NUMBER: 12F187HA-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION		ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 2		SIZE A
								SAT	01-22-15	JESA	NONE			

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

CASSETTE PART NUMBER	DESCRIPTION
FHCX0-12-10AS	12 FIBER LC - OM3 OPTIMIZED LOSS, POLARITY INDICATOR METHOD AS
FHCZ0-12-10AS	12 FIBER LC - OM4 OPTIMIZED LOSS, POLARITY INDICATOR METHOD AS
FHCX0-12-10AF	12 FIBER LC - OM3 OPTIMIZED LOSS, POLARITY INDICATOR METHOD AF
FHCZ0-12-10AF	12 FIBER LC - OM4 OPTIMIZED LOSS, POLARITY INDICATOR METHOD AF
FHCX0-12-10BN	12 FIBER LC - OM3 OPTIMIZED LOSS, POLARITY INDICATOR METHOD B
FHCZ0-12-10BN	12 FIBER LC - OM4 OPTIMIZED LOSS, POLARITY INDICATOR METHOD B
FHCZA-12-10AS	12 FIBER LC - OM4 ULTRA LOW LOSS, POLARITY INDICATOR METHOD AS
FHCZA-12-10AF	12 FIBER LC - OM4 ULTRA LOW LOSS, POLARITY INDICATOR METHOD AF
FHCZA-12-10BN	12 FIBER LC - OM4 ULTRA LOW LOSS, POLARITY INDICATOR METHOD B
FHC9N-12-10AS	12 FIBER LC - OS2 STANDARD LOSS, POLARITY INDICATOR METHOD AS
FHC9N-12-10AF	12 FIBER LC - OS2 STANDARD LOSS, POLARITY INDICATOR METHOD AF
FHC9N-12-10BN	12 FIBER LC - OS2 STANDARD LOSS, POLARITY INDICATOR METHOD B

						TITLE		HD FLEX 12 FIBER LC- MPO CASSETTE	
								CUSTOMER DRAWING	
						ITEM REVISION NAME		12F187HA/00	
						DATASET FILE NAME		12F187HA_DC/00B	
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)			
						.x ± .1 [2.54] .xxx ± .005 [.127]			
						.xx ± .01 [.25] ANGLES ± 5 °			
00 01-22-15 SAT JESA RAR RELEASED TO PRODUCTION						12F187HA-DC			
								THIRD ANGLE PROJECTION	
								DRAWING NUMBER: 12F187HA-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY SAT	DATE 01-22-15	CHK JESA
							SCALE NONE		SIZE A