



AL400ULB

Overview

AL400ULB power supply/charger converts a 28VAC input into a single 12VDC or 24VDC Class 2 Rated power limited output.

Specifications

Input:

- Input 28VAC, 100VA.

Output:

- 12VDC or 24VDC selectable output.
- 12VDC @ 4 amp or 24VDC @ 3 amp supply current.
- Class 2 Rated power limited output.
- Filtered and electronically regulated output.
- Short circuit and thermal overload protection.

Battery Backup:

- Built-in charger for sealed lead acid or gel type batteries.
- Automatic switch over to stand-by battery when AC fails.
- Maximum charge current 1.2 amp.

Supervision:

- AC fail supervision (form “C” contacts).
- Low battery supervision (form “C” contacts).

Visual Indicators:

- AC input and DC output LED indicators.

Electrical:

- Operating temperature: 0° C to 49° C ambient.
- 24.57 or 36.85 BTU/Hr.
- System AC input VA requirement: 166.75VA.

Mechanical:

- Board Dimensions (L x W x H approx.): 4.0” (101.6mm) x 7.0” (177.8mm) x 1.75” (51.05mm)
- Product weight (approx.): 1.05 lbs. (0.48 kg).
- Shipping weight (approx.): 1.25 lbs. (0.57 kg).

Agency Approvals



UL Recognized component for Access Control System Units (UL 294),
Standard for Power Supplies for Use with Burglar-Alarm Systems (UL 603),
Standard for Safety for Fire Protective Signaling Systems (UL 1481).

Board Dimensions (L x W x H) (approximate):

4.0” (101.6mm) x 7.0” (177.8mm) x 1.75” (51.05mm)

