2015/07/06 **MAXIMUS MPX**

MAXIMUS MPX

EX-PROOF PTZ DAY/NIGHT CAMERA















Electropolished AISI 316L stainless steel explosion proof PTZ camera unit

34" NPT threaded hole for use of cable glands or conduit

Variable speed: 0.1°-100°/s Pan and Tilt

Extremely easy electrical connections directly into the unit, thanks to the explosion-proof inspection box

Day/Night camera:

- True Progressive Scan
- High resolution: up to 550 TVLines
- Advanced image stabilizer (Stable Zoom Mode)
- Day/Night (Auto ICR: automatic removal of IR filter)

Up to 2 simultaneous video streams

Position accuracy: 0.02°

Integrated wiper



IP based control, H.264/AVC and JPEG, 25fps, Full D1 (compatible with ONVIF protocol, Profile S)

Prewired certified versions with unarmored cable/barrier cable gland (except for UL versions)

DESCRIPTION

The MAXIMUS ex-proof PTZ cameras ensure excellent performance for monitoring critical processes in areas with risk of explosion, such as refineries, gas pipelines, oil tankers, offshore platforms, industrial processes, chemical industries, etc. The area is always monitored, thanks to the speed and detection accuracy of the

Made of AISI316L stainless steel, which is excellently resistant to UV rays, salt mist and air pollution.

All models are available in analog or IP version.

The flexible operator control of pan/tilt/zoom functions allows the video transmission over the local area network (LAN) or over the Internet with the H.264/AVC compression, compatible with ONVIF Profile S.

The versions certified ATEX / IECEx / EAC / INMETRO / CNex are available with optional prewired unarmored cable/barrier cable gland (IEC/EN 60079-14). (Ref. ACCESSORIES: MPXCABL4, 4m, and MPXCABL10, 10m)



MPX



CABLE INPUT















TECHNICAL DATA

GENERAL

AISI 316L stainless steel construction

Passivated and electropolished external surfaces

Ouick configuration and setup

Dynamic positioning control system

MECHANICAL

13/4" NPT hole for cable glands

Zero backlash

Horizontal rotation: 360° continous

Vertical rotation: -90° to +90°

Horizontal speed (variable): from 0.1° to 100°/s

Tilt speed (variable): from 0.1° to 100°/s

Preset accuracy: 0.02°

12mm thick tempered glass window

Integrated wiper

Unit weight: 27kg (60lb)

ELECTRICAL

Power supply/Current consumption:

- 230Vac, 0.5A, 50/60Hz
- 24Vac, 5A, 50/60Hz
- 120Vac, 1A, 50/60Hz

Power consumption:

• 120W max

1 video output 75 Ohm 1Vpp (PAL/NTSC)

Functions: Autopan, Preset, Patrol, Tour (maximum 3), Autoflip

Maximum number of presets for protocol

- VIDEOTEC MACRO: 250
- ERNITEC: 250
- PANASONIC: 250
- PELCO D: 99
- AMERICAN DYNAMICS: 95

16-character string for zone and preset titling

I/O alarm card:

- 5 alarm inputs
- 2 relay outputs (1A 30Vac/60Vdc max)

COMMUNICATIONS

Configuration through OSD

2 half-duplex serial RS-485 interfaces or full-duplex RS-422

Firmware updating from console in remote mode (only VIDEOTEC MACRO and PELCO D protocols)

Up to 999 units, addressable by means of dip-switches

MPX, IP based control mode:

• Connection Ethernet port LAN 10/100T

Optical connector: ST (standard)

IP MPEG4 control mode:

- Compression MPEG-4/MJPEG
- Image resolution: Full D1 (720x576), VGA (640x480), CIF (352x288)
- Image frame rate max 25fps at Full D1
- Web Server

IP based control mode, H.264/AVC:

- Compression H.264/AVC and JPEG
- Two independent video streams
- Image resolution: from Full D1 (720x576 for PAL, 720x480 for NTSC) to 352x240 in 18 steps
- Web Server
- Compatible with ONVIF protocol, Profile S

PROTOCOLS

Serial communication protocol: AMERICAN DYNAMICS, ERNITEC, PANASONIC, PELCO D, VIDEOTEC MACRO

ENVIRONMENT

Indoor/Outdoor

Operating temperature: -40°C (-40°F)/+60°C (140°F)

Surge immunity: up to 2kV line to line, up to 4kV line to earth (Class 4)

CERTIFICATIONS

ATEX (EN 60079-0: 2012, EN 60079-1: 2007, EN 60079-31: 2009):

- II 2 G Ex d IICT6 T
 -40°C to +60°C Gb
- II 2 D Ex tb IIIC T85°C T
 -40°C to +60°C Db

IP66

IECEx (IEC 60079-0: 2011, IEC 60079-1: 2007, IEC 60079-31: 2008):

Ex d IICT6T -40°C to +60°C Gb

Ex tb IIIC T85°C T₂ -40°C to +60°C Db

IP66

EAC EX:

Ex d IIC T6 Gb X

Ex tb IIIC T85 Db X

CNEx (IP versions only with encoder MPEG4 - MPX...X000A):

Ex d IIC T6 Gb Tamb-40~60°C

DIP A21 TA T6 Tamb-40~60°C

INMETRO:

Ex d IIC T6 Gb Ta -40°C a/to +60°C

Ex tb IIIC T85°C Db Ta -40°C a/to +60°C

IP66

cULus Listed, TYPE 4X

UL listed for USA (only for 24Vac version):

Class I, Zone 1, AEx d IIC T6

Zone 21, AEx tb IIIC T85°C

UL listed for Canada (only for 24Vac version):

Class I, Zone 1, Ex d IIC T6 Gb

Class II, Groups E, F and G

2015/07/06 MAXIMUS MPX

BRACKETS AND A	DAPTORS
MPXWBA	AISI 316L stainless steel wall bracket
MPXCW	AISI 316L stainless steel corner adapter module
MPXCOL	AISI 316L stainless steel pole adapter module
MPXWBTA	AISI 316L stainless steel parapet or ceiling mounting bracket
ACCESSORIES	
WASEX2T4AT	Tank 10I with integrated manual pump controlled by ATEX certified solenoid valve, delivery head up to 20m (66ft) max, IN 24Vac/Vdc
WASEX2T4GOR	Tank 10I with integrated manual pump controlled by EAC certified solenoid valve, delivery head up to 20m (66ft) max, IN 24Vac/Vdc
WASEX2T4IN	Tank 10l with integrated manual pump controlled by INMETRO certified solenoid valve, delivery head up to 20m (66ft) max, IN 24Vac/Vdc

OCTEX3/4C	Cable gland with gasket EX 3/4" NPT, unarmoured cable IECEX-ATEX EAC					
OCTEXA3/4C	Cable gland with gasket EX 3/4" NPT, armoured cable IECEX-ATEX-EAC					
OCTEXB3/4C	Barrier cable gland 3/4" NPT, unarmoured cable IECEX-ATEXEAC					
OCTEXBA3/4C	Barrier cable gland 3/4" NPT, armoured cable IECEX-ATEX-EAC					
OCTEX3/4	Cable gland with gasket EX 3/4" NPT, unarmoured cable ATEX					
OCTEXA3/4	Cable gland with gasket EX 3/4" NPT, armoured cable ATEX					
MPXCABL4	Cabling for MPX/MPXT, 4m (157.5in) (unarmoured cable and barrier cable gland): 2 ethernet cables, 3 power supply wires, 2 coaxial video cables, 15 wires for relays alarms and telemetry					
MPXCABL10	Cabling for MPX/MPXT, 10m (394in) (unarmoured cable and barrier cable gland): 2 ethernet cables, 3 power supply wires, 2 coaxial video cables, 15 wires for relays alarms and telemetry					
PACKAGE						
Model Number	Weight Dimensions (WxHxL) Master carton					
MPX1QVW000A	30.4kg (67lb) 54x31x49cm (21x12x19in) -					

MAXIM	MAXIMUS MPX - CONFIGURATION OPTIONS						
	Voltage	Day/Night camera				Video Output	
МРХ	1 230Vac	P Day/Night camera 36x optical zoom lens, PAL	V With alarm board	W With wiper	0	Analog control	00A
	2 24Vac	Q Day/Night camera 28x optical zoom lens, PAL				X IP MPEG4 control ¹	
	3 120Vac	N Day/Night camera 36x optical zoom lens, NTSC				Z IP H.264/AVC, Protocol ONVIF Profile S	
		M Day/Night camera 28x optical zoom lens, NTSC					

¹ the CNex IP versions only with encoder MPEG4 - MPX...X000A

3/4" NPT CABLE GLA	ND SELECTION LAYOUT						
Zone, Gas	Cable gland type	Certification	Operating temperature	Cable	Cable glands part code	Diameter of the external cable	Under armor cable diameter
IIC, Zone 1 or Zone 2 IIB or IIA, Zone 1	Barrier	IECEX/ATEX/EAC	From -60°C (140°F) a +80°C (+176°F)	Not armored	OCTEXB3/4C	From 13mm (0.5in) a 20.2mm (0.8in)	-
				Armored	OCTEXBA3/4C	From 16.9mm (0.7in) a 26mm (1in)	_
IIB or IIA, Zone 2	With gasket	IECEX/ATEX/EAC	From -60°C (140°F) a +100°C (212°F)	Not armored	OCTEX3/4C	From 13mm (0.5in) a 20.2mm (0.8in)	_
				Armored	OCTEXA3/4C	From 16.9mm (0.7in) a 26mm (1in)	From 11.1mm (0.4in) a 19.7mm (0.8in)
		ATEX	From -20°C (-4°F) a +80°C (+176°F)	Not armored	OCTEX3/4	From 14mm (0.6in) a 17mm (0.7in)	-
				Armored	OCTEXA3/4	From 18mm (0.7in) thick glass a 23mm (0.9in)	From 14mm (0.6in) a 17mm (0.7in)

	Day/Night 36x		Day/Night 28x High sensitivity			
	PAL	NTSC	PAL	NTSC		
Optical zoom	36x		28x			
Wide Dynamic Range (Fix/Auto)	✓		-			
True progressive SCAN	✓		_			
Digital image stabilisation	✓		✓			
White balance	Auto, ATW, Indoor, Outdoor (Fix/Auto), Sodium Vapor Lamp (Fix/Auto)		Auto, ATW, Indoor, Outdoor (Fix/Auto), Sodium Vapor Lamp (Fix/Auto)			
High horizontal resolution	Up to 550 TV Lines		Up to 550 TV Lines	Up to 550 TV Lines		
Day/Night (Auto ICR)	✓		1	✓		
Image Sensor	1/4" EXView HAD CCI	1/4" EXView HAD CCD				
Number of effective Pixels	~ 440000 pixel	~ 380000 pixel	~ 440000 pixel	~ 380000 pixel		
Min. Color illumination (IR-Cut Filter = OFF)	1.4Lux / 1/50s 0.1 Lux / 1/3s	1.4Lux / 1/60s 0.1 Lux / 1/4s	0.25Lux / 1/50s 0.16 Lux / 1/3s	0.25Lux / 1/60s 0.16 Lux / 1/4s		
Min. B/W illumination	0.01 Lux / 1/3s	0.01 Lux / 1/4s	0.0015 Lux / 1/3s	0.0015 Lux / 1/4s		
"Shutter Time" automatic increase to improve the night surveillance	✓		1			
S/N ratio	Greater than 50dB	Greater than 50dB		Greater than 50dB		
AE control		Automatic, Shutter priority, Diaphragm priority, Brightness priority and Manual		Automatic, Shutter priority, Diaphragm priority, Brightness priority and Manual		
Back light compensation	On/Off	On/Off		On/Off		
Spherical masking (3D) of Privacy zones with automatic upgrade	✓	✓		✓		
Privacy Zone Masking	On/Off (24 positions)	On/Off (24 positions)		On/Off (24 positions)		
Maximum number of masking blocks to be displayed	8	8		8		
Resolution of masking blocks	160x120 HxV		160x120 HxV			
Masking	Up to 15 different masking types: 14 colour types or mosaic		Up to 15 different masking types: 14 colour types or mosaic			
Focusing system	Auto (Sensitivity: Normal, Low), Trigger PTZ, Manual		Auto (Sensitivity: Normal, Low), Trigger PTZ, Manual			
"Smart" lens control	Automatic Lens Reset		Automatic Lens Reset			
High Zoom and Wide Horizontal Field of View Capability	1		✓			
Optical zoom	36x, f=3.4 (wide) to 122.4mm (tele) / F1.6 to F4.5		28x, f=3.5 (wide) to 98mm (tele) / F1.35 to F3.7			
Digital Zoom	12x (432x with optical zoom)		12x (336x with optical zoom)			
Angle of view (A)	57.8 degrees (wide) to 1.7 degrees (tele)		55.8 degrees (wide) to 2.1 degrees (tele)			
Minimum object distance	320mm (12.6in) (wide) to 1500mm (59.1in) (tele)		10mm (0.4in) (wide) to 1500mm (59.1in) (tele)			
Electronic Iris Speed	1/1 ÷ 1/10000s 1/1 ÷ 1/10000s					



2015/07/06 MAXIMUS MPX

TECHNICAL DRAWINGS

Sizes in millimeters.







