



AL642ULADA

### **Overview**

AL642ULADA are extremely cost effective voltage regulated remote NAC Power Extenders. They may be connected to any 24 volt Fire Alarm Control Panel (FACP). Primary applications include Notification Appliance Circuit (NAC) expansion (supports ADA requirements) and providing auxiliary power to support system accessories.

### **Specifications**

#### **Agency Listings:**

- UL Listed Control Units and Accessories for Fire Systems (UL 864).
- MEA - NYC Department of Buildings Approved.
- CSFM - California State Fire Marshal Approved.
- FM - Factory Mutual Approved.
- NFPA 72 Compliant.

#### **Input:**

- Power input 120VAC 60 Hz, 4 amp.
- Two (2) Class A, Style Z or two (2) Class B, Style W, X, Y FACP inputs.
- Two (2) NC dry contact trigger inputs.

#### **Output:**

- Class 2 Rated power limited outputs.
- 24VDC voltage regulated power limited outputs.
- 6.5 amp max total alarm current.
- 2.5A max current per output.
- Two auxiliary outputs rated at 1 amp each (1 amp continuous, 1 amp AC disconnect).
- Two (2) outputs may be paralleled for more power on an indicating circuit.
- Programmable supervised indicating circuit outputs: Four (4) Class B, Style W, X, Y or Four (4) Class A, Style Z or Two (2) Class A, Style Z and Two (2) Class B, Style W, X, Y.
- Thermal and short circuit protection with auto reset.

#### **Battery Backup:**

- Charging voltage is 26.2-26.4VDC.
- Built-in charger for sealed lead acid or gel type batteries.
- Automatic switchover to stand-by battery when AC fails.
- Zero voltage drop when switching over to battery backup.

#### **Supervision:**

- AC fail supervision (form "C" contact, 1 amp/28VDC). Factory set for 30 seconds with optional 2.5 to 3 hour delay setting (field selectable).
- Instant local AC trouble reporting relay (form "C" contact, 1 amp / 28VDC).
- Battery presence and low battery supervision (form "C" contact, 1 amp / 28VDC).

#### **Visual Indicators:**

- Input and output status LED indicators.

#### **Special Features:**

- 2-wire horn/strobe Sync mode allows audible notification appliances (horns) to be silenced while visual notification appliances (strobes) continue to operate.
- Sync protocols include Potter/Amseco, Faraday, Gentex®, System Sensor®, and CooperWheelock®.
- Temporal Code 3, Steady Mode, Input to Output Follower Mode (maintains synchronization of notification appliances circuit).
- Compatible with 24VDC fire panels.
- Output loop supervision directed to input 1 or input 2.
- Signal Circuit Trouble Memory - facilitates quick identification of an intermittent/fault (short circuit, open or ground) which has previously occurred on one or more signaling circuit outputs. LEDs indicate/identify which output the fault has occurred.
- Common trouble input and output for external trouble signals tie-in.
- Ground fault detection.
- Unit includes power supply, logic board enclosure, cam lock, and battery leads.

#### **Mechanical:**

- Enclosure Dimensions (H x W x D approx.): 18" x 14.5" x 4.625" (457.2mm x 368.3mm x 117.48mm)
- Product weight (approx.): 15.8 lbs. (7.17 kg).
- Shipping weight (approx.): 18.05 lbs. (8.19 kg).

### **Agency Approvals**



UL Listed Control Units and Accessories for Fire Alarm Systems (UL 864),



NYC Department of Buildings Approved.



California State Fire Marshal Approved.



Factory Mutual Approved.

***Enclosure Dimensions (H x W x D approximate):***  
**18" x 14.5" x 4.625" (457.2mm x 368.3mm x 117.48mm)**

