



Maximal5D

Overview

Maximal5D distributes and switches power to access control systems and accessories. Unit converts a 115VAC 60Hz input into sixteen (16) independently controlled 12VDC Class 2 Rated PTC protected power-limited outputs. The outputs are activated by an open collector sink or normally open (NO) dry trigger input from an Access Control System, Keypad, Push Button, REX PIR, etc. Units will route power to a variety of access control hardware devices including: Mag Locks, Electric Strikes, Magnetic Door Holders, etc. Outputs will operate in both Fail-Safe and/or Fail-Secure modes. The FACP Interface enables Emergency Egress, Alarm Monitoring, or may be used to trigger other auxiliary devices. The fire alarm disconnect feature is individually selectable for any or all of the sixteen (16) outputs. All interconnecting equipment must be UL Listed.

Specifications

Input:

- 115VAC 60Hz, 1.9 amp input.
- Power supply input options:
 - a) Two (2) common power input for either ACM8CB and lock power (factory installed).
 - b) Two (2) isolated power inputs (external power supply is required), (current is determined by the power supply connected, not to exceed a maximum of 10 amp total).
- Sixteen (16) Access Control System trigger inputs. Input options:
 - a) Sixteen (16) normally open (NO) inputs.
 - b) Sixteen (16) open collector inputs.
 - c) Any combination of the above.

Output:

- 12VDC outputs.
- Maximum output current: 12VDC @ 9 amp.
- Class 2 Rated power limited outputs.
- Sixteen (16) independently controlled outputs can be Fail-Safe and/or Fail-Secure power outputs.
- Sixteen (16) auxiliary power outputs (unswitched) (outputs are rated 2 amp).
- Filtered and electronically regulated outputs (built-in power supply).
- Thermal and short circuit protection with auto reset.

Fuse Ratings:

- Power Supply input fuse rated @ 3.5 amp/250V.
- ACM8CB boards main fuse is rated at 10 amp.
- Output PTCs are rated @ 2.5 amp.

Features:

- Fire Alarm disconnect (latching or non-latching) is individually selectable for any or all of the sixteen (16) outputs.

Features (cont'd):

- Fire Alarm disconnect input options:
 - a) Normally open (NO) or normally closed (NC) dry contact input.
 - b) Polarity reversal input from FACP signaling circuit.
- Alarm output relay indicates that FACP input is triggered (form "C" contact rated @ 1 amp 28VDC).
- AC fail supervision (form "C" contact).
- Low battery and battery presence supervision (form "C" contact).

Battery Backup:

- Built-in charger for sealed lead acid or gel type batteries.
- Maximum charge current 0.7 amp.
- Automatic switch over to stand-by battery when AC fails.
- Zero voltage drop when unit switches over to battery backup (AC failure condition).

Visual Indicators:

- Red LEDs indicate outputs are triggered (relays energized).
- Green LED indicates FACP disconnect is triggered.
- AC input and DC output LED indicators.

Electrical:

- Operating temperature: 0° C to 49° C ambient.
- BTU/Hr.: 54.6 BTU/Hr.
- System AC input VA requirement: 218.5VA.

Mechanical:

- Enclosure Dimensions (H x W x D approx.): 26" x 19" x 6.25" (660.4mm x 482.6mm x 158.75mm)
- Enclosure accommodates up to four (4) 12AH batteries.
- Product weight (approx.): 42 lbs. (19.05 kg).
- Shipping weight (approx.): 46 lbs. (20.87 kg).

Agency Approvals



UL Listed for Access Control System Units
(UL 294).



CSFM
California State Fire Marshal Approved.

Enclosure Dimensions (H x W x D approximate): 26" x 19" x 6.25" (660.4mm x 482.6mm x 158.75mm)

