




On Line Catalog



BURNDY Catalog Number
UPC Number
Description
Status

YA342NFXB
781810039922
BELLED LUG-350FLEX-NEMA
Active

Web Use
BURNDY Product Line

Tongue Angle
Length (in)
Tongue Type
Barrell Style
Bolt Hole Size (in)
Barrel Type
Thickness
B Length (in)
Pad Width (in)
E - in
Strip Length

Dimensional
Straight
6.29
Standard
Belled
0.52
Long
0.23
2.48
1.55
1.75
2-9/16

Number of Holes

General
2
Copper Compression Lug, 2 Hole
w/o Inspection Window, 373.7
kcmil, 1/2" Stud, 1-3/4" Stud Hole
Spacing, Long Barrel, Belled End,
Tin Plated

Product Description

Aircraft Cable Size (Range)
Flex (Class H) Size - Range
Flex (Class I) Size - Range
Copper Solid Size (Range)
DLO Size (Range)
Navy Cable Size (Range)
Copper Stranded (Range)
Flex (Class G) Size - Range
Flex (Class M) Size - Range

Conductor(s)
N/A
373.7
373.7
N/A
373.7 (925/#24)
N/A
350 kcmil
373.7
373.7

Type of Plating
Bolt Hole Size
Color Code
Plated (Yes or No)
Index Number
Product Material

Physical
Tin
1/2
Blue
Y
19
Copper

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS

Approvals / Certifications
Y
Y
Compliant
N
N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

BURNDY Technical Servcies

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175

47, industrial Park Drive
Manchester NH03109

47, industrial Park Drive
Manchester NH03109

