

111-01459



Article Number: 111-01459

High Temp Cable Tie, 5.8" Long, 30lb Tensile Strength, PA46, Gray, 1000/pkg

RoHS

Download drawing

Download spec sheet

Base Data

Local Order Number	111-01459
Type	T30R
Color	Gray (GY)
Features and Benefits	• Cable ties made of PA46 material provide a greater resistance to high heat exposures than PA66 heat stabilized material. • Inside serrations allow for strong hold on cables and wire bundles. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
Product Description	HellermannTyton standard cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are availableto ensure consistent and safe installation.
Short Description	High Temp Cable Tie, 5.8" Long, 30lb Tensile Strength, PA46, Gray, 1000/pkg

Product Dimensions

Minimum Tensile Strength (Imperial)	30.0 lbs
Minimum Tensile Strength (Metric)	135.0 N
Length L (Imperial)	5.8 "
Length L (Metric)	148.0 mm
Fixation Method	None
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.14 "
Width W (Metric)	3.6 mm
Bundle Diameter Min. (Imperial)	0.06 "
Bundle Diameter Min. (Metric)	1.5 mm
Bundle Diameter Max. (Imperial)	1.4 "
Bundle Diameter Max. (Metric)	35.0 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	1000

Material and Specifications

Material	Polyamide 4.6 (PA46)
Material Shortcut	PA46
Flammability	UL94 V2
Operating Temperature	-40°F to +275°F (-40°C to +135°C)
ROHS Compliant	Yes
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	No