

T30R0UVM4



Article Number: 111-00439

Standard Cable Tie, 5.8" Long, 30lb Tensile Strength, PA66UV, Black, 1000/pkg

 RoHS

 Download spec sheet

Base Data

Local Order Number	T30R0UVM4
Type	T30R
Color	Black (BK)
Features and Benefits	• UV stabilized cable ties contain an inhibitor which prolongs the life of the tie in UV exposures . • Inside serrations allow for strong hold on cables and wire bundles. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
Product Description	HellermannTyton standard cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are availableto ensure consistent and safe installation.
Short Description	Standard Cable Tie, 5.8" Long, 30lb Tensile Strength, PA66UV, Black, 1000/pkg

Product Dimensions

Minimum Tensile Strength (Imperial)	30.0 lbs
Minimum Tensile Strength (Metric)	135.0 N
Length L (Imperial)	5.8 "
Length L (Metric)	148.0 mm
Fixation Method	None
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.14 "
Width W (Metric)	3.6 mm
Bundle Diameter Min. (Imperial)	0.06 "
Bundle Diameter Min. (Metric)	1.5 mm
Bundle Diameter Max. (Imperial)	1.4 "
Bundle Diameter Max. (Metric)	35.0 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	1000
Carton Quantity	5000

Material and Specifications

Material	Polyamide 6.6 UV-resistant (PA66UV)
Material Shortcut	PA66UV
US MILSPEC	MS3367-5-0
Flammability	UL94 HB
Halogenfree	Yes
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Compliant	Yes
Certification/Specification	SAE - AS33671 UL-ZODZ2.E64139 Cage Code 53421
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	No