



High Intensity SIP LED Strobe Light

Bright visual notification of telephone, safety, and security events. Effective and selectable flash patterns radiate light 360 x 180 degrees for visibility in all directions. Alerts employees in noisy locations and eliminates noise in quiet environments.

Eight efficient and powerful LEDs provide a range of visible effects. Aggressive flash patterns ensure effectiveness in large noisy industrial areas, while milder flash patterns are suitable for less urgent notification or offices.

Available lens covers in amber, blue, or red provide even more choice for distinguishing telephone and safety events from fire or other alarm systems.

SIP, multicast, and dry contact activation allows the 8128 Strobe Light to easily integrate with any unified communication server or security system. For large deployments, transmit and receive multicasting capabilities provide easy scalability over the IP network without multiple SIP extensions.

Adjustable.
Optional amber, blue and red
lens covers.



Flexible.

Wall or ceiling mountable.

Features

- PoE Endpoint
- SIP, multicast, or dry contact activated
- Selectable flash pattern, rate and intensity
- Optional amber, blue or red covers
- Wall or ceiling mountable
- Weather resistant

Benefits

- 16 flash patterns suitable for all applications
- OSHA or ADA compliance
- Distinguishable from fire alarm
- Higher efficiency and longer life than xenon strobe lights
- Notification in noisy or quiet environments
- Easily scales for large deployment using multicast

8128 SIP Strobe Light


ALGO

Specifications

Power Input	48 V PoE Class 0 (Maximum 12.95 W - Idle nominal 1 W)
Size	4.8" W x 4.8" H x 3.0" D (12.2cm W x 12.2cm H x 7.6cm D)
Optical	8 LEDs, 643 lumens, 198 Cd
Strobe Triggers	SIP extension ring, Subscribe/Notify, multicast, dry contact input
Relay Output	Max 30 V 50 mA
Relay Input	Max 1 kOhm
Flash Patterns	16 Selectable patterns
Programming	Web interface
Provisioning	TFTP, FTP, or HTTP
NAT	STUN, CRLF Keep Alive
Environmental	-4 to +122 deg F (-20 to +50° C); 10-95% RH non-condensing. Dry indoor location only unless wiring cavity protected from water ingress using supplied gaskets or other protective measures.
Compliance	EN60950:2001, IEEE 802.3-2008, RFC3261, RoHS, CE, FCC, CSA (USA & Canada)

Connections

- RJ45 Ethernet jack - PoE 802.3af
- Dry contact trigger - terminal block
- Dry contact output - terminal block



Flash Patterns

No	Description	Application		Intensity/Strobe		
		Wall	Ceiling	High	Med	Low
15	Classic strobe slow	✓	✓		✓	
14	Classic strobe medium	✓	✓		✓	
13	Classic strobe fast	✓	✓		✓	
12	Flashing	✓	✓		✓	
11	Side to side	✓			✓	
10	Pulse	✓	✓			✓
9	Steady bright	✓	✓			✓
8	Steady dim	✓	✓			✓
7	Rotating strobe	✓	✓	✓		
6	Multi-strobe slow bright	✓	✓	✓		
5	Multi-strobe slow dimmed	✓	✓		✓	
4	Multi-strobe fast bright	✓	✓	✓		
3	Multi-strobe fast dimmed	✓	✓		✓	
2	Multi-strobe dim holdover	✓	✓	✓		
1	Rotate slow		✓		✓	
0	Rotate fast		✓		✓	

What's Included in the Box

- 8128 Strobe unit with clear lens
- Mounting bracket
- Gaskets
- Colored lens cover (if color option ordered)
- User Guide

Order Codes

8128	SIP Strobe Light, clear lens included.
8128A	SIP Strobe Light, amber lens cover included.
8128B	SIP Strobe Light, blue lens cover included.
8128R	SIP Strobe Light, red lens cover included.
8128ABR	SIP Strobe Light, amber, red, and blue lens cover included.

DC8128BR-01 February 2014 © Algo Communication Products Ltd. All rights reserved. Algo® is a registered trademark of Algo Communication Products Ltd.
Note - Specifications are subject to change without notice. Some features may only be available in specific firmware or hardware releases.

www.algosolutions.com

Algo Communication Products Ltd., 4500 Beedie Street, Burnaby, BC Canada V5J 5L2
Sales: +1-604-454-3790; sales@algosolutions.com