

Sentry Smart CDU

Key Features

- > **Mid and High Density:**
Single-power input feed; 24 outlets per enclosure
- > **High Power Distribution:**
100-120V, 20A and 30A power input options
- > **Input Current Monitor:**
Precisely measure the aggregate current draw (in amps) on each branch circuit. On-site verification of the input current with the LED digital display. Remote verification via web browser or serial screen.
- > **IP Access & Security:** Web interface, SSL, SSH, Telnet, SNMP, FTP, SNTP, Syslog, LDAP, LDAPS, TACACS and RS-232 access
- > **Alerts:** Provide automated SNMP-based alarms or email alerts for power and environmental conditions
- > **Environmental Monitoring:** Each Smart CDU supports two external temperature & humidity probes and reports conditions through the user interface without the need for additional IP addresses
- > **Add an Expansion Module:** Daisy chain the Smart CDU Expansion Module (CS/CL) for power monitoring of separate power circuits from a single IP address


CS-24V

Mid and High Density Power Distribution

The Smart Cabinet Power Distribution Units (CDU) provide reliable power distribution combined with local and remote power monitoring and environmental monitoring via IP. Use the network interface to view power, temperature and humidity levels via Web browser, or receive SNMP-based alarms and email alerts when conditions exceed defined thresholds.

The Smart CDU family now has the capability to daisy chain units together. The Expansion CDU Module gives the ability to use one IP address across different power circuits.

Additional Benefits:



Fuse Retractors for Branch Circuit Protection

These tool-less retractors pull out for easy access and replacement of fuses. The Sentry CDU Family meets the UL 60950-1 requirement for branch circuit protection.

Attention! The Sentry CDU products meet the above criteria by providing overcurrent protection with UL-listed Bussman SC fuses for each branch circuit.



Input Current Monitoring

Exclusive Digital True RMS current monitoring is critical to preventing overloads in high-density computing environments. LED digital display on the CDU enclosure report the input current of the branch circuit.



Temperature and Humidity

The Smart CDU supports two external 10ft (3m) probes. Each of these probes measure both temperature and humidity. Receive SNMP-based alerts or email notifications when conditions exceed defined thresholds.



Linking for Smart CDU (Expansion Modules)

The Smart CDU family now has the capability to daisy chain units together. The Expansion Module provides the ability to link two power circuits under one IP address.



NEMA 5-20R

Model	Available Input Voltages	Amperage	Available Input Cord	Outlets	Dimensions** (L x W x D)
CS-24V1-C20M CL-24V1-C20M*	100-120V 50/60Hz	20A	IEC 60320/C20 Power Inlet	(24) NEMA 5-20R	69.0 x 1.75 x 2.25 in. (1753 x 44.4 x 57 mm)
CS-24V1-L30M CL-24V1-L30M*	100-120V 50/60Hz	30A	NEMA L5-30P Cordset, 10 ft (3m)	(24) NEMA 5-20R	69.0 x 1.75 x 2.25 in. (1753 x 44.4 x 57 mm)

* CL part numbers refer to the Expansion CDU

**Please note that the depths of these enclosures are 3.0" deep at the placement of the fuse retractors

Additional Features and Specifications

Agency Approvals

- > US & Canada (cTUVus mark) to UL 60950-1:2007 and CAN/CSA 22.2 No. 60950-1-07
- > FCC Class A, Part 15
- > EMC to EN 55022 Class A, EN 55024, CISPR 22 Class A

Communications and Security

- > 10/100 BaseT Ethernet
- > HTTP/HTTPS
- > SSLv3/TLSv1
- > SNMPv2/3
- > SSHv2
- > Telnet
- > LDAPv3
- > LDAPS
- > TACACS+
- > RADIUS
- > RS-232 (Serial)
- > IPv6

Power Cord Options (for units with C20 power inlets)

- > PTCORD-5 IEC 60320/C19 - 5-15P (15A Straight-Blade) 10 ft (3m)
- > PTCORD-6 IEC 60320/C19 - 5-20P (20A Straight-Blade) 10 ft (3m)
- > PTCORD-7 IEC 60320/C19 - L5-20P (20A Twist-Lock) 10 ft (3m)

Branch Circuit Protection

- > Compliant to UL 60950-1

Accessories

- > Optional Temperature & Humidity Probe
 - EMTH-1-1 Temperature & Humidity Probe, 10ft (3m)
- > Environmental Monitor
 - EMCU-1-1B allows up to (2) additional temperature & humidity probes, (1) water sensor, (4) dry contact closures, (1) analog-to-digital contact sensor. Includes (1) temperature/humidity probe with unit.
- > SPM (Sentry Power Manager):
 - Monitor and Manage multiple Sentry CDU's
 - Monitor and Manage all alarm conditions
 - Reporting and Trending
 - Group or Cluster outlets for reboot and power information
 - Optional Appliance or virtual version
 - SPM v5.1+ is VMware READY



VMware and VMware Ready is a registered trademark or trademark of VMware, Inc. in the United States and/or other jurisdictions



1U SPM Appliance

Expansion Module
Model Numbers
CL-24V1-C20M
CL-24V1-L30M



Server Technology

HEADQUARTERS - NORTH AMERICA

Server Technology, Inc.
1040 Sandhill Drive
Reno, NV 89521
United States
1.775.284.2000 Tel
1.775.284.2065 Fax
sales@servertech.com
www.servertech.com
www.servertechblog.com

Western Europe, Middle East and Africa

Fountain Court
2 Victoria Square
Victoria Street
St. Albans
AL1 3TF
United Kingdom
+44 (0) 1727 884676 Tel
+44 (0) 1727 220815 Fax
salesint@servertech.com

Central Europe, Eastern Europe and Russia

Niederlassung Deutschland
Server Technology LLC
42119 Wuppertal
Germany
Tel: + 49 202 693917 x 0
Fax: + 49 202 693917-10
salesint@servertech.com

APAC

37th Floor
Singapore Land Tower
50 Raffles Place
Singapore 048623
Phone: +65 9739.0396
Fax: +65 6234.4574
salesint@servertech.com