

# Sentry Smart CDU

## CS-4HD/HY with 3-Phase NEMA Locking Outlets

### Key Features

- > **High Density:** Single power input feed, 4 each NEMA L15-30R Outlets
- > **High Power Distribution:** 208V 3-Phase 50 and 60 amp single input feed options
- > **Input Current Monitor:** Precisely measure the aggregate current draw (in amps) on each phase. On-site verification of the input current with the LED digital display. Remote verification via browser or serial screen.
- > **IP Access & Security:** Web interface, SSL, SSH, Telnet, SNMP, FTP, SNMP, Syslog, LDAP, LDAPS, RADIUS, TACACS, RS-232 access
- > **Traps & Alerts:** Provide automated SNMP-based alarms and email alerts for power and environmental conditions
- > **Environmental Monitoring:** Each Smart CDU supports two temperature & humidity probes and reports conditions thru the Web interface
- > **Add an Expansion Module:** Connect the Smart Expansion CDU (CL) to a Master unit (CS) for power monitoring of separate power circuits from a single IP address



### High-Density Power Distribution

The Sentry CS-4HD/HY products provide a NEMA locking outlet solution for high density applications found in data center cabinets. Smart Cabinet Distribution Units (CDU) provide reliable 3-phase power distribution combined with local and remote power monitoring and environmental monitoring via IP. Use the network interface to view power, temperature, and humidity levels via Web browser, or receive SNMP-based alarms and email alerts when conditions exceed defined thresholds.

The Smart CDU family has the capability to daisy chain units together. The expansion CDU Module give the ability to use one IP address across different power circuits.


### Additional Benefits:



#### Branch Circuit Protection

The Sentry CDU Family meets the UL 60950-1 requirement for Branch Circuit Protections

- > UL-489 rated circuit breakers



#### Input Current Monitoring

Exclusive Digital True RMS current monitoring is critical to preventing overloads in high-density computing environments. LED digital display on the CDU enclosure report the input current of the branch circuit.



#### Temperature and Humidity

The Smart CDU supports two external probes. Each of these probes measure both temperature and humidity. Receive SNMP-based alert notifications when conditions exceed defined thresholds.



#### Linking (Expansion Modules)

The Smart CDU family has the capability to daisy chain units together. The Expansion Module provides the ability to link two power circuits under one IP address.

Model	Available Input Voltages	Amperage	Available Input Cord	Outlets	Dimensions (L x W x D)
CS-4HDX452B6 CL-4HDX452B6*	240V 3-Phase Delta, 50/60 Hz	60A	IEC 60309 Cordset, 10 ft (3m)	(4) NEMA L15-30R	3.50 x 17.00 x 10.00 in. (89 x 432 x 254mm)
CS-4HDV452B6 CL-4HDV452B6*	240V 3-Phase Delta, 50/60 Hz	50A	CS8365C Cordset, 10 ft (3m)	(4) NEMA L15-30R	3.50 x 17.00 x 10.00 in. (89 x 432 x 254mm)
CS-4HYY452B6 CL-4HYY452B6*	208V 3-Phase Wye, 50/60 Hz	60A	IEC 60309 Cordset, 10 ft (3m)	(4) NEMA L15-30R	3.50 x 17.00 x 10.00 in. (89 x 432 x 254mm)

\*CL refers to the Expansion Module

## Additional Features and Specifications

### Agency Approvals

- > US & Canada (cTUVus mark) to UL 60950-1:2003 and CAN/CSA 22.2 No. 60950-1-03
- > FCC Class A, Part 15
- > EMC to EN 55022 Class A, EN 55024, CISPR 22 Class A

### Communications and Security


- > 10/100 BaseT Ethernet
- > HTTP/HTTPS
- > SSLv3/TLSv1
- > SNMPv2
- > SSHv2
- > Telnet
- > LDAPv3
- > LDAPS
- > TACACS+
- > RADIUS
- > RS-232 (Serial)

### Branch Circuit Protection

- > Compliant to UL 60950-1

### Accessories

- > Optional Temperature & Humidity Probe
  - EMTH-1-1 Temperature & Humidity Probe, 10ft (3m)
- > Environmental Monitor
  - EMCU-1-1B allows up to (2) additional temperature & humidity probes, (1) water sensor, (4) dry contact closures, (1) analog-to-digital contact sensor. Includes (1) temperature/humidity probe with unit.
- > SPM (Sentry Power Manager) Appliance:
  - Monitor and Manage multiple Sentry CDU's
  - Monitor and Manage all alarm conditions
  - Reporting and Trending
  - Group or Cluster outlets for reboot and power information



Rear View: breakers, network, serial, linking and temperature/humidity inputs



## Server Technology

**HEADQUARTERS - NORTH AMERICA**  
 Server Technology, Inc.  
 1040 Sandhill Drive  
 Reno, NV 89521  
 United States  
 1.775.284.2000 Tel  
 1.775.284.2065 Fax  
[sales@servertech.com](mailto:sales@servertech.com)  
[www.servertech.com](http://www.servertech.com)  
[www.servertechblog.com](http://www.servertechblog.com)

**EMEA**  
 Server Technology Intl  
 Sienna Court  
 The Broadway  
 Maidenhead  
 Berkshire  
 SL6 1NJ  
 United Kingdom  
 +44 (0) 1628 509053 Tel  
 +44 (0) 1628 509100 Fax  
[salesint@servertech.com](mailto:salesint@servertech.com)

**APAC**  
 Server Technology Intl  
 37th Floor, Singapore Land Tower  
 50 Raffles Place  
 Singapore 048623  
 +65 (0) 6829 7008 Tel  
 +65 (0) 6234 4574 Fax  
[salesint@servertech.com](mailto:salesint@servertech.com)