

Performance you can trust

RTD[®] COMPOUND Hand Applied Metal Cutting Lubricant

RTD[®] Compound is a soft paste for use in reaming, tapping and drilling and other metal cutting operations. RTD[®] Compound is suitable for all metals including hardened steels, nimonics and titaniums. Containing extreme pressure additives, RTD[®] Compound significantly reduces friction giving superb cutting performance.

Features

- Extends tool life.
- Improves surface finish.
- Allows increases removal rates.
- Reduces production costs.

Directions for Use

Apply directly to the tool or workpiece by brush, or by dipping tool into the compound.

Appearance	Brown paste
Odour	Mild pine
Shell 4-Ball	
Weld Load (Neat)	>800 kg
Weld Load (5% in Oil)	315 kg
Storage	Store at normal ambient temperature (5 to 30°C)
Pack Sizes – Part Codes	50g - 53020 500g - 53023 5 kg - 53026 18 kg - 53028 185 kg - 53029
Rolls Royce Specification	OMAT 1090 CSS137 Type B & C

Date: Jan-09

T +44 (0) 113 232 2600
F +44 (0) 113 232 2740
E customer-service@rocol.com
www.rocol.com

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67
Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of **ITW** Ltd



BS EN ISO 9001
Certificate No. FM 12448



BS EN ISO 14001
Certificate No. EMS 67596



OHSAS 18001
Certificate No. OHS 78173



INVESTOR IN PEOPLE

The information in this publication is based on our experience and reports from customers. There are many factors outside our control or knowledge which affect the use and performance of our products, for which reason it is given without responsibility.