

# Sentry Switched CDU

## Key Features

- > **High Density:** Single-power input feed; 24 outlets per enclosure (12 IEC C13 and 12 IEC C19 outlets)
- > **High Power Distribution:** 208V, 3-Phase power option; 50A Delta or 60A Wye or Delta power input feed option.
- > **Input Current Monitor:** Precisely measure the aggregate current draw (in amps) on each phase. On-site verification of the input current with LED digital displays. Remote verification via web browser or serial screen.
- > **Remote Power Management:** Power cycle individual power outlets, or groups of power outlets, to remotely reboot servers and network devices, anywhere in the world. Or, power-off unused power receptacles
- > **IP Access & Security:** Web interface, SSL, SSH, Telnet, SNMP, FTP, SNT, Syslog, LDAP, LDAPS, RADIUS, TACACS and RS-232 access
- > **SNMP Traps and Email alerts:** Provide automated alerts for power and environmental conditions
- > **Environmental Monitoring:** Each Switched CDU supports two external temperature & humidity probes and reports conditions thru the user interface without the need for additional IP addresses
- > **Add an Expansion Module:** Connect the Switched Expansion CDU (CX) to a Master unit (CW) for power monitoring of separate power circuits from a single IP address

## CW-24VD/VY 50/60A Overhead Power, Mixed Outlets

### High-Density Power Distribution

The Switched CDU combines remote configuration and management with power distribution and power and environmental monitoring. Reboot a single or dual-power server with one command. Receive SNMP or email-based alerts when power or environmental conditions exceed thresholds. Assign user specific access rights to designated outlets or groups.

This Switched CDU has a 69" length with top front power cord and was specifically designed for use in standard 42U equipment racks. With a middle LED display, network, and environmental ports the unit can be easily inverted via the web GUI or serial interface to work with either busway or raised floor power sources.

### Additional Benefits:



#### Branch Circuit Protection

The Sentry CDU Family meets the UL 60950-1 requirement for Branch Circuit Protection

- > UL-489 rated circuit breakers



#### Input Current Monitoring

Exclusive Digital True RMS current monitoring is critical to preventing overloads in high-density computing environments. LED digital display on the CDU enclosure report the input current of the branch circuit.



#### Temperature and Humidity

The Switched CDU supports two external 10ft (3m) probes. Each of these probes measure both temperature and humidity. Receive SNMP-based alerts or email notifications when conditions exceed defined thresholds.



#### Mixed Outlets

This Switched CDU combines both IEC 60320/C13 and IEC 60320/C19 switched outlets within a single CDU. For rebooting non-responsive servers & network devices.



Model	Available Input Voltages	Amperage	Available Input Cord	Outlets	Dimensions (L x W x D)
CW-24VDX451A9 CX-24VDX451A9*	240V, 3-phase Delta, 50/60Hz	60A	IEC Blue 9hr 3P+G Plug, 10'(3m), Top/Frt Cord	(12) IEC 60320/C13 (12) IEC 60320/C19	69.0 x 1.75 x 3.50 in. (1753 x 44 x 89 mm)
CW-24VDV451A9 CX-24VDV451A9*	240V, 3-phase Delta, 50/60Hz	50A	CS8365C Plug, 10'(3m), Top/Frt Cord	(12) IEC 60320/C13 (12) IEC 60320/C19	69.0 x 1.75 x 3.50 in. (1753 x 44 x 89 mm)
CW-24VYY451A9 CX-24VYY451A9*	208V, 3-phase Wye, 50/60Hz	60A	IEC Blue 9hr 3P+N+G Plug, 10'(3m), Top/Frt Cord	(12) IEC 60320/C13 (12) IEC 60320/C19	69.0 x 1.75 x 3.50 in. (1753 x 44 x 89 mm)

\* CX part numbers refer to the Expansion CDU

## Additional Features and Specifications

### Agency Approvals

- > US & Canada (cTUVus mark) to UL 60950-1:2003 and CAN/CSA 22.2 No. 60950-1-03
- > FCC Class A, Part 15
- > EMC to EN 55022 Class A, EN 55024, CISPR 22 Class A

### Communications and Security

- > 10/100 BaseT Ethernet
- > HTTP/HTTPS
- > SSLv3/TLSv1
- > SNMPv2
- > SSHv2
- > Telnet
- > LDAPv3
- > LDAPS
- > TACACS+
- > RADIUS
- > RS-232 (Serial)

### Branch Circuit Protection

- > Compliant to UL 60950-1

### Accessories

- > Optional Temperature & Humidity Probe
  - EMTH-1-1 Temperature & Humidity Probe, 10ft (3m)
- > Environmental Monitor
  - EMCU-1-1B allows up to (2) additional temperature & humidity probes, (1) water sensor, (4) dry contact closures, (1) analog-to-digital converter. Includes (1) temperature/humidity probe with unit.
- > SPM (Sentry Power Manager) Appliance:
  - Monitor and Manage multiple Sentry CDU's
  - Monitor and Manage all alarm conditions
  - Reporting and Trending
  - Group or Cluster outlets for reboot and power information

> 1U SPM Appliance



Expansion Module  
Model Numbers

- > CX-24VDX451A9
- > CX-24VDV451A9
- > CX-24VYY451A9



## Server Technology

HEADQUARTERS - NORTH AMERICA  
Server Technology, Inc.  
1040 Sandhill Drive  
Reno, NV 89521  
United States  
1.775.284.2000 Tel  
1.775.284.2065 Fax  
sales@servertech.com  
www.servertech.com  
www.servertechblog.com

EMEA  
Server Technology Intl  
Sienna Court  
The Broadway  
Maidenhead  
Berkshire  
SL6 1NJ  
United Kingdom  
+44 (0) 1628 509053 Tel  
+44 (0) 1628 509100 Fax  
salesintl@servertech.com

APAC  
Server Technology Intl  
37th Floor, Singapore Land Tower  
50 Raffles Place  
Singapore 048623  
+65 (0) 6829 7008 Tel  
+65 (0) 6234 4574 Fax  
salesintl@servertech.com